



CorePro Plastic LED bulbs

CorePro LEDbulb ND 13-100W A60 E27 827

CorePro, LEDbulb, A60, 100 W, E27, 2700 K, 1521 lm, CRI 80, 15000 hour(s), Plastic

CorePro, LEDbulb, A60, 100 W, E27, 2700 K, 1521 lm, CRI 80, 15000 hour(s), Plastic, 117 lm/W, EEL E, PF 0.54, Beam angle 180 degree(s), RGO, IP20, SVM 0.4, PstLM 1

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	1,521 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	117 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Photobiological safety according to EN 62471	RGO
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	13 W
Lamp Current (Nom)	105 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.54
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No

CorePro Plastic LED bulbs

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60
Net Weight (Piece)	0.045 kg

Approval and Application

Energy Efficiency Class	E
Energy Consumption kWh/1000 h	13 kWh
EPREL Registration Number	397615
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data



Order product name	CorePro LEDbulb ND 13-100W A60 E27 827
Full product name	CorePro LEDbulb ND 13-100W A60 E27 827
Full product code	872016916901200
Order code	929002306808
Material Nr. (12NC)	929002306808
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169169012
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169169029

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 13-100W A60 E27 827	60 mm	120 mm

Photometric data




General uniform lighting - CorePro LEDbulb ND 13-100W A60 E27 827

Light Distribution Diagram - CorePro LEDbulb ND 13-100W A60 E27 827

General uniform lighting - CorePro LEDbulb ND 13-100W A60 E27 827


CorePro Plastic LED bulbs

Photometric data




Spectral Power Distribution Colour - CorePro LEDbulb ND 13-100W A60 E27 827

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDbulb ND 13-100W A60 E27 827

