



Corepro LED Strip



CorePro LEDstrip 6W865 780LM/M 5M

A complete family that are bright, slim, safe & reliable. Choose the best fit for every projects, from 4 lumen packs/wattages, and 4 CCTs, and enjoy easy installation with slimness

Product data

General Information	
Driver included	No
Lighting Technology	LED
Warranty period	3 years
Light Technical	
Luminous Flux	780 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	130.00 lm/W
Color rendering index (CRI)	80
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Voltage	24 V
Initial CLO power consumption	27 W
Average CLO power consumption	0 W
Power Consumption	27 W
Power Factor (Fraction)	1
Cable	Cable 0,3 m without plug
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class III
Controls and Dimming	
Dimmable	Yes

Control interface	depends on driver (1-10V, DALI...)
Constant light output	No
Maximum dim level	10% (depends on dimmer, ELV)
Mechanical and Housing	
Reflector material	-
Overall length	5,000 mm
Overall width	8 mm
Overall height	1.3 mm
Dimensions (Height x Width x Depth)	1 x 8 x 5000 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Net Weight (Piece)	0.100 kg
Approval and Application	
Energy Efficiency Class	E
EPREL Registration Number	620721
Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Corepro LED Strip



Initial chromaticity	(0.3090, 0.3230) 5SDCM
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	35,000 hour(s)
Product Data	
Order product name	CorePro LEDstrip 6W865 780LM/M 5M
Full product name	CorePro LEDstrip 6W865 780LM/M 5M

Full product code	871951434414300
Order code	929002695402
Material Nr. (12NC)	929002695402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514344143
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514344150

Dimensional drawing



Photometric data



General uniform lighting - CorePro LEDstrip 6W865 780LM/M 5M

Light Distribution Diagram - CorePro LEDstrip 6W865 780LM/M 5M

