PHILIPS

Lighting

MASTER LED Strip

MAS LEDstrip 21.3W930 2400LM/M 5M

A complete family delivering superior light with great uniformity and safety. Choose the best fit for every projects, from 5 lumen packs/wattages, and 4 CCTs, and enjoy great reliable performance free of maintenance

Product data

General Information	
Driver included	No
Lighting Technology	LED
Warranty period	5 years

Light Technical	
Luminous Flux	2,400 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	112.00 lm/W
Color rendering index (CRI)	>90
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Input Voltage	24 V
Initial CLO power consumption	81 W
Average CLO power consumption	0 W
Power Consumption	81 W
Power Factor (Fraction)	1
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	Yes
Control interface	depends on driver (1-10V, DALI...)
Constant light output	Yes
Maximum dim level	10% (depends on dimmer, ELV)

Mechanical and Housing	
Reflector material	-
Overall length	5,000 mm
Overall width	8 mm
Overall height	1.3 mm
Dimensions (Height x Width x Depth)	1 x 8 x 5000 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Net Weight (Piece)	0.100 kg

Approval and Application	
Energy Efficiency Class	F
EPREL Registration Number	620717
Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

MASTER LED Strip

Initial chromaticity	(0.4338, 0.403) 3SDCM
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	60,000 hour(s)

Product Data	
Order product name	MAS LEDstrip 21.3W930 2400LM/M 5M
Full product name	MAS LEDstrip 21.3W930 2400LM/M 5M

Full product code	871951434466200
Order code	929002698002
Material Nr. (12NC)	929002698002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514344662
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514344679

Dimensional drawing

Photometric data



Light Distribution Diagram - MAS LEDstrip 21.3W930 2400LM/M 5M



General uniform lighting - MAS LEDstrip 21.3W930 2400LM/M 5M

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.