LED Lamps

LEDBulb 8W E27 965 230V 2PF/3 AU

LEDbulb, A60S, 76 W, E27, 6500 K, 910 lm, 25000 hour(s), Plastic

LEDbulb, A60S, 76 W, E27, 6500 K, 910 lm, 25000 hour(s), Plastic, 113 lm/W

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb

Light Technical	
Color Code	965 [CCT of 6500K]
Color Code	965 [CCT of 6500K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	910 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	113 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	65 mA
Wattage Equivalent	76 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	95 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	110 mm
Overall width	60 mm
Overall height	110 mm
Dimensions (Height x Width x Depth)	110 x 60 x 110 mm
Bulb Shape	A60S

LED Lamps

Net Weight (Piece)	0.042 kg

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

Application Conditions

Wireless Technology	Not applicable

Product Data

Order product name	LEDBulb 8W E27 965 230V 2PF/3 AU
Full product name	LEDBulb 8W E27 965 230V 2PF/3 AU
Full product code	871869968804200
Order code	929003007319
Material Nr. (12NC)	929003007319
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8718699688042
Numerator - Packs per outer box	3
EAN/UPC - Case	8718699688059

Dimensional drawing



Product	D	C
LEDBulb 8W E27 965 230V 2PF/3 AU	60 mm	110 mm

Photometric data



General uniform lighting - LEDBulb 8W E27 965 230V 2PF/3 AU



Light Distribution Diagram - LEDBulb 8W E27 965 230V 2PF/3 AU

LED Lamps

Photometric data



Spectral Power Distribution Colour - LEDBulb 8W E27 965 230V 2PF/3 AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 8W E27 965 230V 2PF/3 AU

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.