



LED Lamps

LEDBulb 12W B22 930 230V 1PF/6 AU

LEDbulb, A60M, 98 W, B22, 3000 K, 1360 lm, 25000 hour(s), Plastic

LEDbulb, A60M, 98 W, B22, 3000 K, 1360 lm, 25000 hour(s), Plastic, 113 lm/W

Product data

General Information	
Cap-Base	B22
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDBulb
Light Technical	
Color Code	930 [CCT of 3000K]
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,360 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	113 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	12 W

Lamp Current (Nom)	105 mA
Wattage Equivalent	98 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	110 mm
Overall width	60 mm
Overall height	110 mm
Dimensions (Height x Width x Depth)	110 x 60 x 110 mm
Bulb Shape	A60M

LED Lamps

Net Weight (Piece)	0.060 kg
--------------------	----------

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	LEDBulb 12W B22 930 230V 1PF/6 AU
--------------------	-----------------------------------

Full product name	LEDBulb 12W B22 930 230V 1PF/6 AU
Full product code	871869965181700
Order code	929003008299
Material Nr. (12NC)	929003008299
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699651817
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699651824



Dimensional drawing



Product

LEDBulb 12W B22 930 230V 1PF/6 AU

Photometric data




General uniform lighting - LEDBulb 12W B22 930 230V 1PF/6 AU

Light Distribution Diagram - LEDBulb 12W B22 930 230V 1PF/6 AU

LED Lamps

Photometric data




Spectral Power Distribution Colour - LEDBulb 12W B22 930 230V 1PF/6 AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 12W B22 930 230V 1PF/6 AU

