



Ecofit LED tubes T8

Ecofit E Mains 600mm 8W 765 T8

Ecofit, LEDtube, T8, Mains, Single-end, 600 mm, 220-240 V, 8 W, 18W TL-D, 6500 K, 800 lm, 15000 hour(s)

Ecofit, LEDtube, T8, Mains, Single-end, 600 mm, 220-240 V, 8 W, LED alternative to 18W TL-D, 6500 K, 800 lm, 15000 hour(s), 100 lm/W, G13, Beam angle 240 degree(s), Glass

Product data

General Information	
Cap-Base	G13
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	765 [CCT of 6500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	800 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<7
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	8 W
Lamp Current (Nom)	70 mA
Wattage Equivalent	18 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	18W TL-D
Ballast Compatibility	Mains
Temperature	
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	600 mm

Ecofit LED tubes T8

Bulb Shape	T8
Net Weight (Piece)	0.120 kg
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C
Application Conditions	
Wireless Technology	Not applicable



Product Data	
Order product name	Ecofit E Mains 600mm 8W 765 T8
Full product name	Ecofit E Mains 600mm 8W 765 T8
Full product code	871951436058700
Order code	36058700
Material Nr. (12NC)	929003087411
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514360587
Numerator - Packs per outer box	20
EAN/UPC - Case	8719514360594

Dimensional drawing



Product	D1	D2	A1	A2	A3
Ecofit E Mains 600mm 8W 765 T8	25.7 mm	28 mm	1,198.2 mm	595.5 mm	602.5 mm

Photometric data




Light Distribution Diagram - Ecofit E Mains 600mm 8W 765 T8

General uniform lighting - Ecofit E Mains 600mm 8W 765 T8


Ecofit LED tubes T8

Photometric data



Spectral Power Distribution Colour - Ecofit E Mains 600mm 8W 765 T8

Lifetime



Lumen Maintenance Diagram - Ecofit E Mains 600mm 8W 765 T8

