



# LED PAR20

## 5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB

CorePro, LEDspot, PAR20, 50 W, E26, 3000 K, 600 lm, 25000 hour(s), Plastic

CorePro, LEDspot, PAR20, 50 W, E26, 3000 K, 600 lm, 25000 hour(s), Plastic, 109 lm/W

### Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	600 lm
Luminous Intensity (Nom)	1,000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	109 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	5.5 W

Lamp Current (Nom)	65 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR20
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.050 kg

# LED PAR20

## Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-40 to +45 °C

## Application Conditions


can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

## Product Data

Order product name	5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB
--------------------	--------------------------------------



Full product name	5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB
Order code	929003739604
Material Nr. (12NC)	929003739604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677586386
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677586381

## Dimensional drawing



Product	D	C
5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB	64 mm	87 mm

## Photometric data




Accent Lighting Spots - 5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB

Spectral Power Distribution Colour - 5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB


# LED PAR20

## Photometric data




Light Distribution Diagram - 5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5.5PAR20/COR/F40/930/DIM/P/T20 6/1FB

