



# Dipswitch LED bulb

## LEDBulb 9W E27 DS FR DIM 1PF/6 AU

LEDbulb, A60, 60 W, E27, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 900 lm, 15000 hour(s), Plastic

LEDbulb, A60, 60 W, E27, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 900 lm, 15000 hour(s), Plastic, 100 lm/W

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	2700K/3000K/4000K/5000K/6500K
Beam Angle (Nom)	200 degree(s)
Luminous Flux	900 lm
Color Designation	2700K/3000K/4000K/5000K/6500K
Correlated Color Temperature (Nom)	2700 3000 4000 5000 6500 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	9 W
Lamp Current (Nom)	40 mA


Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	115 mm
Overall width	60 mm
Overall height	115 mm
Dimensions (Height x Width x Depth)	115 x 60 x 115 mm
Bulb Shape	A60

# Dipswitch LED bulb

Net Weight (Piece)	0.043 kg
<b>Approval and Application</b>	
EU RoHS compliant	Yes
Warranty	2 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C
<b>Application Conditions</b>	
Wireless Technology	Not applicable



<b>Product Data</b>	
Order product name	LEDBulb 9W E27 DS FR DIM 1PF/6 AU
Full product name	LEDBulb 9W E27 DS FR DIM 1PF/6 AU
Full product code	872016930073600
Order code	929003785219
Material Nr. (12NC)	929003785219
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169300736
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169300743

## Dimensional drawing



Product	D	C
LEDBulb 9W E27 DS FR DIM 1PF/6 AU	60 mm	115 mm

## Photometric data




Spectral Power Distribution Colour - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

General uniform lighting - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

# Dipswitch LED bulb

## Photometric data



Light Distribution Diagram - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

