



# Dipswitch LED bulb

## LEDBulb 9W E27 DS FR DIM 1PF/6 AU

LEDbulb, A60, 60 W, E27, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 900 lm, 15000 hour(s), Plastic

Not sure about the color that will best fit your application? No need to worry. Philips Dipswitch LED bulb offer 5 colors in one product and is easy-to-operate by switching the button to change the color.

### Product data

General Information		Lamp Current (Nom)	
Cap-Base	E27		40 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	60 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LEDbulb	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	2700K/3000K/4000K/5000K/6500K	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	200 degree(s)		
Luminous Flux	900 lm	Controls and Dimming	
Color Designation	2700K/3000K/4000K/5000K/6500K	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	2700 3000 4000 5000 6500 K		
Luminous Efficacy (rated) (Nom)	100 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	80	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Overall length	115 mm
		Overall width	60 mm
		Overall height	115 mm
		Dimensions (Height x Width x Depth)	115 x 60 x 115 mm
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power Consumption	9 W		

# Dipswitch LED bulb


Bulb Shape	A60
Net Weight (Piece)	0.043 kg
<b>Approval and Application</b>	
EU RoHS compliant	Yes
Warranty	2 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

## Product Data

Order product name	LEDBulb 9W E27 DS FR DIM 1PF/6 AU
--------------------	-----------------------------------



Full product name	LEDBulb 9W E27 DS FR DIM 1PF/6 AU
Full product code	872016930073600
Order code	929003785219
Material Nr. (12NC)	929003785219
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169300736
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169300743

## Dimensional drawing



Product	D	C
LEDBulb 9W E27 DS FR DIM 1PF/6 AU	60 mm	115 mm

## Photometric data




© 2024 Philips Lighting B.V. Page 11

Spectral Power Distribution Colour - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

General uniform lighting - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

# Dipswitch LED bulb

## Photometric data



Light Distribution Diagram - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 9W E27 DS FR DIM 1PF/6 AU

