



Dipswitch LED bulb

LEDBulb 9W B22 DS FR DIM 1PF/6 AU

LEDbulb, A60, 60 W, B22, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 900 lm, 15000 hour(s), Plastic

Not sure about the color that will best fit your application? No need to worry. Philips Dipswitch LED bulb offer 5 colors in one product and is easy-to-operate by switching the button to change the color.

Product data

General Information	
Cap-Base	B22
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	2700K/3000K/4000K/5000K/6500K
Beam Angle (Nom)	200 degree(s)
Luminous Flux	900 lm
Color Designation	2700K/3000K/4000K/5000K/6500K
Correlated Color Temperature (Nom)	2700 3000 4000 5000 6500 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	9 W

Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	114 mm
Overall width	60 mm
Overall height	114 mm
Dimensions (Height x Width x Depth)	114 x 60 x 114 mm

Dipswitch LED bulb

Bulb Shape	A60
Net Weight (Piece)	0.045 kg

Approval and Application

EU RoHS compliant	Yes
Warranty	2 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	LEDBulb 9W B22 DS FR DIM 1PF/6 AU
Full product name	LEDBulb 9W B22 DS FR DIM 1PF/6 AU
Full product code	872016930075000
Order code	929003785319
Material Nr. (12NC)	929003785319
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169300750
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169300767

Dimensional drawing



Product	D	C
LEDBulb 9W B22 DS FR DIM 1PF/6 AU	60 mm	114 mm

Photometric data




General uniform lighting - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

Spectral Power Distribution Colour - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

Dipswitch LED bulb

Photometric data



Light Distribution Diagram - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

