



Multi-CCT Dimmable LED bulbs

LEDBulb 9W B22 DS FR DIM 1PF/6 AU

LEDbulb, A60, 60 W, B22, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 900 lm, 15000 h, Plastic

LEDbulb, A60, 60 W, B22, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 900 lm, 15000 h, Plastic, 100 lm/W

Product data

General Information		Power Consumption	
Cap-Base	B22	Lamp Current (Nom)	40 mA
Nominal lifetime	15,000 h	Wattage Equivalent	60 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LEDbulb	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.7
Color Code	2700K/3000K/4000K/5000K/6500K	Voltage (Nom)	220-240 V
Beam Angle (Nom)	200 degree(s)	Temperature	
Luminous Flux	900 lm	T-Case Maximum (Nom)	80 °C
Color Designation	2700K/3000K/4000K/5000K/6500K	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 3000 4000 5000 6500 K	Dimmable	Only with specific dimmers
Luminous Efficacy (rated) (Nom)	100 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	80	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Overall length	114 mm
Operating and Electrical		Overall width	60 mm
Input Frequency	50 to 60 Hz		

Multi-CCT Dimmable LED bulbs

Overall height	114 mm
Dimensions (Height x Width x Depth)	114 x 60 x 114 mm
Bulb Shape	A60
Net Weight (Piece)	0.045 kg

Approval and Application

EU RoHS compliant	Yes
Warranty	2 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	LEDBulb 9W B22 DS FR DIM 1PF/6 AU
Full product name	LEDBulb 9W B22 DS FR DIM 1PF/6 AU
Full product code	872016930075000
Order code	929003785319
Material Nr. (12NC)	929003785319
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169300750
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169300767

Dimensional drawing



Product	D	C
LEDBulb 9W B22 DS FR DIM 1PF/6 AU	60 mm	114 mm

Photometric data




General uniform lighting - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

Spectral Power Distribution Colour - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

Multi-CCT Dimmable LED bulbs

Photometric data



Light Distribution Diagram - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDBulb 9W B22 DS FR DIM 1PF/6 AU

