



CorePro LED capsule MV

CorePro LEDcapsule 1.9-25W ND G9 830

CorePro, LEDspot, G9, 25 W, G9, 3000 K, 220 lm, CRI 80, 15000 hour(s), Plastic

CorePro, LEDspot, G9, 25 W, G9, 3000 K, 220 lm, CRI 80, 15000 hour(s), Plastic, 115 lm/W, EEL E, PF 0.5, Beam angle 320 degree(s), RG0, IP20, SVM 0.4, PstLM 1

Product data

General Information	
Cap-Base	G9
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	320 degree(s)
Luminous Flux	220 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	1.9 W
Lamp Current (Nom)	17 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	92 °C
Controls and Dimming	
Dimmable	No

CorePro LED capsule MV

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	G9
Net Weight (Piece)	0.006 kg

Approval and Application

Energy Efficiency Class	E
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	1932587
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per 1 EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data



Order product name	CorePro LEDcapsule 1.9-25W ND G9 830
Full product name	CorePro LEDcapsule 1.9-25W ND G9 830
Full product code	872016930183200
Order code	30183200
Material Nr. (12NC)	929003790602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169301832
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169301849

Dimensional drawing



Product	D	C
CorePro LEDcapsule 1.9-25W ND G9 830	14 mm	43 mm

Photometric data




General uniform lighting - CorePro LEDcapsule 1.9-25W ND G9 830

Light Distribution Diagram - CorePro LEDcapsule 1.9-25W ND G9 830

CorePro LED capsule MV

Photometric data




Spectral Power Distribution Colour - CorePro LEDcapsule 1.9-25W ND G9 830

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDcapsule 1.9-25W ND G9 830

