



LED Corn Cobs

180-130-100CC/LED/3PW/750/EX39 BB 3/1

LED, Corncob, Mains, 100 W, 130 W, 180 W, HPS
 400/310/250W, MH 400/400/350W, EX39, 5000 K, 30000 lm,
 50000 hour(s)

LED, Corncob, Mains, 100 W, 130 W, 180 W, EX39, 5000 K, 30000 lm, 50000
 hour(s), 166 lm/W, RG1

Product data

General Information	
Cap-Base	EX39
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Warranty period	5 years
Light Technical	
Color Code	750 [CCT of 5000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	30,000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	166 lm/W
Color Consistency	<6
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	100 130 180 W
Lamp Current (Nom)	900 1,600 mA
Starting Time (Nom)	2 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	HIB_UL Type B (UL classified+RU)
Wattage Equivalent (LED HID only)	HPS 400/310/250W MH 400/400/350W
Ballast Compatibility	Mains

Temperature	
T-Case Maximum (Nom)	34.7 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear

LED Corn Cobs

Bulb Shape	Corncob
Net Weight (Piece)	0.620 kg

Approval and Application

Energy Saving Product	Yes
Energy Consumption kWh/1000 h	180 kWh
EU RoHS compliant	Yes
Ambient temperature range	-40 to +45 °C


Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data


Order product name	180-130-100CC/LED/3PW/750/EX39 BB 3/1
Full product name	180-130-100CC/LED/3PW/750/EX39 BB 3/1
Order code	929004280504
Material Nr. (12NC)	929004280504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677607432
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677607437

Dimensional drawing




Product	D	C
180-130-100CC/LED/3PW/750/EX39 BB 3/1	77.5 mm	250 mm

Photometric data




Light Distribution Diagram - 180-130-100CC/LED/3PW/750/EX39 BB 3/1



Spectral Power Distribution Colour - 180-130-100CC/LED/3PW/750/EX39 BB 3/1

LED Corn Cobs

Photometric data



General Parameters 43
Photometric Data 44
Page 10

General uniform lighting - 180-130-100CC/LED/3PW/750/EX39 BB 3/1

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 180-130-100CC/LED/3PW/750/EX39 BB 3/1

