



Tornado T2

12 W (40 W) E27 cap Warm white Spiral energy saving bulb

Tornado has outstanding brightness which makes your colors appear more Vivid. It fits everywhere due to its compact design With comprehensive product range, it allows easy replacement of incandescent lamps all the way

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	E27		
Nominal lifetime	8,000 hour(s)		
Switching Cycle	5,000		
Rated Lifetime (Hours)	8,000 hour(s)		
Lighting Technology	Compact Fluorescent Integrated		
Light Technical		Operating and Electrical	
Color Code	827 [CCT of 2700K]	Line Frequency	50 or 60 Hz
Luminous Flux	741 lm	Input Frequency	50 or 60 Hz
Color Designation	Warm White (WW)	Power Consumption	12 W
Chromaticity Coordinate X (Nom)	463	Lamp Current (Nom)	90 mA
Chromaticity Coordinate Y (Nom)	420	Starting Time (Nom)	0.3 s
Correlated Color Temperature (Nom)	2700 K	Power Factor (Fraction)	0.6
Luminous Efficacy (rated) (Nom)	61 lm/W	Voltage (Nom)	220-240 V
Color rendering index (CRI)	82	Controls and Dimming	
		Dimmable	No
		Mechanical and Housing	
		Bulb Shape	Spiral

Tornado T2

Net Weight (Piece)	0.051 kg
Approval and Application	
Mercury (Hg) Content (Nom)	1.5 mg
Energy Consumption kWh/1000 h	12 kWh
Product Data	
Order product name	12 W (40 W) E27 cap Warm white Spiral energy saving bulb
Full product name	12 W (40 W) E27 cap Warm white Spiral energy saving bulb

Full product code	871829121834000
Order code	929689868501
Material Nr. (12NC)	929689868501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291218340
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291218357

Dimensional drawing



Product	D (max)	C (max)	F (max)
12 W (40 W) E27 cap Warm white Spiral energy saving bulb	47.5 mm	94.0 mm	40.5 mm

