



Tornado T2

12W (40W) B22 Cool daylight Spiral

Tornado has outstanding brightness which makes your colors appear more Vivid. It fits everywhere due to its compact design. With comprehensive product range, it allows easy replacement of incandescent lamps all the way.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information	
Cap-Base	B22
Nominal lifetime	8,000 hour(s)
Switching Cycle	5,000
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	700 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	58 lm/W
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	12 W
Lamp Current (Nom)	90 mA
Starting Time (Nom)	0.3 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Spiral

Tornado T2

Net Weight (Piece)	0.051 kg
Approval and Application	
Mercury (Hg) Content (Nom)	1.5 mg
Energy Consumption kWh/1000 h	12 kWh
Product Data	
Order product name	12W (40W) B22 Cool daylight Spiral
Full product name	12W (40W) B22 Cool daylight Spiral

Full product code	871829121832600
Order code	929689888601
Material Nr. (12NC)	929689888601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291218326
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291218333

Dimensional drawing



Product	D (max)	C (max)	F (max)
12W (40W) B22 Cool daylight Spiral	47.5 mm	92.5 mm	40.5 mm

