



Uni Posttop Classic: Urban Street Light targets at residential areas, pathways, Plazas, etc.

Uni Posttop Classic

Inspired by the well-known street lanterns in 20th Century, the Philips Uni Posttop classic mixes the conventional classic with Philips's modern design, meeting various criteria in quality and safety while providing outstanding lumen performance under the standard of street lighting. The classical housing creates a contemporary feel which fits not only traditional settings but also modern environments. In addition, to cater for different needs in application scenarios, Philips Uni Posttop provides two optics option, i.e., symmetric and asymmetric. Besides, the Philips Uni Posttop classic features a NEMA socket in option, which enables this fixture ready for smart system based on 1-10V or Dali 2.0 interface.

Benefits

- Contemporary shape inspired by traditional lanterns.
- Suits not only traditional settings but also modern environments.
- Ready for Interact and other smart systems.

Features


- Optimized optics for efficient and comfortable lighting levels
- Ready to be paired with Interact and other lighting controls
- Direct retrofit for conventional classic looking post-top

Uni Posttop Classic

Application

- Road and Street
- Parks and Plazas
- Residential
- Main urban roads and streets, side and residential roads and streets
- City centers and historical areas
- Cycle and pedestrian paths, squares, parks and playground

Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	70
Mechanical and Housing	
Optical cover type	Clear dome
Housing Color	Black
Mech. impact protection code	IK09
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
Flammability mark	-

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401700004	BDP400 LED WW 220V 80W TA PSD P7 9005	730 warm white	3000 K	9,600 lm
911401700014	BDP400 LED WW 220V 80W TS PSU 9005	730 warm white	3000 K	9,600 lm
911401700024	BDP400 LED WW 220V 80W TS PSD P7 9005	730 warm white	3000 K	9,600 lm
911401700034	BDP400 LED NW 220V 80W TA PSU 9005	740 neutral white	4000 K	9,600 lm
911401700044	BDP400 LED NW 220V 80W TA PSD P7 9005	740 neutral white	4000 K	9,600 lm
911401700054	BDP400 LED NW 220V 80W TS PSU 9005	740 neutral white	4000 K	9,600 lm
911401700064	BDP400 LED NW 220V 80W TS PSD P7 9005	740 neutral white	4000 K	9,600 lm
911401799833	BDP400 LED WW 220V 30W TA PSU 9005	730 warm white	3000 K	3,600 lm
911401799843	BDP400 LED WW 220V 30W TA PSD P7 9005	730 warm white	3000 K	3,600 lm
911401799853	BDP400 LED WW 220V 30W TS PSU 9005	730 warm white	3000 K	3,600 lm
911401799863	BDP400 LED WW 220V 30W TS PSD P7 9005	730 warm white	3000 K	3,600 lm
911401799873	BDP400 LED NW 220V 30W TA PSU 9005	740 neutral white	4000 K	3,600 lm
911401799883	BDP400 LED NW 220V 30W TA PSD P7 9005	740 neutral white	4000 K	3,600 lm

Order Code	Full Product Name	Light source	Correlated Color	
		color	Temperature (Nom)	Luminous Flux
911401799893	BDP400 LED NW 220V 30W TS PSU 9005	740 neutral white	4000 K	3,600 lm
911401799903	BDP400 LED NW 220V 30W TS PSD P7 9005	740 neutral white	4000 K	3,600 lm
911401799913	BDP400 LED WW 220V 60W TA PSU 9005	730 warm white	3000 K	7,200 lm
911401799923	BDP400 LED WW 220V 60W TA PSD P7 9005	730 warm white	3000 K	7,200 lm
911401799933	BDP400 LED WW 220V 60W TS PSU 9005	730 warm white	3000 K	7,200 lm
911401799943	BDP400 LED WW 220V 60W TS PSD P7 9005	730 warm white	3000 K	7,200 lm
911401799953	BDP400 LED NW 220V 60W TA PSU 9005	740 neutral white	4000 K	7,200 lm
911401799963	BDP400 LED NW 220V 60W TA PSD P7 9005	740 neutral white	4000 K	7,200 lm
911401799973	BDP400 LED NW 220V 60W TS PSU 9005	740 neutral white	4000 K	7,200 lm
911401799983	BDP400 LED NW 220V 60W TS PSD P7 9005	740 neutral white	4000 K	7,200 lm
911401799993	BDP400 LED WW 220V 80W TA PSU 9005	730 warm white	3000 K	9,600 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401700004	BDP400 LED WW 220V 80W TA PSD P7 9005	80 W	911401799883	BDP400 LED NW 220V 30W TA PSD P7 9005	30 W
911401700014	BDP400 LED WW 220V 80W TS PSU 9005	80 W	911401799893	BDP400 LED NW 220V 30W TS PSU 9005	30 W
911401700024	BDP400 LED WW 220V 80W TS PSD P7 9005	80 W	911401799903	BDP400 LED NW 220V 30W TS PSD P7 9005	30 W
911401700034	BDP400 LED NW 220V 80W TA PSU 9005	80 W	911401799913	BDP400 LED WW 220V 60W TA PSU 9005	60 W
911401700044	BDP400 LED NW 220V 80W TA PSD P7 9005	80 W	911401799923	BDP400 LED WW 220V 60W TA PSD P7 9005	60 W
911401700054	BDP400 LED NW 220V 80W TS PSU 9005	80 W	911401799933	BDP400 LED WW 220V 60W TS PSU 9005	60 W
911401700064	BDP400 LED NW 220V 80W TS PSD P7 9005	80 W	911401799943	BDP400 LED WW 220V 60W TS PSD P7 9005	60 W
911401799833	BDP400 LED WW 220V 30W TA PSU 9005	30 W	911401799953	BDP400 LED NW 220V 60W TA PSU 9005	60 W
911401799843	BDP400 LED WW 220V 30W TA PSD P7 9005	30 W	911401799963	BDP400 LED NW 220V 60W TA PSD P7 9005	60 W
911401799853	BDP400 LED WW 220V 30W TS PSU 9005	30 W	911401799973	BDP400 LED NW 220V 60W TS PSU 9005	60 W
911401799863	BDP400 LED WW 220V 30W TS PSD P7 9005	30 W	911401799983	BDP400 LED NW 220V 60W TS PSD P7 9005	60 W
911401799873	BDP400 LED NW 220V 30W TA PSU 9005	30 W	911401799993	BDP400 LED WW 220V 80W TA PSU 9005	80 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401700004	BDP400 LED WW 220V 80W TA PSD P7 9005	Yes	911401799843	BDP400 LED WW 220V 30W TA PSD P7 9005	Yes
911401700014	BDP400 LED WW 220V 80W TS PSU 9005	No	911401799853	BDP400 LED WW 220V 30W TS PSU 9005	No
911401700024	BDP400 LED WW 220V 80W TS PSD P7 9005	Yes	911401799863	BDP400 LED WW 220V 30W TS PSD P7 9005	Yes
911401700034	BDP400 LED NW 220V 80W TA PSU 9005	No	911401799873	BDP400 LED NW 220V 30W TA PSU 9005	No
911401700044	BDP400 LED NW 220V 80W TA PSD P7 9005	Yes	911401799883	BDP400 LED NW 220V 30W TA PSD P7 9005	Yes
911401700054	BDP400 LED NW 220V 80W TS PSU 9005	No	911401799893	BDP400 LED NW 220V 30W TS PSU 9005	No
911401700064	BDP400 LED NW 220V 80W TS PSD P7 9005	Yes	911401799903	BDP400 LED NW 220V 30W TS PSD P7 9005	Yes
911401799833	BDP400 LED WW 220V 30W TA PSU 9005	No	911401799913	BDP400 LED WW 220V 60W TA PSU 9005	No

Uni Posttop Classic

Order Code	Full Product Name	Dimmable
911401799923	BDP400 LED WW 220V 60W TA PSD P7 9005	Yes
911401799933	BDP400 LED WW 220V 60W TS PSU 9005	No
911401799943	BDP400 LED WW 220V 60W TS PSD P7 9005	Yes
911401799953	BDP400 LED NW 220V 60W TA PSU 9005	No

Order Code	Full Product Name	Dimmable
911401799963	BDP400 LED NW 220V 60W TA PSD P7 9005	Yes
911401799973	BDP400 LED NW 220V 60W TS PSU 9005	No
911401799983	BDP400 LED NW 220V 60W TS PSD P7 9005	Yes
911401799993	BDP400 LED WW 220V 80W TA PSU 9005	No

