



**BN058 offers exceptional value. It is Perfect for your everyday lighting installations. It provides quality light and substantial energy and maintenance savings.**

### **Essential Smartbright T5 Batten**

BN058 Batten provide flexibility to customer to choose from 3 CCT and 4 different size and lumen packages, based on their specific need.

#### **Benefits**

- Slim and trunkable, integrated design
- Polycarbonate housing with one pc extrusion process
- Slim profile: Ideal for task lighting / cove lighting applications

# Essential Smartbright T5 Batten

## Features

- 15,000 hrs life, L70/B50
- 1 Year warranty
- 4 lengths, 3 colors Increased number of options for easy application
- CRI 70, SDCM < 7, 85lm/W
- Mounting accessories included

## Application

- Hospitality
- Offices
- Residential

Light Technical	
Color rendering index (CRI)	>70
Luminous Efficacy (rated) (Nom)	85 lm/W
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

## Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
31397999	BN058C LED9/WW L900 GM	3000 K	900 lm
31398699	BN058C LED9/NW L900 GM	4000 K	900 lm
31399399	BN058C LED9/CW L900 GM	6500 K	900 lm
31400699	BN058C LED5/WW L600 GM	3000 K	600 lm
31401399	BN058C LED5/NW L600 GM	4000 K	600 lm
31402099	BN058C LED5/CW L600 GM	6500 K	600 lm
31394899	BN058C LED11/WW L1200 GM	3000 K	1,200 lm
31395599	BN058C LED11/NW L1200 GM	4000 K	1,200 lm
31396299	BN058C LED11/CW L1200 GM	6500 K	1,200 lm
31403799	BN058C LED3/WW L300 GM	3000 K	300 lm
31404499	BN058C LED3/NW L300 GM	4000 K	300 lm
31405199	BN058C LED3/CW L300 GM	6500 K	300 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
31397999	BN058C LED9/WW L900 GM	9.6 W
31398699	BN058C LED9/NW L900 GM	9.6 W
31399399	BN058C LED9/CW L900 GM	9.6 W
31400699	BN058C LED5/WW L600 GM	6.5 W
31401399	BN058C LED5/NW L600 GM	6.5 W
31402099	BN058C LED5/CW L600 GM	6.5 W

Order Code	Full Product Name	Power Consumption
31394899	BN058C LED11/WW L1200 GM	13 W
31395599	BN058C LED11/NW L1200 GM	13 W
31396299	BN058C LED11/CW L1200 GM	13 W
31403799	BN058C LED3/WW L300 GM	3.4 W
31404499	BN058C LED3/NW L300 GM	3.4 W
31405199	BN058C LED3/CW L300 GM	3.4 W

## Essential Smartbright T5 Batten

