

Dipswitch LED bulb

9377853



One choice, five colors

Not sure about the color that will best fit your application? No need to worry. Philips Dipswitch LED bulb offer 5 colors in one product and is easy-to-operate by switching the button to change the color.

Benefits

- Enjoy 5 possible light colors in one product
- Change the color of your light easily with by switching the button on the product
- No guesswork

Applications

- Home
- Offices
- Education

Features

- 5 color temperatures
- Dimmable
- Change the color by switching the button
- Lifetime up to 15,000 hours
- Easy retrofit

Versions



LEDStick 14W E27 DS FR DIM
1PF 6 AU RTP



LEDBulb 14W E27 DS FR DIM
1PF 6 AU RTP



LEDBulb 9W E27 DS FR DIM
1PF 6 AU RTP




LEDStick 10W E27 DS FR DIM
1PF 6 AU RTP


Dimensional drawing



Product	D	C
LEDBulb 14W E27 DS FR DIM 1PF/6 AU	60 mm	119 mm
LEDBulb 9W E27 DS FR DIM 1PF/6 AU	60 mm	115 mm



Product	D	C
LEDStick 14W E27 DS FR DIM 1PF/6 AU	41 mm	133 mm



Product	D	C
LEDStick 10W E27 DS FR DIM 1PF/6 AU	41 mm	107 mm

General Information

Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000

Light Technical

Color Code	2700K/3000K/4000K/5000K/6500K
Beam Angle (Nom)	200 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom) 80 °C

Controls and Dimming

Dimmable Only with specific dimmers

Mechanical and Housing

Bulb Finish Frosted

Approval and Application

Ambient temperature range -20 to +45 °C

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	1,400 lm	2700 K 3000 K 4000 K 5000 K 6500 K
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	1,400 lm	2700 K 3000 K 4000 K 5000 K 6500 K
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	900 lm	2700 K 3000 K 4000 K 5000 K 6500 K
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	1,000 lm	2700 K 3000 K 4000 K 5000 K 6500 K

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	14 W	100 W
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	14 W	100 W
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	9 W	60 W
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	10 W	75 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	Stick
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	A60
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	A60
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	Stick