



The new generation of energy-saving LED PLT 4P tube lighting

CorePro LED PLT 4P

The CorePro LED PLT 4P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly

Benefits

- Highly energy-efficient
- Easy installation
- Conventional form factor to fit into existing luminaire
- No mercury

Features

- Reduced operational cost thanks to lower energy consumption
- Lower maintenance cost thanks to 2-3 times longer lifetime than conventional lamps
- Fastest and easiest way to upgrade existing luminaires to LED technology
- Completely safe product and installation process

Application

- Hospitality, retail, office, industrial and home applications

CorePro LED PLT 4P

Versions



CorePro LED PLT HF Mains 16W
20250410



CorePro LED PLT HF Mains 13.5W
20250410





CorePro LED PLT HF Mains 6.5W
20250410



CorePro LED PLT HF Mains 9W
20250410

Dimensional drawing





Product	D1	D	A1	A2	A3
CorePro LED PLT HF 9W 830 4P GX24q-3	42 mm	42 mm	115 mm	127 mm	142 mm
CorePro LED PLT HF 9W 840 4P GX24q-3	42 mm	42 mm	115 mm	127 mm	142 mm
CorePro LED PLT HF/Mains 13.5W 830 4P	42 mm	42 mm	129 mm	141 mm	156 mm
CorePro LED PLT HF/Mains 13.5W 840 4P	42 mm	42 mm	129 mm	141 mm	156 mm
CorePro LED PLT HF/Mains 16W 830 4P	42 mm	42 mm	139 mm	151 mm	166 mm
CorePro LED PLT HF/Mains 16W 840 4P	42 mm	42 mm	139 mm	151 mm	166 mm
CorePro LED PLT HF/Mains 6.5W 830 4P	42 mm	42 mm	93 mm	103 mm	119 mm
CorePro LED PLT HF/Mains 6.5W 840 4P	42 mm	42 mm	93 mm	103 mm	119 mm
CorePro LED PLT HF/Mains 9W 830 4P	42 mm	42 mm	115 mm	127 mm	142 mm
CorePro LED PLT HF/Mains 9W 840 4P	42 mm	42 mm	115 mm	127 mm	142 mm

Product	D1	D2	A1	A2	A3
CorePro LED PLT HF 6.5W 830 4P GX24q-2	42 mm	42 mm	93 mm	103 mm	119 mm
CorePro LED PLT HF 6.5W 840 4P GX24q-2	42 mm	42 mm	93 mm	103 mm	119 mm

CorePro LED PLT 4P

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLT HF 15W 830 4P GX24q-3	42 mm	42 mm	129 mm	141 mm	156 mm
CorePro LED PLT HF 15W 840 4P GX24q-3	42 mm	42 mm	129 mm	141 mm	156 mm

Product	D1	D2	A1	A2	A3
CorePro LED PLT HF 18.5W 830 4P GX24q-4	42 mm	42 mm	139 mm	151 mm	166 mm
CorePro LED PLT HF 18.5W 840 4P GX24q-4	42 mm	42 mm	139 mm	151 mm	166 mm

General Information	
Switching Cycle	200,000
Nominal lifetime	30,000 hour(s)
Light Technical	
Beam Angle (Nom)	120 degree(s)
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	PL-T

General Information

Order Code	Full Product Name	Cap-Base
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	GX24Q-3 Rotatable end-cap
929003576802	CorePro LED PLT HF 15W 840 4P GX24q-3	GX24Q-3 Rotatable end-cap
929004267202	CorePro LED PLT HF/Mains 16W 830 4P	GX24Q-4 Rotatable end-cap
929004267302	CorePro LED PLT HF/Mains 16W 840 4P	GX24Q-4 Rotatable end-cap
929003576302	CorePro LED PLT HF 6.5W 830 4P GX24q-2	GX24Q-2 Rotatable end-cap
929003576402	CorePro LED PLT HF 6.5W 840 4P GX24q-2	GX24Q-2 Rotatable end-cap
929004267002	CorePro LED PLT HF/Mains 13.5W 830 4P	GX24Q-3 Rotatable end-cap
929004267102	CorePro LED PLT HF/Mains 13.5W 840 4P	GX24Q-3 Rotatable end-cap
929003576502	CorePro LED PLT HF 9W 830 4P GX24q-3	GX24Q-3 Rotatable end-cap
929003576602	CorePro LED PLT HF 9W 840 4P GX24q-3	GX24Q-3 Rotatable end-cap
929004266602	CorePro LED PLT HF/Mains 6.5W 830 4P	GX24Q-2 Rotatable end-cap
929004266702	CorePro LED PLT HF/Mains 6.5W 840 4P	GX24Q-2 Rotatable end-cap
929003576902	CorePro LED PLT HF 18.5W 830 4P GX24q-4	GX24Q-4 Rotatable end-cap
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	GX24Q-4 Rotatable end-cap
929004266802	CorePro LED PLT HF/Mains 9W 830 4P	GX24Q-3 Rotatable end-cap
929004266902	CorePro LED PLT HF/Mains 9W 840 4P	GX24Q-3 Rotatable end-cap

Light Technical

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	3000 K	830	1,620 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003576802	CorePro LED PLT HF 15W 840 4P GX24q-3	4000 K	840	1,800 lm

CorePro LED PLT 4P

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929004267202	CorePro LED PLT HF/ Mains 16W 830 4P	3000 K	830	2,100 lm
929004267302	CorePro LED PLT HF/ Mains 16W 840 4P	4000 K	840	2,250 lm
929003576302	CorePro LED PLT HF 6.5W 830 4P GX24q-2	3000 K	830	720 lm
929003576402	CorePro LED PLT HF 6.5W 840 4P GX24q-2	4000 K	840	800 lm
929004267002	CorePro LED PLT HF/ Mains 13.5W 830 4P	3000 K	830	1,620 lm
929004267102	CorePro LED PLT HF/ Mains 13.5W 840 4P	4000 K	840	1,800 lm
929003576502	CorePro LED PLT HF 9W 830 4P GX24q-3	3000 K	830	990 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003576602	CorePro LED PLT HF 9W 840 4P GX24q-3	4000 K	840	1,100 lm
929004266602	CorePro LED PLT HF/ Mains 6.5W 830 4P	3000 K	830	720 lm
929004266702	CorePro LED PLT HF/ Mains 6.5W 840 4P	4000 K	840	800 lm
929003576902	CorePro LED PLT HF 18.5W 830 4P GX24q-4	3000 K	830	2,100 lm
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	4000 K	840	2,250 lm
929004266802	CorePro LED PLT HF/ Mains 9W 830 4P	3000 K	830	990 lm
929004266902	CorePro LED PLT HF/ Mains 9W 840 4P	4000 K	840	1,100 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003576802	CorePro LED PLT HF 15W 840 4P GX24q-3	20K-80K Hz	20K-80K Hz	15 W	-
929004267202	CorePro LED PLT HF/ Mains 16W 830 4P	50 to 60 Hz	-	16 W	42 W
929004267302	CorePro LED PLT HF/ Mains 16W 840 4P	50 to 60 Hz	-	16 W	42 W
929003576302	CorePro LED PLT HF 6.5W 830 4P GX24q-2	20K-80K Hz	20K-80K Hz	6.5 W	-
929003576402	CorePro LED PLT HF 6.5W 840 4P GX24q-2	20K-80K Hz	20K-80K Hz	6.5 W	-
929004267002	CorePro LED PLT HF/ Mains 13.5W 830 4P	50 to 60 Hz	-	13.5 W	32 W
929004267102	CorePro LED PLT HF/ Mains 13.5W 840 4P	50 to 60 Hz	-	13.5 W	32 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003576602	CorePro LED PLT HF 9W 840 4P GX24q-3	20K-80K Hz	20K-80K Hz	9 W	-
929004266602	CorePro LED PLT HF/ Mains 6.5W 830 4P	50 to 60 Hz	-	6.5 W	18 W
929004266702	CorePro LED PLT HF/ Mains 6.5W 840 4P	50 to 60 Hz	-	6.5 W	18 W
929003576902	CorePro LED PLT HF 18.5W 830 4P GX24q-4	20K-80K Hz	20K-80K Hz	18.5 W	-
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	20K-80K Hz	20K-80K Hz	18.5 W	-
929004266802	CorePro LED PLT HF/ Mains 9W 830 4P	50 to 60 Hz	-	9 W	26 W

CorePro LED PLT 4P

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929004266902	CorePro LED PLT HF/ PLT HF/	50 to 60 Hz	-	9 W	26 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
	Mains 9W 840 4P				

Temperature


Order Code	Full Product Name	T-Case Maximum (Nom)
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	70 °C
929003576802	CorePro LED PLT HF 15W 840 4P GX24q-3	70 °C
929004267202	CorePro LED PLT HF/Mains 16W 830 4P	75 °C
929004267302	CorePro LED PLT HF/Mains 16W 840 4P	75 °C
929003576302	CorePro LED PLT HF 6.5W 830 4P GX24q-2	65 °C
929003576402	CorePro LED PLT HF 6.5W 840 4P GX24q-2	65 °C
929004267002	CorePro LED PLT HF/Mains 13.5W 830 4P	65 °C
929004267102	CorePro LED PLT HF/Mains 13.5W 840 4P	65 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003576502	CorePro LED PLT HF 9W 830 4P GX24q-3	65 °C
929003576602	CorePro LED PLT HF 9W 840 4P GX24q-3	65 °C
929004266602	CorePro LED PLT HF/Mains 6.5W 830 4P	55 °C
929004266702	CorePro LED PLT HF/Mains 6.5W 840 4P	55 °C
929003576902	CorePro LED PLT HF 18.5W 830 4P GX24q-4	75 °C
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	75 °C
929004266802	CorePro LED PLT HF/Mains 9W 830 4P	60 °C
929004266902	CorePro LED PLT HF/Mains 9W 840 4P	60 °C











Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	-20 °C to 35 °C	15 kWh
929003576802	CorePro LED PLT HF 15W 840 4P GX24q-3	-20 °C to 35 °C	15 kWh
929004267202	CorePro LED PLT HF/ Mains 16W 830 4P	-20 to +35 °C	16 kWh
929004267302	CorePro LED PLT HF/ Mains 16W 840 4P	-20 to +35 °C	16 kWh
929003576302	CorePro LED PLT HF 6.5W 830 4P GX24q-2	-20 °C to 35 °C	7 kWh
929003576402	CorePro LED PLT HF 6.5W 840 4P GX24q-2	-20 °C to 35 °C	7 kWh
929004267002	CorePro LED PLT HF/ Mains 13.5W 830 4P	-20 to +35 °C	14 kWh
929004267102	CorePro LED PLT HF/ Mains 13.5W 840 4P	-20 to +35 °C	14 kWh
929003576502	CorePro LED PLT HF 9W 830 4P GX24q-3	-20 °C to 35 °C	9 kWh
929003576602	CorePro LED PLT HF 9W 840 4P GX24q-3	-20 °C to 35 °C	9 kWh
929004266602	CorePro LED PLT HF/ Mains 6.5W 830 4P	-20 to +35 °C	7 kWh
929004266702	CorePro LED PLT HF/ Mains 6.5W 840 4P	-20 to +35 °C	7 kWh
929003576902	CorePro LED PLT HF 18.5W 830 4P GX24q-4	-20 °C to 35 °C	19 kWh
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	-20 °C to 35 °C	19 kWh
929004266802	CorePro LED PLT HF/ Mains 9W 830 4P	-20 to +35 °C	9 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929004266902	CorePro LED PLT HF/ Mains 9W 840 4P	-20 to +35 °C	9 kWh



CorePro LED PLT 4P



CorePro LED PLT 4P

