



Andal, Lampu sorot LED Hemat energi

SmartBright G3 LED Floodlight

Lampu Sorot LED SmartBright G3 adalah penerus baru dengan housing aluminium die-cast kokoh yang cocok untuk aplikasi umum di luar ruangan. Ini memberikan kemanjuran tinggi dan penghematan energi yang luar biasa.

Benefits

- Daya penerangan sistem tinggi
- Kualitas dan performa yang andal
- Desain yang kuat
- Awet

Features

- CCT: 6500K
- Daya: 10W, 20W, 30W, 50W, 70W, 100W, 150W dan 200W
- Tegangan masuk: 220V-240V
- Kemanjuran lumen hingga 120lm/w
- Suhu kerja: -25°C hingga +40°C
- Masa pakai 50.000 jam

Application

- Gudang penyimpanan
- Lanskap
- Arena dan Olahraga
- Cahaya arsitektur
- Papan iklan
- Pencahayaan area parkir
- Hiasan

SmartBright G3 LED Floodlight

Versions



SMARTBRIGHT G3 LED FLOODLIGHT



SmartBright G3 LED Floodlight



SMARTBRIGHT G3 LED FLOODLIGHT



SMARTBRIGHT G3 LED FLOODLIGHT



SMARTBRIGHT G3 LED FLOODLIGHT



SMARTBRIGHT G3 LED FLOODLIGHT







SmartBright G3 LED Floodlight








SMARTBRIGHT G3 LED FLOODLIGHT

Dimensional drawing



SmartBright G3 LED Floodlight

Dimensional drawing



Product details



BVP151 G3 SWB



SmartBright G3 LED Floodlight

SmartBright G3 LED Floodlight

Informasi Umum

Driver tercakup	Ya
Teknis Lampu	
Penyebaran sinar lampu luminer	110°
Warna sumber cahaya	865 cool daylight
Suhu Warna Terkorelasi (Nom)	6500 K
Indeks renderasi warna (CRI)	80
Jumlah sumber cahaya	1

Kontrol dan Peredupan

Tingkat redup maksimum	Tidak berlaku
------------------------	---------------

Mekanis dan Housing

Warna Housing	Abu-abu
Kode perlindungan masuknya debu dan air	IP65

Penyetujuan dan Aplikasi

Tanda CE	Tidak
Tanda dapat menyala	Untuk pemasangan pada permukaan mudah terbakar normal
Pengujian kawat pijar	Suhu 650 °C, durasi 30 detik

Informasi Umum

Order Code	Full Product Name	Alat	Jumlah unit alat
911401867286	BVP151 LED180/CW PSU 150W SWB G3 GM	-	1 unit
911401830987	BVP151 LED300/CW PSU 250W SWB G3 GM	EB	1 unit
911401864286	BVP151 LED60/CW PSU 50W SWB G3 GM	-	1 unit
911401868286	BVP151 LED240/CW PSU 200W SWB G3 GM	-	1 unit
911401866286	BVP151 LED120/CW PSU 100W SWB G3 GM	-	1 unit
911401865286	BVP151 LED84/CW PSU 70W SWB G3 GM	-	1 unit
911401831087	BVP151 LED360/CW PSU 300W SWB G3 GM	EB	2 unit
911401863286	BVP151 LED36/CW PSU 30W SWB G3 GM	-	1 unit

Teknis Lampu

Order Code	Full Product Name	Flux Cahaya
911401867286	BVP151 LED180/CW PSU 150W SWB G3 GM	18.000 lm
911401830987	BVP151 LED300/CW PSU 250W SWB G3 GM	30.000 lm
911401864286	BVP151 LED60/CW PSU 50W SWB G3 GM	6.000 lm
911401868286	BVP151 LED240/CW PSU 200W SWB G3 GM	24.000 lm

Order Code	Full Product Name	Flux Cahaya
911401866286	BVP151 LED120/CW PSU 100W SWB G3 GM	12.000 lm
911401865286	BVP151 LED84/CW PSU 70W SWB G3 GM	8.400 lm
911401831087	BVP151 LED360/CW PSU 300W SWB G3 GM	36.000 lm
911401863286	BVP151 LED36/CW PSU 30W SWB G3 GM	3.600 lm

Pengoperasian dan Kelistrikan

Order Code	Full Product Name	Konsumsi Daya
911401867286	BVP151 LED180/CW PSU 150W SWB G3 GM	150 W
911401830987	BVP151 LED300/CW PSU 250W SWB G3 GM	250 W
911401864286	BVP151 LED60/CW PSU 50W SWB G3 GM	50 W
911401868286	BVP151 LED240/CW PSU 200W SWB G3 GM	200 W

Order Code	Full Product Name	Konsumsi Daya
911401866286	BVP151 LED120/CW PSU 100W SWB G3 GM	100 W
911401865286	BVP151 LED84/CW PSU 70W SWB G3 GM	70 W
911401831087	BVP151 LED360/CW PSU 300W SWB G3 GM	300 W
911401863286	BVP151 LED36/CW PSU 30W SWB G3 GM	30 W

Kontrol dan Peredupan

Order Code	Full Product Name	Dapat diredupkan
911401867286	BVP151 LED180/CW PSU 150W SWB G3 GM	Tidak
911401830987	BVP151 LED300/CW PSU 250W SWB G3 GM	-
911401864286	BVP151 LED60/CW PSU 50W SWB G3 GM	Tidak
911401868286	BVP151 LED240/CW PSU 200W SWB G3 GM	Tidak

Order Code	Full Product Name	Dapat diredupkan
911401866286	BVP151 LED120/CW PSU 100W SWB G3 GM	Tidak
911401865286	BVP151 LED84/CW PSU 70W SWB G3 GM	Tidak
911401831087	BVP151 LED360/CW PSU 300W SWB G3 GM	-
911401863286	BVP151 LED36/CW PSU 30W SWB G3 GM	Tidak

Mekanis dan Housing

SmartBright G3 LED Floodlight

Order Code	Full Product Name	Tipe penutup optik	Kode pelindung dampak mekanis
911401867286	BVP151 LED180/CW PSU 150W SWB G3 GM	Kaca	IK08
911401830987	BVP151 LED300/CW PSU 250W SWB G3 GM	Kaca keras	IK08
911401864286	BVP151 LED60/CW PSU 50W SWB G3 GM	Kaca	IK07
911401868286	BVP151 LED240/CW PSU 200W SWB G3 GM	Kaca	IK08

Order Code	Full Product Name	Tipe penutup optik	Kode pelindung dampak mekanis
911401866286	BVP151 LED120/CW PSU 100W SWB G3 GM	Kaca	IK08
911401865286	BVP151 LED84/CW PSU 70W SWB G3 GM	Kaca	IK08
911401831087	BVP151 LED360/CW PSU 300W SWB G3 GM	Kaca keras	IK08
911401863286	BVP151 LED36/CW PSU 30W SWB G3 GM	Kaca	IK07

