



Product Description

Plusline Large

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime of 2000 hours

Features

- Clear tubular quartz bulb
- Constant light output during life
- Colour temperature 2900K
- Excellent colour rendering ($R_a = 100$)
- Limited burning position: $+\/-4^\circ$

Application

- Typically used in outdoor applications: billboards, car parks, security lighting and construction sites
- Also used in Indoor applications: homes, offices, shops and museums

Versions




8727900808551 - RFT


LPPR HLINEAR 0001

Plusline Large

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
1000 W R7s cap Clear Halogen linear lamp	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm



Product	D (max)	C (max)
Plusline L 500W 240-250V CL 1SL/4X50CT	12.75 mm	185.7 mm

General Information

Cap-Base	R7s
Rated Lifetime (Hours)	2,000 hour(s)

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

General Information

Order Code	Full Product Name	Switching	Nominal	Operating
		Cycle	lifetime	Position
923932145741	1000 W R7s cap Clear Halogen linear lamp	8,000 hour(s)	2,000	P4
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	-	UNIVERSAL

Light Technical

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Color index (CRI)	rendering (Nom)	Flux (rated)
923932145741	1000 W R7s cap Clear Halogen linear lamp	2900 K	100	21.5 lm/W	21,500 lm

Order Code	Full Product Name	Correlated Color		Luminous Efficacy	
		Temperature (Nom)	Color index (CRI)	rendering (Nom)	Flux (rated)
	Halogen linear lamp				

Plusline Large

Order Code	Name	Correlated Color				Luminous Color				Correlated Color				Luminous Color			
		Full Product Name	Temperature (Nom)	rendering index (CRI)	(rated) (Nom)	Luminous Flux	Full Product Name	Temperature (Nom)	rendering index (CRI)	(rated) (Nom)	Luminous Flux						
											Order Code	Name	Color	Efficacy			
923880345799	Plusline L 500W	-	-	-	8,900 lm	240-250V CL 1SL/4X50CT											

Operating and Electrical

Order Code	Full Product Name	Warm-up time to 60% light	Lamp Current (Nom)	Voltage (Nom)	Power Consumption	Starting Time (Nom)
923932145741	1000 W R7s cap Clear Halogen linear lamp	instant full light s	4.17 A	240 V	1,000.0 W	0.0 s
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	-	240-250 V	500 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
923932145741	1000 W R7s cap Clear Halogen linear lamp	Yes	923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape	Order Code	Full Product Name	Bulb Shape
923932145741	1000 W R7s cap Clear Halogen linear lamp	T11	923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	T37

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/	
		1000 h	1,000 kWh
923932145741	1000 W R7s cap Clear Halogen linear lamp	1,000 kWh	
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	

