



# Product Description

## Standard Candle B35 clear

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

### Benefits

- At their best in decorative glass chandeliers and wall brackets with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

### Features

- Slender, crystal-clear lamps designed for sparkling highlights
- Creates a classic sparkling atmosphere

### Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

# Standard Candle B35 clear

## Versions



LPPR1\_ICANESTD\_E14\_B35\_CL.JP  
G





LPPR ICANBSTD B22 B35 CL



LPPR\_ICANESTD\_E27\_B35\_CL-  
Product photo

## Dimensional drawing




Product	D	C (max)
230V 25W CANDLE BC CLEAR	35 mm	94.5 mm

Product	D	C (max)
Stan 40W E14 230V B35 CL U 1CT/6X50CT	35 mm	100 mm
Stan 60W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm

# Standard Candle B35 clear

## Dimensional drawing



Product	D	C (max)
Stan 40W E27 230V B35 CL 1CT/10X10F	35 mm	96.5 mm

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35

## General Information

Order Code	Full Product Name	Cap-Base
926000003017	Stan 60W E14 230V B35 CL 1CT/10X10F	E14
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	E14
921485544299	230V 25W CANDLE BC CLEAR	B22
921492044218	Stan 40W E27 230V B35 CL 1CT/10X10F	E27

## Light Technical

Order Code	Full Product Name	Luminous Flux
926000003017	Stan 60W E14 230V B35 CL 1CT/10X10F	670 lm
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	410 lm

Order Code	Full Product Name	Luminous Flux
921485544299	230V 25W CANDLE BC CLEAR	205 lm
921492044218	Stan 40W E27 230V B35 CL 1CT/10X10F	390 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
926000003017	Stan 60W E14 230V B35 CL 1CT/10X10F	60 W
926000205010	Stan 40W E14 230V B35 CL U 1CT/6X50CT	40 W

Order Code	Full Product Name	Power Consumption
921485544299	230V 25W CANDLE BC CLEAR	25 W
921492044218	Stan 40W E27 230V B35 CL 1CT/10X10F	40 W

## Standard Candle B35 clear

