



# Product Description

## Softone Standard T-shape

T-shaped gas-filled lamps with a modern appearance

### Benefits

- Enhances colours in the home and adds a new dimension to interior decoration
- Creates a pleasant, relaxed atmosphere with a high degree of visual comfort


### Features

- Gives a delicate, glare-free light in a subtle white or pastel colour
- Glare free and soft white or soft pastel lighting effect

### Application

- Home use in living and dining rooms, halls and studies
- Offices
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs, social areas and public accommodation
- Shops and boutiques
- Other similar areas


### Dimensional drawing



Product	D	C (max)
Soft 100W B22 230V T55 WH U 1CT/100	55 mm	93.5 mm
Soft 100W B22 240V T55 WH 1CT/5X20FT	55 mm	93.5 mm
Soft 40W B22 230V T55 WH U 1CT/100	55 mm	93.5 mm
Soft 60W B22 230V T55 WH U 1CT/100	55 mm	93.5 mm
Soft 60W B22 240V T55 WH 1CT/5X20FT	55 mm	93.5 mm
Soft 75W B22 240V T55 WH 1CT/5X20FT	55 mm	96.5 mm

# Softone Standard T-shape

## Dimensional drawing



Product	D	C (max)
Soft 60W E27 240V T55 WH 1CT/5X20FT	55 mm	95 mm
Soft 75W E27 240V T55 WH 1CT/5X20FT	55 mm	98 mm

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Soft White
Bulb Shape	T55

## General Information

Order Code	Full Product Name	Cap-Base
922801245537	Soft 60W B22 240V T55 WH 1CT/5X20FT	B22
922801345537	Soft 75W B22 240V T55 WH 1CT/5X20FT	B22
922801445537	Soft 100W B22 240V T55 WH 1CT/5X20FT	B22
926000205012	Soft 60W B22 230V T55 WH U 1CT/100	B22

Order Code	Full Product Name	Cap-Base
926000205013	Soft 40W B22 230V T55 WH U 1CT/100	B22
926000205014	Soft 100W B22 230V T55 WH U 1CT/100	B22
922800345537	Soft 60W E27 240V T55 WH 1CT/5X20FT	E27
922800445537	Soft 75W E27 240V T55 WH 1CT/5X20FT	E27

## Light Technical

Order Code	Full Product Name	Luminous Flux
922801245537	Soft 60W B22 240V T55 WH 1CT/5X20FT	630 lm
922801345537	Soft 75W B22 240V T55 WH 1CT/5X20FT	830 lm
922801445537	Soft 100W B22 240V T55 WH 1CT/5X20FT	1,200 lm
926000205012	Soft 60W B22 230V T55 WH U 1CT/100	630 lm

Order Code	Full Product Name	Luminous Flux
926000205013	Soft 40W B22 230V T55 WH U 1CT/100	370 lm
926000205014	Soft 100W B22 230V T55 WH U 1CT/100	1,200 lm
922800345537	Soft 60W E27 240V T55 WH 1CT/5X20FT	630 lm
922800445537	Soft 75W E27 240V T55 WH 1CT/5X20FT	830 lm

## Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
922801245537	Soft 60W B22 240V T55 WH 1CT/5X20FT	240 V	60 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
922801345537	Soft 75W B22 240V T55 WH 1CT/5X20FT	240 V	75 W

## Softone Standard T-shape

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
922801445537	Soft 100W B22 240V T55 WH 1CT/5X20FT	240 V	100 W
926000205012	Soft 60W B22 230V T55 WH U 1CT/100	230 V	60 W
926000205013	Soft 40W B22 230V T55 WH U 1CT/100	230 V	40 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
926000205014	Soft 100W B22 230V T55 WH U 1CT/100	230 V	100 W
922800345537	Soft 60W E27 240V T55 WH 1CT/5X20FT	240 V	60 W
922800445537	Soft 75W E27 240V T55 WH 1CT/5X20FT	240 V	75 W

