

PHILIPS

Lighting



Product Description

Appliance Oven Tubular

Tubular vacuum lamps with clear glass (T-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

Versions



LPPR_ITUBAPE_E14_T22_CL-
Product photo



LPPR_ITUBAPE_E14_T25_CL-
Product photo

Appliance Oven Tubular

Versions




15 W E14 cap Incandescent
appliance bulb - RFT




15 W E14 cap Oven Incandescent
appliance bulb - RFT


Dimensional drawing



Product	D (max)	C (max)
15 W E14 cap Oven Incandescent appliance bulb	22 mm	49 mm
15 W E14 cap Incandescent appliance bulb	22 mm	49 mm
App 15.4W E14 230-240V T22 CL OV 1CT	22 mm	49 mm



Product	D (max)	C (max)
App 26.0W E14 230-240V T25 CL OV 1CT	25 mm	57 mm
App 26.0W E14 230-240V T25CL OV 1CT/20F	25 mm	57 mm



Product	D (max)	C (max)
10 W E14 cap Clear Incandescent tubular bulb	26 mm	59 mm

Appliance Oven Tubular

General Information	
Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Switching Cycle	4,000
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230-240 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Light Technical

Order Code	Full Product Name	Luminous Flux
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	90 lm
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	172 lm
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	172 lm
924198344441	10 W E14 cap Clear Incandescent tubular bulb	34 lm
924196244451	15 W E14 cap Oven Incandescent appliance bulb	90 lm
924196244452	15 W E14 cap Oven Incandescent appliance bulb	90 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	0.06 A	15.0 W
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	0.11 A	25.0 W
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	0.11 A	25.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
924198344441	10 W E14 cap Clear Incandescent tubular bulb	0.04 A	10.0 W
924196244451	15 W E14 cap Oven Incandescent appliance bulb	0.06 A	15.0 W
924196244452	15 W E14 cap Oven Incandescent appliance bulb	0.06 A	15.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	T22
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	T25
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	T25

Order Code	Full Product Name	Bulb Shape
924198344441	10 W E14 cap Clear Incandescent tubular bulb	T25
924196244451	15 W E14 cap Oven Incandescent appliance bulb	T22
924196244452	15 W E14 cap Oven Incandescent appliance bulb	T22

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	15 kWh
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	25 kWh
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	25 kWh
924198344441	10 W E14 cap Clear Incandescent tubular bulb	10 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
924196244451	15 W E14 cap Oven Incandescent appliance bulb	15 kWh
924196244452	15 W E14 cap Oven Incandescent appliance bulb	15 kWh

Appliance Oven Tubular



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2025, December 13 - data subject to change