

PHILIPS

Lighting



Product Description

Appliance Oven Tubular

Tubular vacuum lamps with clear glass (T-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

Versions




LPPR_ITUBAPE_E14_T22_CL-Product photo




LPPR_ITUBAPE_E14_T25_CL-Product photo

Appliance Oven Tubular

Dimensional drawing



Product	D (max)	C (max)
App 15.4W E14 230-240V T22 CL OV 1CT	22 mm	49 mm



Product	D (max)	C (max)
App 26.0W E14 230-240V T25 CL OV 1CT	25 mm	57 mm

General Information	
Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Switching Cycle	4,000
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230-240 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Light Technical

Order Code	Full Product Name	Luminous Flux
03659950	Appliance 15.4W E14 230-240V T22 CL OV 1CT	90 lm
03871550	Appliance 26.0W E14 230-240V T25 CL OV 1CT	172 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
03659950	Appliance 15.4W E14 230-240V T22 CL OV 1CT	0.06 A	15.0 W

Appliance Oven Tubular

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
03871550	Appliance 26.0W E14 230-240V T25 CL OV 1CT	0.11 A	25.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
03659950	Appliance 15.4W E14 230-240V T22 CL OV 1CT	T22

Order Code	Full Product Name	Bulb Shape
03871550	Appliance 26.0W E14 230-240V T25 CL OV 1CT	T25

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/	
		1000 h	1CT
03659950	Appliance 15.4W E14 230-240V T22 CL OV	15 kWh	

Order Code	Full Product Name	Energy Consumption kWh/	
		1000 h	1CT
03871550	Appliance 26.0W E14 230-240V T25 CL OV	25 kWh	

