



RCS750 3-circuit square track system – flexible and multifunctional

3-circuit Square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminum track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available

Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily.
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors.
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided.

Features

- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

3-circuit Square RCS750

Application

- Retail
- Indoor architectural lighting

Versions







RBS750 recessed track, alu




RCS750 track, black

Dimensional drawing



3-circuit Square RCS750

Dimensional drawing



Operating and Electrical

Protection class IEC	Safety class I
Protection class IEC	Safety class I

Mechanical and Housing

Ingress protection code	IP30
Ingress protection code	IP30

Approval and Application

CE mark	Yes
CE mark	Yes
Glow-wire test	Temperature 850 °C, duration 5 s
Glow-wire test	Temperature 850 °C, duration 5 s

Mechanical and Housing

Order Code	Full Product Name	Accessory color
910930009118	RBS750 3C L2000 WH (XTSF4200-3)	White
910930009318	RBS750 3C L3000 WH (XTSF4300-3)	White
910500188815	RCS750 3C L1000 WH (XTS4100-3)	White
910500188915	RCS750 3C L2000 WH (XTS4200-3)	White
910500189015	RCS750 3C L3000 WH (XTS4300-3)	White
910500189115	RCS750 3C L4000 WH (XTS4400-3)	White
910500188415	RCS750 3C L1000 ALU (XTS4100-1)	Aluminum
910500188515	RCS750 3C L2000 ALU (XTS4200-1)	Aluminum
910500188615	RCS750 3C L3000 ALU (XTS4300-1)	Aluminum
910500188715	RCS750 3C L4000 ALU (XTS4400-1)	Aluminum
910930009018	RBS750 3C L2000 ALU (XTSF4200-1)	Aluminum
910930009218	RBS750 3C L3000 ALU (XTSF4300-1)	Aluminum
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Black
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Black
910930013418	RCS750 3C L3000 BK (XTS4300-2)	Black
910930013518	RCS750 3C L4000 BK (XTS4400-2)	Black

