



3-circuit square RCS750

3-circuit Square RCS750

The Philips 3-circuit square track system consists of an anodised aluminium profile in natural anodised or painted white in lengths of 1, 2, 3 and 4 m. It contains four electrical conductors allowing easy creation of any required configuration: horizontal or vertical, recessed or surface-mounted, on the wall, on free-standing panels or floating. All luminaires have their separate power supply and can be switched selectively by phase or by circuit. Because the luminaires are easy to move, by simply clicking them in place in the adaptor on the track, changes in the lighting and presentation can be made very simply. All 230V projectors in the Philips range can be installed on this track system. All the associated accessories are common to both the surface-mounted and recessed models and guarantee a good electrical and mechanical connection.

Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided

Features

- -

Application

- Retail
- Indoor architectural lighting







3-circuit Square RCS750

Versions



RBS750 recessed track, white

Dimensional drawing



3-circuit Square RCS750

Operating and Electrical			Mechanical and Housing		
Order Code	Full Product Name	Accessory color	Order Code	Full Product Name	Accessory color
14980600	RBS750 3C L2000 WH (XTSF4200-3)	White	14982000	RBS750 3C L3000 WH (XTSF4300-3)	White
38110700	RCS750 3C L1000 WH (XTS4100-3)	White	38111400	RCS750 3C L2000 WH (XTS4200-3)	White
38112100	RCS750 3C L3000 WH (XTS4300-3)	White	38113800	RCS750 3C L4000 WH (XTS4400-3)	White
38106000	RCS750 3C L1000 ALU (XTS4100-1)	Aluminum	38107700	RCS750 3C L2000 ALU (XTS4200-1)	Aluminum
38108400	RCS750 3C L3000 ALU (XTS4300-1)	Aluminum	38109100	RCS750 3C L4000 ALU (XTS4400-1)	Aluminum
14979000	RBS750 3C L2000 ALU (XTSF4200-1)	Aluminum	14981300	RBS750 3C L3000 ALU (XTSF4300-1)	Aluminum
79851600	RCS750 3C L1000 BK (XTS4100-2)	Black	79852300	RCS750 3C L2000 BK (XTS4200-2)	Black
79853000	RCS750 3C L3000 BK (XTS4300-2)	Black	79854700	RCS750 3C L4000 BK (XTS4400-2)	Black

