



Small but comprehensive

GreenUp hospitality spot

GreenUp hospitality spot is a small cut out spot but with comprehensive offers. It offers flexible wattages for different indoor applications, such as retail and hospitality. This family delivers high CRI90 and 3 different beam angles to perfectly fit the light requirement of indoor retail and hospitality applications.

Benefits

- High color rendering index helps better visual comfort in hospitality retail applications
- 3 different beams facilitate the lighting designers for wide lighting applications
- Tilttable angle for easier installation options
- Multiple lumen output and wattages to provide more choices for the designers

Features

- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- 30 degree tilt angle
- 5/7/9/12w options are available

Application

- Retail and Hospitality

GreenUp hospitality spot

Versions





GreenUp hospitality accent



GreenUp Hospitality RS318

Dimensional drawing



Product details

GreenUp hospitality accent



GreenUp hospitality spot

Light Technical

Color rendering index (CRI) >90

Operating and Electrical

Protection class IEC Safety class II

Input Voltage 220 to 240 V

Line Frequency 0/50/60 Hz

Mechanical and Housing

Optical cover type -

Housing Color Aluminum and gray

Mech. impact protection code IK03

Ingress protection code IP20

Approval and Application

Ambient temperature range +20 to +40 °C

CE mark No

Flammability mark -

Initial Performance (IEC Compliant)

Initial chromaticity -

Luminous flux tolerance +/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401537402	RS318B P5 930 PSU-E WB S	3000 K	101 lm/W	80 lm
911401538202	RS318B P9 927 PSU-E MB S	2700 K	96 lm/W	75 lm
911401538502	RS318B P9 930 PSU-E MB S	3000 K	101 lm/W	75 lm
911401593422	RS318B P9 930 PSR-E MB S	3000 K	101 lm/W	70 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401537402	RS318B P5 930 PSU-E WB S	5 W
911401538202	RS318B P9 927 PSU-E MB S	9 W

Order Code	Full Product Name	Power Consumption
911401538502	RS318B P9 930 PSU-E MB S	9 W
911401593422	RS318B P9 930 PSR-E MB S	9 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401537402	RS318B P5 930 PSU-E WB S	No
911401538202	RS318B P9 927 PSU-E MB S	No

Order Code	Full Product Name	Dimmable
911401538502	RS318B P9 930 PSU-E MB S	No
911401593422	RS318B P9 930 PSR-E MB S	Yes

