



# GreenSpace Flex Luna – Bringing moonlight inside.

## GreenSpace Flex Luna

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Benefits

- Sustainable, more light with less energy consumption, up to 120lm/W.
- Silent brilliance with superior visual comfort.
- Deliver light that speaks luxury, supported by superior color consistency and beam control.
- Comprehensive family offering, maintain effortlessly with ceiling proof design.

### Features

- Leading lm/W, up to 120lm/W on luminaire level.
- 40° cut off angle and UGR19 for major variants.
- Leading color performance, with CRI92, R9>50.
- Super color consistency, SDCM 3 on luminaire level and SDCM 2 on COB level.
- Modular design concept, supporting strong customization and flexibility on family level, covering cut out(D35 to D100), optics (12° to 55°), controls (PSU, PSD, 1-10V, WIA) and customized reflector and front ring color options.

### Application

- Hospitality
- Retail
- Offices
- General indoor space


# GreenSpace Flex Luna

## Versions



GreenSpace Flex Luna

## Dimensional drawing



## Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz

## Mechanical and Housing

Optical cover type	Lens
Housing Color	Black
Mech. impact protection code	IK03
Ingress protection code	IP20

## Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

## Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401520146	RS378B P7 PSD-TNW NB M43 PRO	Tunable White	90	71 lm/W	530 lm
911401597345	RS378B P6 930 PSU-E NB M43 PRO	3000 K	92	90 lm/W	530 lm
911401597745	RS378B P6 940 PSU-E MB M43 PRO	4000 K	92	99 lm/W	585 lm
911401598245	RS378B P8 930 PSU-E NB M43 PRO	3000 K	92	83 lm/W	665 lm
911401598645	RS378B P8 940 PSU-E MB M43 PRO	4000 K	92	91 lm/W	725 lm
911401599445	RS378B P7 930 PSD-E NB M43 PRO	3000 K	92	79 lm/W	585 lm
911401599845	RS378B P7 940 PSD-E MB M43 PRO	4000 K	92	87 lm/W	645 lm
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	3000 K	92	92 lm/W	660 lm
911401501446	RS378B P7 940 PSU-E MB M55 PRO	4000 K	92	118 lm/W	835 lm
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	3000 K	92	88 lm/W	705 lm
911401502246	RS378B P9 930 PSU-E NB M55 PRO	3000 K	92	106 lm/W	950 lm
911401502646	RS378B P9 940 PSU-E MB M55 PRO	4000 K	92	111 lm/W	1,000 lm
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	3000 K	92	84 lm/W	630 lm
911401505646	RS378B P7 940 PSD-E MB M55 PRO	4000 K	92	107 lm/W	780 lm
911401506146	RS378B P9 930 PSD-E NB M55 PRO	3000 K	92	100 lm/W	950 lm
911401506546	RS378B P9 940 PSD-E MB M55 PRO	4000 K	92	105 lm/W	1,000 lm
911401506746	RS378B P9 930 PSD-E WB M55 PRO	3000 K	92	105 lm/W	1,000 lm
911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	2700 K	92	74 lm/W	230 lm
911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	3000 K	92	79 lm/W	245 lm
911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	4000 K	92	84 lm/W	260 lm
911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	3000 K	92	79 lm/W	370 lm
911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	3000 K	92	63 lm/W	335 lm
911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	3000 K	92	62 lm/W	330 lm
911401510246	RS378B P12 930 PSU-E NB M70 PRO	3000 K	92	132 lm/W	1,585 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401510646	RS378B P12 940 PSU-E MB M70 PRO	4000 K	92	138 lm/W	1,650 lm
911401511146	RS378B P17 930 PSU-E NB M70 PRO	3000 K	92	128 lm/W	2,245 lm
911401512046	RS378B P19 930 PSU-E NB M70 PRO	3000 K	92	123 lm/W	2,390 lm
911401512146	RS378B P19 940 PSU-E NB M70 PRO	4000 K	92	129 lm/W	2,510 lm
911401513846	RS378B P12 930 PSD-E NB M70 PRO	3000 K	92	124 lm/W	1,585 lm
911401514246	RS378B P12 940 PSD-E MB M70 PRO	4000 K	92	129 lm/W	1,650 lm
911401514746	RS378B P18 930 PSD-E NB M70 PRO	3000 K	92	121 lm/W	2,245 lm
911401515046	RS378B P18 930 PSD-E MB M70 PRO	3000 K	92	124 lm/W	2,295 lm
911401515146	RS378B P18 940 PSD-E MB M70 PRO	4000 K	92	128 lm/W	2,365 lm
911401515546	RS378B P20 927 PSD-E NB M70 PRO	2700 K	92	111 lm/W	2,270 lm
911401515646	RS378B P20 930 PSD-E NB M70 PRO	3000 K	92	117 lm/W	2,390 lm
911401515746	RS378B P20 940 PSD-E NB M70 PRO	4000 K	92	122 lm/W	2,510 lm
911401517646	RS378X P19 930 WIA WB M70 PRO	3000 K	92	129 lm/W	2,585 lm
911401512946	RS378B P27 930 PSU-E NB M70 PRO	3000 K	92	112 lm/W	3,090 lm
911401513046	RS378B P27 940 PSU-E NB M70 PRO	4000 K	92	116 lm/W	3,185 lm
911401516546	RS378B P27 930 PSD-E NB M70 PRO	3000 K	92	108 lm/W	2,925 lm
911401516946	RS378B P27 940 PSD-E MB M70 PRO	4000 K	92	115 lm/W	3,105 lm
911401503146	RS378B P12 930 PSU-E NB M55 PRO	3000 K	92	106 lm/W	1,330 lm
911401503546	RS378B P12 940 PSU-E MB M55 PRO	4000 K	92	116 lm/W	1,460 lm
911401503946	RS378B P14 927 PSU-E NB M55 PRO	2700 K	92	96 lm/W	1,390 lm
911401504046	RS378B P14 930 PSU-E NB M55 PRO	3000 K	92	102 lm/W	1,480 lm
911401504446	RS378B P14 940 PSU-E MB M55 PRO	4000 K	92	113 lm/W	1,635 lm
911401507046	RS378B P13 930 PSD-E NB M55 PRO	3000 K	92	99 lm/W	1,330 lm
911401507346	RS378B P13 930 PSD-E MB M55 PRO	3000 K	92	103 lm/W	1,390 lm
911401507446	RS378B P13 940 PSD-E MB M55 PRO	4000 K	92	108 lm/W	1,460 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401507946	RS378B P15 930 PSD-E NB M55 PRO	3000 K	92	95 lm/W	1,480 lm
911401508346	RS378B P15 940 PSD-E MB M55 PRO	4000 K	92	105 lm/W	1,635 lm
911401508546	RS378B P15 930 PSD-E WB M55 PRO	3000 K	92	103 lm/W	1,600 lm
911401509246	RS378X P14 930 WIA WB M55 PRO	3000 K	92	107 lm/W	1,600 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401520146	RS378B P7 PSD-TNW NB M43 PRO	7.5 W	911401512146	RS378B P19 940 PSU-E NB M70 PRO	19.5 W
911401597345	RS378B P6 930 PSU-E NB M43 PRO	5.9 W	911401513846	RS378B P12 930 PSD-E NB M70 PRO	12.8 W
911401597745	RS378B P6 940 PSU-E MB M43 PRO	5.9 W	911401514246	RS378B P12 940 PSD-E MB M70 PRO	12.8 W
911401598245	RS378B P8 930 PSU-E NB M43 PRO	8 W	911401514746	RS378B P18 930 PSD-E NB M70 PRO	18.5 W
911401598645	RS378B P8 940 PSU-E MB M43 PRO	8 W	911401515046	RS378B P18 930 PSD-E MB M70 PRO	18.5 W
911401599445	RS378B P7 930 PSD-E NB M43 PRO	7.4 W	911401515146	RS378B P18 940 PSD-E MB M70 PRO	18.5 W
911401599845	RS378B P7 940 PSD-E MB M43 PRO	7.4 W	911401515546	RS378B P20 927 PSD-E NB M70 PRO	20.5 W
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	7.2 W	911401515646	RS378B P20 930 PSD-E NB M70 PRO	20.5 W
911401501446	RS378B P7 940 PSU-E MB M55 PRO	7.1 W	911401515746	RS378B P20 940 PSD-E NB M70 PRO	20.5 W
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	8 W	911401517646	RS378X P19 930 WIA WB M70 PRO	20 W
911401502246	RS378B P9 930 PSU-E NB M55 PRO	9 W	911401512946	RS378B P27 930 PSU-E NB M70 PRO	27.5 W
911401502646	RS378B P9 940 PSU-E MB M55 PRO	9 W	911401513046	RS378B P27 940 PSU-E NB M70 PRO	27.5 W
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	7.5 W	911401516546	RS378B P27 930 PSD-E NB M70 PRO	27 W
911401505646	RS378B P7 940 PSD-E MB M55 PRO	7.3 W	911401516946	RS378B P27 940 PSD-E MB M70 PRO	27 W
911401506146	RS378B P9 930 PSD-E NB M55 PRO	9.5 W	911401503146	RS378B P12 930 PSU-E NB M55 PRO	12.6 W
911401506546	RS378B P9 940 PSD-E MB M55 PRO	9.5 W	911401503546	RS378B P12 940 PSU-E MB M55 PRO	12.6 W
911401506746	RS378B P9 930 PSD-E WB M55 PRO	9.5 W	911401503946	RS378B P14 927 PSU-E NB M55 PRO	14.5 W
911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	3.1 W	911401504046	RS378B P14 930 PSU-E NB M55 PRO	14.5 W
911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	3.1 W	911401504446	RS378B P14 940 PSU-E MB M55 PRO	14.5 W
911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	3.1 W	911401507046	RS378B P13 930 PSD-E NB M55 PRO	13.5 W
911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	4.7 W	911401507346	RS378B P13 930 PSD-E MB M55 PRO	13.5 W
911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	5.3 W	911401507446	RS378B P13 940 PSD-E MB M55 PRO	13.5 W
911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	5.3 W	911401507946	RS378B P15 930 PSD-E NB M55 PRO	15.5 W
911401510246	RS378B P12 930 PSU-E NB M70 PRO	12 W	911401508346	RS378B P15 940 PSD-E MB M55 PRO	15.5 W
911401510646	RS378B P12 940 PSU-E MB M70 PRO	12 W	911401508546	RS378B P15 930 PSD-E WB M55 PRO	15.5 W
911401511146	RS378B P17 930 PSU-E NB M70 PRO	17.5 W	911401509246	RS378X P14 930 WIA WB M55 PRO	15 W
911401512046	RS378B P19 930 PSU-E NB M70 PRO	19.5 W			

## Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401520146	RS378B P7 PSD-TNW NB M43 PRO	DALI	911401599845	RS378B P7 940 PSD-E MB M43 PRO	DALI
911401597345	RS378B P6 930 PSU-E NB M43 PRO	-	911401500746	RS378B P7 930 PSU-E SNB M55 PRO	-
911401597745	RS378B P6 940 PSU-E MB M43 PRO	-	911401501446	RS378B P7 940 PSU-E MB M55 PRO	-
911401598245	RS378B P8 930 PSU-E NB M43 PRO	-	911401501946	RS378B P8 930 PSU-E SNB M55 PRO	-
911401598645	RS378B P8 940 PSU-E MB M43 PRO	-	911401502246	RS378B P9 930 PSU-E NB M55 PRO	-
911401599445	RS378B P7 930 PSD-E NB M43 PRO	DALI	911401502646	RS378B P9 940 PSU-E MB M55 PRO	-

## GreenSpace Flex Luna

Order Code	Full Product Name	Dimmable
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	DALI
911401505646	RS378B P7 940 PSD-E MB M55 PRO	DALI
911401506146	RS378B P9 930 PSD-E NB M55 PRO	DALI
911401506546	RS378B P9 940 PSD-E MB M55 PRO	DALI
911401506746	RS378B P9 930 PSD-E WB M55 PRO	DALI
911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	-
911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	-
911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	-
911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	-
911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	DALI
911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	DALI
911401510246	RS378B P12 930 PSU-E NB M70 PRO	-
911401510646	RS378B P12 940 PSU-E MB M70 PRO	-
911401511146	RS378B P17 930 PSU-E NB M70 PRO	-
911401512046	RS378B P19 930 PSU-E NB M70 PRO	-
911401512146	RS378B P19 940 PSU-E NB M70 PRO	-
911401513846	RS378B P12 930 PSD-E NB M70 PRO	DALI
911401514246	RS378B P12 940 PSD-E MB M70 PRO	DALI
911401514746	RS378B P18 930 PSD-E NB M70 PRO	DALI
911401515046	RS378B P18 930 PSD-E MB M70 PRO	DALI
911401515146	RS378B P18 940 PSD-E MB M70 PRO	DALI

Order Code	Full Product Name	Dimmable
911401515546	RS378B P20 927 PSD-E NB M70 PRO	DALI
911401515646	RS378B P20 930 PSD-E NB M70 PRO	DALI
911401515746	RS378B P20 940 PSD-E NB M70 PRO	DALI
911401517646	RS378X P19 930 WIA WB M70 PRO	Wireless Dim
911401512946	RS378B P27 930 PSU-E NB M70 PRO	-
911401513046	RS378B P27 940 PSU-E NB M70 PRO	-
911401516546	RS378B P27 930 PSD-E NB M70 PRO	DALI
911401516946	RS378B P27 940 PSD-E MB M70 PRO	DALI
911401503146	RS378B P12 930 PSU-E NB M55 PRO	-
911401503546	RS378B P12 940 PSU-E MB M55 PRO	-
911401503946	RS378B P14 927 PSU-E NB M55 PRO	-
911401504046	RS378B P14 930 PSU-E NB M55 PRO	-
911401504446	RS378B P14 940 PSU-E MB M55 PRO	-
911401507046	RS378B P13 930 PSD-E NB M55 PRO	DALI
911401507346	RS378B P13 930 PSD-E MB M55 PRO	DALI
911401507446	RS378B P13 940 PSD-E MB M55 PRO	DALI
911401507946	RS378B P15 930 PSD-E NB M55 PRO	DALI
911401508346	RS378B P15 940 PSD-E MB M55 PRO	DALI
911401508546	RS378B P15 930 PSD-E WB M55 PRO	DALI
911401509246	RS378X P14 930 WIA WB M55 PRO	Wireless Dim

### Approval and Application

Order Code	Full Product Name	CE mark
911401520146	RS378B P7 PSD-TNW NB M43 PRO	No
911401597345	RS378B P6 930 PSU-E NB M43 PRO	Yes
911401597745	RS378B P6 940 PSU-E MB M43 PRO	Yes
911401598245	RS378B P8 930 PSU-E NB M43 PRO	Yes
911401598645	RS378B P8 940 PSU-E MB M43 PRO	Yes
911401599445	RS378B P7 930 PSD-E NB M43 PRO	Yes
911401599845	RS378B P7 940 PSD-E MB M43 PRO	Yes
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	Yes
911401501446	RS378B P7 940 PSU-E MB M55 PRO	Yes
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	Yes
911401502246	RS378B P9 930 PSU-E NB M55 PRO	Yes
911401502646	RS378B P9 940 PSU-E MB M55 PRO	Yes
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	Yes
911401505646	RS378B P7 940 PSD-E MB M55 PRO	Yes
911401506146	RS378B P9 930 PSD-E NB M55 PRO	Yes
911401506546	RS378B P9 940 PSD-E MB M55 PRO	Yes
911401506746	RS378B P9 930 PSD-E WB M55 PRO	Yes
911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	Yes
911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	Yes
911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	Yes
911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	Yes
911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	Yes
911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	Yes
911401510246	RS378B P12 930 PSU-E NB M70 PRO	Yes
911401510646	RS378B P12 940 PSU-E MB M70 PRO	Yes
911401511146	RS378B P17 930 PSU-E NB M70 PRO	Yes
911401512046	RS378B P19 930 PSU-E NB M70 PRO	Yes

Order Code	Full Product Name	CE mark
911401512146	RS378B P19 940 PSU-E NB M70 PRO	Yes
911401513846	RS378B P12 930 PSD-E NB M70 PRO	Yes
911401514246	RS378B P12 940 PSD-E MB M70 PRO	Yes
911401514746	RS378B P18 930 PSD-E NB M70 PRO	Yes
911401515046	RS378B P18 930 PSD-E MB M70 PRO	Yes
911401515146	RS378B P18 940 PSD-E MB M70 PRO	Yes
911401515546	RS378B P20 927 PSD-E NB M70 PRO	Yes
911401515646	RS378B P20 930 PSD-E NB M70 PRO	Yes
911401515746	RS378B P20 940 PSD-E NB M70 PRO	Yes
911401517646	RS378X P19 930 WIA WB M70 PRO	Yes
911401512946	RS378B P27 930 PSU-E NB M70 PRO	Yes
911401513046	RS378B P27 940 PSU-E NB M70 PRO	Yes
911401516546	RS378B P27 930 PSD-E NB M70 PRO	Yes
911401516946	RS378B P27 940 PSD-E MB M70 PRO	Yes
911401503146	RS378B P12 930 PSU-E NB M55 PRO	Yes
911401503546	RS378B P12 940 PSU-E MB M55 PRO	Yes
911401503946	RS378B P14 927 PSU-E NB M55 PRO	Yes
911401504046	RS378B P14 930 PSU-E NB M55 PRO	Yes
911401504446	RS378B P14 940 PSU-E MB M55 PRO	Yes
911401507046	RS378B P13 930 PSD-E NB M55 PRO	Yes
911401507346	RS378B P13 930 PSD-E MB M55 PRO	Yes
911401507446	RS378B P13 940 PSD-E MB M55 PRO	Yes
911401507946	RS378B P15 930 PSD-E NB M55 PRO	Yes
911401508346	RS378B P15 940 PSD-E MB M55 PRO	Yes
911401508546	RS378B P15 930 PSD-E WB M55 PRO	Yes
911401509246	RS378X P14 930 WIA WB M55 PRO	Yes

