



# Powerful discreet spots with an accent on sustainability

## LuxSpace Accent Performance Adjustable

With LuxSpace Accent Performance Adjustable, retailers and building operators can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a refined and neutral product design. Powerful and discreet, LuxSpace Accent combines a high luminous flux in a compact form factor. Design-in and installation are easy due to its small built-in dimensions. Maintenance and upgrades of the optics is fast and requires no tools. Furthermore, LuxSpace Accent Performance Adjustable spots are certified as circular lighting and offer multiple system integration and dimming options, including wired as well as wireless. LuxSpace Accent Performance Adjustable allows spot head rotation and two-directional tilting for maximum aiming flexibility. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

### Benefits

- More sparkle and enhanced shopper eye comfort with PerfectAccent optics
- Best-in-class efficacy to reduce carbon footprint and save on energy use
- Certified as circular lighting with PerfectAccent high-efficacy reflectors
- Easy maintenance and upgrades with tool-less access to driver and optics
- The clean and refined product design helps the spots blend in with ceilings

# LuxSpace Accent Performance Adjustable

## Features

- RS781B offers high maximum flux (6000 lm) in a very compact housing with limited built-in dimensions
- Available with PerfectAccent high-efficacy reflectors
- Optional front glass (advised in dusty environments)
- Two-directional tilt for great light control
- Available with fresh food LED lighting recipes and LED flavors
- Wired (DALI) and wireless connectivity options available

## Application

- Convenience stores
- Supermarkets & hypermarkets
- Offices and hospitality areas

## Warnings and Safety



- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

## Versions



RS781B LuxSpace Accent  
Performance Adjustable White

## Dimensional drawing



# LuxSpace Accent Performance Adjustable

## Product details

LuxSpace Accent Adjustable luminaires offer 2-way tilting for easy aiming in any installation



Step5 (optional): Add or remove the front glass



Step4: Replace the reflector



Step1: Press the button to unlock the front face



Step2: Remove the optical assembly from the luminaire



RS781B LuxSpace Accent Performance Adjustable Back View



Step3: Pull the clip of the frontface to release the reflector




# LuxSpace Accent Performance Adjustable

## Product details



PerfectAccent reflector and front glass maintenance and upgrading is easy with an integrated button

## Polar Wide Diagrams



Polar Normal (separate) - RS780BI -  
910505101624

