



Aesthetic, Comprehensive and Reliable

GreenUp Track

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Benefits

- Aesthetic product design with compact and integrated concept.
- Comprehensive offerings to meet various application requirements.
- Outstanding color rendering performance and visual comfort design


Features

- Multiple options of lumen output, wattage and optics.
- Full control availability including on/off, 1-10v, triac and DALI.
- CRI 90, R9 \geq 50
- UGR 19, cut off angle 50°

Application

- Retail
- Hospitality
- Fashion

Dimensional drawing



Light Technical

Color rendering index (CRI) >90

Operating and Electrical

Input Voltage 220-240 V

Line Frequency 50 or 60 Hz

Mechanical and Housing

Optical cover type Lens

Mech. impact protection code IK03

Ingress protection code IP20

Approval and Application

Ambient temperature range -20 to +40 °C

CE mark No

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401530522	ST306T P20 940 PSU WB WH BR	4000 K	90 lm/W	1,800 lm
911401542222	ST306T P10 940 PSD WB WH SR	4000 K	90 lm/W	900 lm
911401545522	ST306T P20 930 PSD WB WH SR	3000 K	85 lm/W	1,700 lm
911401556422	ST306T P10 940 PSD NB BK BR	4000 K	90 lm/W	900 lm
911401559022	ST306T P20 930 PSU WB BK BR	3000 K	85 lm/W	1,700 lm
911401559322	ST306T P20 940 PSU WB BK BR	4000 K	90 lm/W	1,800 lm
911401566222	ST306T P40 930 PSU WB BK BR	3000 K	93 lm/W	3,720 lm
911401569822	ST306T P10 930 PSU WB BK SR	3000 K	85 lm/W	850 lm
911401580622	ST306T P40 930 PSU WB BK SR	3000 K	93 lm/W	3,720 lm
911401580922	ST306T P40 940 PSU WB BK SR	4000 K	95 lm/W	3,800 lm

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401530522	ST306T P20 940 PSU WB WH BR	Safety class II	20 W
911401542222	ST306T P10 940 PSD WB WH SR	Safety class I	10 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401545522	ST306T P20 930 PSD WB WH SR	Safety class I	20 W
911401556422	ST306T P10 940 PSD NB BK BR	Safety class I	10 W

Order Code	Full Product Name	Protection class IEC	Power
			Consumption
911401559022	ST306T P20 930 PSU WB BK BR	Safety class II	20 W
911401559322	ST306T P20 940 PSU WB BK BR	Safety class II	20 W
911401566222	ST306T P40 930 PSU WB BK BR	Safety class II	40 W

Order Code	Full Product Name	Protection class IEC	Power
			Consumption
911401569822	ST306T P10 930 PSU WB BK SR	Safety class II	10 W
911401580622	ST306T P40 930 PSU WB BK SR	Safety class II	40 W
911401580922	ST306T P40 940 PSU WB BK SR	Safety class II	40 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401530522	ST306T P20 940 PSU WB WH BR	No
911401542222	ST306T P10 940 PSD WB WH SR	Yes
911401545522	ST306T P20 930 PSD WB WH SR	Yes
911401556422	ST306T P10 940 PSD NB BK BR	Yes
911401559022	ST306T P20 930 PSU WB BK BR	No

Order Code	Full Product Name	Dimmable
911401559322	ST306T P20 940 PSU WB BK BR	No
911401566222	ST306T P40 930 PSU WB BK BR	No
911401569822	ST306T P10 930 PSU WB BK SR	No
911401580622	ST306T P40 930 PSU WB BK SR	No
911401580922	ST306T P40 940 PSU WB BK SR	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401530522	ST306T P20 940 PSU WB WH BR	White
911401542222	ST306T P10 940 PSD WB WH SR	White
911401545522	ST306T P20 930 PSD WB WH SR	White
911401556422	ST306T P10 940 PSD NB BK BR	Black
911401559022	ST306T P20 930 PSU WB BK BR	Black

Order Code	Full Product Name	Housing Color
911401559322	ST306T P20 940 PSU WB BK BR	Black
911401566222	ST306T P40 930 PSU WB BK BR	Black
911401569822	ST306T P10 930 PSU WB BK SR	Black
911401580622	ST306T P40 930 PSU WB BK SR	Black
911401580922	ST306T P40 940 PSU WB BK SR	Black

