



# For fresh looking food

## MASTER TL-D Food

The TL-D Food lamp makes the appearance of meat and bakery products more fresh and tasty. It can be applied for food illumination in butcher shops, bakeries, supermarkets etc.

### Benefits

- Makes the appearance of meat products and poultry more tasty

### Features

- Spectral distribution optimal tuned to emphasize deep red colors such as those of meat and poultry


### Application

- Food illumination (butcher shops, bakeries, supermarkets etc.)

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Food 18W/79 SLV/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
MASTER TL-D Food 30W/79 SLV/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
MASTER TL-D Food 36W/79 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
MASTER TL-D Food 58W/79 SLV/25	28 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

# MASTER TL-D Food

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Food
Correlated Color Temperature (Nom)	3800 K
Color rendering index (CRI)	74
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

## Light Technical

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
928025402043	MASTER TL-D Food 30W/79 SLV/25	43 lm/W	1,300 lm
928048002043	MASTER TL-D Food 18W/79 SLV/25	41 lm/W	740 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
928048502043	MASTER TL-D Food 36W/79 SLV/25	49 lm/W	1,750 lm
928049002043	MASTER TL-D Food 58W/79 SLV/25	48 lm/W	2,800 lm

## Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928025402043	MASTER TL-D Food 30W/79 SLV/25	0.360 A	98 V	30.0 W
928048002043	MASTER TL-D Food 18W/79 SLV/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048502043	MASTER TL-D Food 36W/79 SLV/25	0.440 A	103 V	36.0 W
928049002043	MASTER TL-D Food 58W/79 SLV/25	0.670 A	111 V	58.5 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000
		h
928025402043	MASTER TL-D Food 30W/79 SLV/25	37 kWh
928048002043	MASTER TL-D Food 18W/79 SLV/25	23 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000
		h
928048502043	MASTER TL-D Food 36W/79 SLV/25	43 kWh
928049002043	MASTER TL-D Food 58W/79 SLV/25	69 kWh

## MASTER TL-D Food

