



A small and sustainable wallmount in a sleek, subtle design

GreenSpace Evo Mini Wallmount

The GreenSpace Evo Mini Wallmount is a sustainable wall-mounted fixture that comes with a sleek and subtle design. This makes the wall-mount an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini wall-mount a sustainable choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customisation of colours and textures is possible via Philips MyCreation

Benefits

- The sleek and subtle design fits perfectly in any installation
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Mini Wallmount

Features

- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Fashion
- Hospitality
- Residential

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth

Versions




WL321W WL322W GreenSpace Evo
Mini Wallmount Black



WL321W WL322W GreenSpace Evo
Mini Wallmount White

Dimensional drawing



GreenSpace Evo Mini Wallmount

Product details



WL322W Up- and downward light effect



WL321W Downward light effect



WL322W Up- and downward light effect



WL321W Downward light effect



WL321W Downward light effect



WL322W Up- and downward light effect

GreenSpace Evo Mini Wallmount

General Information

Driver included	Yes
Number of gear units	Unit

Light Technical

Correlated Colour Temperature (Nom)	3000 K
Colour rendering index (CRI)	>90
Optic type	High-reflective metal reflector Medium beam 20 to 40 degrees

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

Mechanical and Housing

Mech. impact protection code	IK02
Ingress protection code	IP20

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	(0.422, 0.386) SDCM <2
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous efficacy (rated) (nom.)	Luminous Flux
910505104904	WL321W 10S/PW930 PSU HMB FG BK482	123 lm/W	1.000 lm
910505104916	WL322W 10S/PW930 PSU HMB FG BK482	138 lm/W	2.100 lm
910505104898	WL321W 8S/PW930 PSU HMB FG WH481	118 lm/W	800 lm
910505104911	WL322W 8S/PW930 PSU HMB FG WH481	138 lm/W	1.600 lm
910505104910	WL321W 12S/PW930 WIA HMB FG GR482	126 lm/W	1.300 lm
910505104921	WL322W 12S/PW930 WIA HMB FG GR482	137 lm/W	2.600 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505104904	WL321W 10S/PW930 PSU HMB FG BK482	8.5 W
910505104916	WL322W 10S/PW930 PSU HMB FG BK482	15.3 W
910505104898	WL321W 8S/PW930 PSU HMB FG WH481	6.7 W

Order Code	Full Product Name	Power Consumption
910505104911	WL322W 8S/PW930 PSU HMB FG WH481	11.7 W
910505104910	WL321W 12S/PW930 WIA HMB FG GR482	10.3 W
910505104921	WL322W 12S/PW930 WIA HMB FG GR482	18.9 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505104904	WL321W 10S/PW930 PSU HMB FG BK482	No
910505104916	WL322W 10S/PW930 PSU HMB FG BK482	No
910505104898	WL321W 8S/PW930 PSU HMB FG WH481	No

Order Code	Full Product Name	Dimmable
910505104911	WL322W 8S/PW930 PSU HMB FG WH481	No
910505104910	WL321W 12S/PW930 WIA HMB FG GR482	Yes
910505104921	WL322W 12S/PW930 WIA HMB FG GR482	Yes


Mechanical and Housing

GreenSpace Evo Mini Wallmount


Order Code	Full Product Name	Housing Colour
910505104904	WL321W 10S/PW930 PSU HMB FG BK482	Black
910505104916	WL322W 10S/PW930 PSU HMB FG BK482	Black
910505104898	WL321W 8S/PW930 PSU HMB FG WH481	White
910505104911	WL322W 8S/PW930 PSU HMB FG WH481	White
910505104910	WL321W 12S/PW930 WIA HMB FG GR482	Grey
910505104921	WL322W 12S/PW930 WIA HMB FG GR482	Grey

GreenSpace Evo Mini Wallmount


Polar Wide Diagrams




Polar Normal (separate) - WL320WI -
910505104898




Polar Normal (separate) - WL320WI -
910505104910




Polar Normal (separate) - WL320WI -
910505104921



Polar Normal (separate) - WL320WI -
910505104904



Polar Normal (separate) - WL320WI -
910505104911



Polar Normal (separate) - WL320WI -
910505104916

