



Actinic BL PL-S/PL-L – compact for design freedom

Actinic BL PL-S/PL-L

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Vantaggi

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

Caratteristiche

- Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- Low mercury content
- Compact lamp format

Applicazione

- Insect traps, Electronic Fly Killers (EFKs)

Actinic BL PL-S/PL-L

Warnings and safety

- È estremamente improbabile che la rottura di una lampada possa avere conseguenze sulla salute dei consumatori. Nel caso in cui una lampada si rompa, ventilare la stanza per 30 minuti e rimuovere i frammenti, preferibilmente indossando dei guanti. Riporre i frammenti in una busta di plastica sigillata e smaltirli presso i luoghi opportuni per il riciclo. Non utilizzare un aspirapolvere.

Versions




XPPR_XURPLL_0001-Product photo




XPPR XUAPLS 0001

Disegno tecnico



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
Actinic BL PL-S 9W/10/2P 1CT/ 6X10BOX	13 mm	28 mm	128,8 mm	144,5 mm	167 mm



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 18W/10/4P 1CT/25	18 mm	39 mm	194,2 mm	220 mm	226,6 mm

Dati tecnici di illuminazione

Designazione colore UltraViolet A

Informazioni generali

Order Code	Full Product Name	Attacco
26018540	PL-L 18W/10/4P 1CT/25	2G11

Actinic BL PL-S/PL-L

Order Code	Full Product Name	Attacco
95194680	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	G23

Dati tecnici di illuminazione

Order Code	Full Product Name	Codice colore
26018540	PL-L 18W/10/4P 1CT/25	10

Order Code	Full Product Name	Codice colore
95194680	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	210

Funzionamento e parte elettrica

Order Code	Full Product Name	Corrente lampada (Nom)	Consumo energetico
26018540	PL-L 18W/10/4P 1CT/25	0,375 A	18 W
95194680	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	0,17 A	8,6 W

Meccanica e corpo

Order Code	Full Product Name	Forma lampadina
26018540	PL-L 18W/10/4P 1CT/25	2xT16

Order Code	Full Product Name	Forma lampadina
95194680	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	2XT12

