

UrbanFlex: uniformity in design

Today's modern cities are looking to be more attractive, welcoming, convenient and safe. These characteristics help ensure that inhabitants want to live in the city, businesses can maximize their prosperity and visitors can better enjoy their stay. For these reasons, we designed UrbanFlex: a visually coherent and flexible lighting solution to perfectly fit a wide range of urban applications. The signature style is modern and minimal, thereby giving your cityscape a visually coherent, elegant and discrete identity. UrbanFlex is available in two sizes and offers a large diversity of mountings and dedicated brackets and poles. Thanks to the built in Philips Ledgine optimized LED platform, and the wide range of available application-tailored optics, UrbanFlex delivers best in class lighting performance in a broad range of applications. By being System Ready our luminaire offers connectivity and dimming options while it can be paired with lighting management systems such as Interact City or existing and upcoming sensor innovations. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application, making maintenance and programming operations faster and easier, and enabling you to create your digital library of lighting assets and spare parts. As a company conscious about the impact of light on the environment and biodiversity, we also equipped UrbanFlex with our dedicated light recipe that preserves a dark night sky. UrbanFlex is designed for customers looking for ways to achieve uniformity in design and quality of light with elegant, energy-efficient and sustainable products.


Benefits

- Coherent and flexible solution for a wide range of urban applications
- Future-ready thanks to the SR (System Ready) socket
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information
- Luminaire is also equipped with dedicated light recipes that help preserve a dark night sky and reduce light pollution

Applications

- Road and Street
- Parks and Plazas
- Residential
- Main urban roads and streets, side and residential roads and streets

Versions




- City centers and historical areas
- Cycle and pedestrian paths, squares, parks and playgrounds


Features

- Distinguished, flawless, modern design
- A broad range of elegant, dedicated or standard complete sets, including rectangular poles, brackets Lyre and Accent, post-top and side-entry versions
- Efficacy up to 157 lm/W, further optimization on performance flux level enabled by the Philips L-Tune
- Large choice of different beams and internal louvers to ensure minimized glare
- Surge protection, up to 10kV
- Ready to be connected to the Interact City lighting management software or to be paired with third party lighting management systems and sensors


Dimensional drawing



Pole with flange - 4.0 m - RAL color -



Pole with flange - 8.0 m - RAL color -



UrbanFlex lyre bracket - Pole-mounting bracket 1 arm - 0 mm - 0° - Dark gray - Mounting device diameter 60 mm -

Approval and Application

CE mark

Yes

Product Data

Product family code

JRP633 [URBANFLEX LYRE BRACKET]