






Recessed



Inrush current

Product Type	Run Current (A)(@220V)	Start (Inrush) Current(A) / Ipeak (A)	Start Current Duration (μs) / T(@50% of Ipeak) (μs)	Touch current or protective conductor current (mA)	MCB Type B 16A (or Type C 16A) Max no. fitting (pcs)
RC550B LED40S L120 PSU CD	0.196	19	275	0.3	≤24 for B (≤40 for C)
RC550B LED40S L120 PSU CD	0.196	19	275	0.3	≤24 for B (≤40 for C)
SM550C LED20S L60 PSU CD	0.105	14	250	0.3	≤33 for B (≤56 for C)
SM550C LED40S L120 PSD CD	0.196	22	275	0.4	≤24 for B (≤40 for C)
SM550C LED40S L120 PSU CD	0.196	19	280	0.3	≤24 for B (≤40 for C)
SP550P LED20S L60 PSU CD	0.105	14	250	0.3	≤33 for B (≤56 for C)
SP550P LED40S L120 PSD CD	0.196	22	275	0.4	≤24 for B (≤40 for C)





SlimBalance SP550P SM550C RC550B Mounting Instruction

4441 000 06603 1b



Product Type	Voltage (v)	Frequency (Hz)	I (A)	Power (w)	CCT	Installation	Weight (Kg)	Max. Number (PCS)
RC550B LED40S 840 L120 PSU CD GM	220-240~	50/60	0.196	41	NW	Recessed	3.7	10
RC550B LED40S 865 L120 PSU CD GM	220-240~	50/60	0.196	41	CW	Recessed	3.7	10
SM550C LED20S 840 L60 PSU CD GM	220-240~	50/60	0.105	22	NW	Surfaced	2.3	10
SM550C LED40S 840 L120 PSD CD GM	220-240~	50/60	0.196	41	NW	Surfaced	3.8	10
SM550C LED40S 840 L120 PSU CD GM	220-240~	50/60	0.196	41	NW	Surfaced	3.7	10
SP550P LED20S 840 L60 PSU CD GM	220-240~	50/60	0.105	22	NW	Suspended	2.3	10
SP550P LED40S 840 L120 PSD CD GM	220-240~	50/60	0.196	41	NW	Suspended	3.8	10
SP550P LED40S 840 L120 PSU CD GM	220-240~	50/60	0.196	41	NW	Suspended	3.7	10
SP550P LED40S 865 L120 PSD CD GM	220-240~	50/60	0.196	41	CW	Suspended	3.8	10
SP550P LED40S 865 L120 PSU CD GM	220-240~	50/60	0.196	41	CW	Suspended	3.7	10
ACS50Z End cap PSD	220-240~	50/60					0.12	
ACS50Z End cap PSU	220-240~	50/60					0.12	




Signify (China) Investment Co., Ltd.
Building No. 9, Lane 888 Tianlin Road, Minghang District, Shanghai, China
Postalcode: 200233





PHILIPS

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.

Installation & Connection



Suspended



Surfaced

