

by (Signify

Step into the future of site lighting

Site & Area

OptiForm





Bring innovation to your site

Introducing OptiForm, a luminaire family that does it all. Invest in area and site lighting that supports your creative vision, enables easy installation and maintenance, and outperforms industry leaders. Escalate your outdoor space with luminaires that revolutionize site and area illumination by saving time, energy and money. Elevate your space with OptiForm.



Redefining efficiency

For any site and area project, OptiForm luminaires are the intersection of aesthetics, efficacy, and flexibility.

- With up to 190 LPW, OptiForm offers best-in-class efficacy to meet energy codes and wattage requirements.
- Lumen outputs range from 2,000-63,000, creating a heightened sense of security for any outdoor site.
- Eleven optical distributions are available to meet photometric requirements for even the most challenging applications.
- A low-profile and lightweight design enhances any project for site integration and simplifies installation.







Illumination your way

666666

Optical Distributions



OptiForm offers three sizes and multiple optical distributions to suit a variety of applications. Specialty optics and shields are available to illuminate the spaces you need and shield the spaces you don't.

Optical distributions available with OptiForm

- Precision Plus Optics: Type 2, 3, 4, 5
- Site & Area Optics: Type 2, 3, 4, 5 medium, type 4 wide, type 5 wide, type 5 narrow, auto front row
- **Specialty optics** eliminate spill light: backlight control, LEED corner left, LEED corner right
- Internal shields also available

Installation designed with you in mind



Retrofit arm mount capability standard

Offering the convenience of a Retrofit Arm Mount, built-in to the luminaire. This means you can mount to existing drill patterns with no additional pieces necessary.



Lightweight design

Enjoy the convenience of installation facilitated by just one person – whether you are mounting the small luminaire or the large.



Round or square pole mounting standard

A standard arm that easily mounts to round and square poles, no additional pieces required. No action is required for mounting to a square pole. When mounting to a round pole, simply remove the knock out on the back of the arm.

Two-piece housing

Experience easy installation enabled by the two-piece housing







Three mounting options

Maintain continuity in your site with cohesive designs across three mounting options.





Mast Arm



Wall Bracket

gardcolighting.com/optiform 7

A sustainable choice

At Signify, we are on a mission to create a better world with environmentally friendly light. While we transition toward a sustainable and circular economy, we are rethinking the way we produce and consume. As a new generation of LED lighting, OptiForm luminaires were designed to have as minimal of an impact on the environment as possible.

OptiForm achieves this in several ways:





Maintenance, simplified.

All OptiForm luminaires are equipped with Service Tag.

Service Tag identifies each product with a unique QR code that can be scanned to access specific product information using a hand-held device like a smartphone or tablet. If required, spare parts can also be configured to the original registered settings for any specific luminaire. Your installation and maintenance process become faster, easier and more cost-effective throughout the life of the product with these Service Tag features.





Controls



Dimming Options

Save energy automatically and on demand

- Comes with a dimmable LED driver for 0-10V dimming.
- Dynadimmer facilitates on-demand light levels for high energy savings.
- Field Adjustable Wattage Selector enables user to manually adjust the wattage in the field.

Programmable Motion Response

Standalone Motion Sensor

- Dims luminaires to 25% power when no motion is detected
- Settings can be adjusted in the field



Outdoor Multisensor

Observe and adjust with monitoring sensors

- Allows for advanced adaptive lighting management.
- Monitor motion detection, temperature and noise levels with environmental sensors.

Unlock connectivity with Interact

Make the leap from smart lighting to super smart lighting

Connectivity is the future and key to unlocking your smart building potential. Interact is a connected system with wireless luminaire level controls and integral occupancy & daylight sensing.



Start simple and lay the foundation

- Smart lighting with luminaire integrated occupancy and daylight sensor.
- Save up to 80% on installation and material cost compared with more complex systems.¹
- 1. Compared to wired networked lighting control systems.

Features

- No additional wiring required during installation.
- Motion, daylight sensing and grouping can be done right out of the box.
- A gateway can be added at any time for additional features, such as scheduling and remote management.
- Set up is simple and can be done from your smart phone.
- Interact delivers a consistent experience between indoor and outdoor lighting control.
- Interact is the only system that offers wireless connectivity and control for lamps, luminaries, and retrofit kits.







Join the OptiForm revolution

Learn how Gardco Optiform luminaires revolutionize site lighting for your projects. Simplify installation and maintenance and achieve industryleading efficacy without compromising on your design.

Contact a Sales Representative for a personal demonstration or visit **gardcolighting.com/optiform** for more information.

Signify

© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

PGc-2301BR - OptiForm Brochure 03/23 www.gardcolighting.com

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008