

**INSTALLATION INSTRUCTIONS:
CF4, CF6, CXF4, & CXF6
TOP MOUNT FIXTURES****CAUTION**

1. The electrical power must be disconnected from the fixture and pole before installing, servicing, or relamping the fixture.
2. These directions must be read carefully and adhered to. Failure to do so may result in injury, damage to the fixture, and voiding the warranty.
3. "CF4T OR CF6T" Hanging Option (only): This version of the fixture must be hung from a Universal Fixture adapter, supplied with all Hadco arms, or as a separate accessory to be mounted to a non-Hadco arm. See the instructions supplied with the adapter for further information.

TOOLS REQUIRED**FOR INSTALLATION**

1. #2 Phillips screw driver - to remove or re-install the reflector assembly and ballast assembly.
2. 5/16" Allen wrench - to assemble (2) piece clamp collar

INSTALLATION (CF4T or CF6T)

WARNING - The power **MUST** be turned off prior to proceeding. Read these instructions carefully. If any problems are encountered that are not covered in these instructions, contact Hadco for assistance.

STEP 1: The fixture is designed to hang from the Universal Fixture Adapter.

- To hang the fixture, first connect the power supply quick-connect on the fixture to the quick-connect on the arm.
- Then hang the fixture per the instructions supplied with your Adapter.
 - * Be sure the fixture is straight and securely attached before proceeding.
- For CXF fixtures, skip to Step 6.

STEP 2: OPEN LENS DOOR

- To open the lens door, push the spring latch away from the fixture. This allows the door to swing open. A safety cable will prevent it from falling, should it come out of the hinge.

STEP 3: INSTALL LAMP

- Install the correct lamp based upon the lamp label next to the socket.

STEP 4: TYPE 3 REFLECTOR (only)

- Carefully loosen the (2) Adapter screws just enough to rotate the fixture.
- Rotate the fixture to the desired orientation.
- Then retighten the screws to lock the fixture in that position.

STEP 5: CLOSE LENS DOOR

- Close by pushing lens door up. Ensure that spring latch engages completely.

STEP 6: Connect the power, and test the fixture for proper operation.

STEP 7: After the installation is complete, deliver this instruction manual to the owner.

TO REPLACE LAMP

STEP 1: It is a good idea to clean the fixture each time you relamp. Avoid using harsh solvents or abrasives while cleaning fixture.

STEP 2: Open the lens door by pushing the spring latch away from the fixture.

STEP 3: Remove the old lamp and dispose of it in a responsible manner.

STEP 4: Install a new lamp, referring to the lamp label next to the socket to ensure the correct type.


STEP 5: Close by pushing lens door up. Ensure that spring latch engages completely.



This fixture is intended for installation in accordance with the National Electrical Code and local code specifications. Failure to adhere to these codes and instructions may result in serious injury and/or damage to the ballast and void the warranty. These instructions do not purport to cover all details or variations in equipment, nor to provide for every possible contingency related to installation, operation, maintenance, or mounting situation. Should specific problems occur that are not addressed by these instructions, contact your Sales Representative or distributor for assistance. Retain these instructions for future reference.

DISCLAIMER

While we believe these instructions to be accurate at the time of publication, Hadco reserves the right to make changes to this fixture and/or components. The contractor should follow local and national electrical codes where required. For any further information please contact Hadco customer service.



(CF Series Shown)