

Day-Brite

CFI

by Signify

Surface

DuaLED 2x2

2100, 2700, 3400, 3800,
or 4400 lumens



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

The Day-Brite / CFI DuaLED surface LED is a highly efficient, visually comfortable, architecturally styled surface LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. Its clean modern design offers a fresh variation on the popular dual chamber theme and provides architectural styling compatible with virtually any area

Ordering guide

Example: **2SDL27L840-2-D-UNV-DIM**

Width	Family	Lumen Package	Color	Length	Center Diffuser	Voltage	Driver	Options
2	SDL		—	2	D	—	—	
2 2'	SDL Surface DuaLED	21L 2100 nominal delivered lumens 27L 2700 nominal delivered lumens 34L 3400 nominal delivered lumens 38L 3800 nominal delivered lumens 44L 4400 nominal delivered lumens	830 80 CRI, 3000K 835 80 CRI, 3500K 840 80 CRI, 4000K 850 80 CRI, 5000K	2 2'	D Diffuse (opal)	UNV Universal Voltage, 120-277 volt 347 347V	DIM ¹ 0-10V dimming SDIM Step dimming to 40% input power DALI DALI dimming	AG Antimicrobial paint CC Custom color GLR Fusing, fast blow SWZG2 ^{2,3} Integral sensor, daylighting and occupancy, advanced grouping with dwell time and zoning SWZDT ² Integral sensor, daylighting and occupancy, advanced grouping with dwell time DAYOCC ² Integral sensor, daylighting and occupancy, basic grouping DSC Quick driver disconnect

Footnotes

- 1 Integral SWZDT and DAYOCC options dimmable to 5% via wireless wall switch, all other 0-10V wired configurations dimmable to 1%.
- 2 Specify only with -DIM driver option.
- 3 Must order SWZ-REMOTE SpaceWise handheld remote with each system order.

SpaceWise (SWZG2) Accessories (order separately)

- **SWZ-REMOTE** – SpaceWise handheld remote for grouping and configuration (at least one remote required for any SpaceWise installation)
- **LRM1743** – External sensor to increase occupancy coverage area of SpaceWise luminaire groups
- **UID8451/10** – Wireless Dimmer Switch Selector
- **UID8461/10** – Wireless Scene Selector

Energy Data

Luminaire	Catalog Number	Input Power	Efficacy
2x2	2SDL27L840	22.5	118
	2SDL34L840	29.3	117
	2SDL38L840	32.9	117
	2SDL44L840	39.0	114



2SDL DuaLED surface LED 2x2

2100, 2700, 3400, 3800, or 4400 lumens

Application

- A highly efficient, visually comfortable, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives.
- Low profile configuration is only 3" high with sloped sides for a sleek appearance.
- Clean, modern design offers a fresh variation on the popular dual chamber theme and provides architectural styling compatible with virtually any area.
- Soft opal diffusers with large luminous area minimize apparent brightness and provide high visual comfort perfect for a wide variety of general lighting applications like offices, schools, retail, or healthcare.
- Multiple lumen packages over a wide range provide significant application flexibility over light levels and/or luminaire spacing.
- A high lumen package can be used in conjunction with wide luminaire spacing to reduce luminaire quantities and overall cost while maintaining good uniformity.
- High efficiency source and luminaire design create significant energy savings over conventional solutions. Recommended light levels can frequently be achieved with lighting power densities of 0.5 to 0.85 Watts per square foot, complying with any known energy code.
- Directs a controlled amount of light to the higher angles in the room to balance the brightness of the surfaces and eliminate "cave effect" while creating the impression of a larger, brighter space without glare.
- Excellent color rendering with a CRI of 80.
- LEDs are an excellent source for use with controls since dimming or frequent switching does not degrade the performance or life of the source. Integral or external sensors are available for use.
- Surface mount design requires no plenum space.
- DuaLED luminaires are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers. (www.designlights.org/QPL)

Construction/Finish

- Uncomplicated design is well under 3" in depth and only requires a few parts outside of the electrical system and hardware, creating several benefits:
 - Less material required
 - Less packaging required
 - Reduced weight
 - Less energy required for construction and assembly
 - More luminaires can be shipped per truck to reduce fuel use and emissions

- Luminaire is painted after fabrication with a matte white polyester powder coating for a high quality, durable finish with no unfinished edges to create an installation hazard or potential for corrosion.

Electrical

- Total luminaire efficacy as high as 118 LPW (lumens per Watt) significantly reduces energy usage compared to conventional 2x2 sources.
- Driver and LED boards are easily accessible from below without tools. Multiple LED boards are individually replaceable if needed via plug-in connectors to ensure long service life.
- 0-10V dimming is standard.
- Five year limited luminaire warranty includes LED boards and driver. Visit www.philips.com/warranties for complete warranty information.
- High efficiency LEDs have a minimum 70,000 hour rated life (L70). Predicted L70 lifetime based on LED manufacturer's LM-80 data and in-situ laboratory testing.
- cETLus listed to UL and CSA standards, suitable for damp locations.

Enclosure

- Dual chamber configuration utilizes two diffusers with large surface area for brightness control.
- Opal diffusers provide soft, comfortable lighting while maintaining high efficiency.
- Diffusers require no frames or fasteners and can be easily removed from below without tools if needed.

General Notes

- All options factory installed.
- All accessories are field installed.
- Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

SpaceWise (SWZG2)

- Commissioning via SWZ-REMOTE handheld remote, must order a minimum of one per installation
- Integral sensing options (DAYOCC, SWZG2, SWZDT) may not be combined
- For more information on the sensor, please refer to www.lightingproducts.philips.com/documents/webdb2/DayBrite/pdf/SWZG2_sensor.pdf
- Visit www.philips.com/spacewise for more information about SpaceWise Technology (SWZG2)



DAYOCC & SpaceWise DT (SWZDT)

- Commissioning via compatible Android phone and Philips Field App
- Dimming via compatible wireless wall switch only (see below)
- Register for the commissioning app at <http://registration.componentcloud.philips.com/appregistration/>
- Integral sensing options (DAYOCC, SWZG2, SWZDT) may not be combined
- For more information including recommended switches, refer to the following –
 - DAYOCC** – www.lightingproducts.philips.com/documents/webdb2/DayBrite/pdf/DAYOCC_sensor.pdf
 - SWZDT** – www.lightingproducts.philips.com/documents/webdb2/DayBrite/pdf/SWZDT_sensor.pdf

2SDL DuaLED surface LED 2x2

2100, 2700, 3400, 3800, or 4400 lumens

Dimensions



SpaceWise (SWZ) automated wireless technology is available for integrated occupancy and daylight harvesting. Individual options for dimming, occupancy detection, and daylight harvesting are also available if SpaceWise option is not selected.

Photometry

2x2 DuaLED, 2700 nominal delivered lumens

LER – 118

Catalog No. 2SDL27L840-2-D-UNV-DIM Test No. 35426 S/MH 1.3 Lamp Type LED Lumens/Lamp 2671 Input Watts 22.5 Comparative yearly lighting energy cost per 1000 lumens – \$2.02 based on 3000 hrs. and \$.08 pwr KWH. The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology. Photometric values based on test performed in compliance with LM-79.	Candela distribution				Light Distribution			Average Luminance																																																																																																																																																					
	<table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>918</td><td>918</td><td>918</td><td>918</td></tr> <tr><td>5</td><td>915</td><td>914</td><td>915</td><td>914</td></tr> <tr><td>15</td><td>886</td><td>885</td><td>888</td><td>885</td></tr> <tr><td>25</td><td>819</td><td>823</td><td>828</td><td>823</td></tr> <tr><td>35</td><td>724</td><td>731</td><td>741</td><td>731</td></tr> <tr><td>45</td><td>607</td><td>618</td><td>630</td><td>618</td></tr> <tr><td>55</td><td>472</td><td>486</td><td>497</td><td>486</td></tr> <tr><td>65</td><td>327</td><td>340</td><td>344</td><td>340</td></tr> <tr><td>75</td><td>183</td><td>186</td><td>185</td><td>186</td></tr> <tr><td>85</td><td>53</td><td>50</td><td>51</td><td>50</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	918	918	918	918	5	915	914	915	914	15	886	885	888	885	25	819	823	828	823	35	724	731	741	731	45	607	618	630	618	55	472	486	497	486	65	327	340	344	340	75	183	186	185	186	85	53	50	51	50	<table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>716</td><td>26.8</td></tr> <tr><td>0-40</td><td>1174</td><td>44.0</td></tr> <tr><td>0-60</td><td>2084</td><td>78.0</td></tr> <tr><td>0-90</td><td>2671</td><td>100.0</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	716	26.8	0-40	1174	44.0	0-60	2084	78.0	0-90	2671	100.0	<table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>3118</td><td>3176</td><td>3236</td></tr> <tr><td>55</td><td>2987</td><td>3076</td><td>3144</td></tr> <tr><td>65</td><td>2811</td><td>2925</td><td>2952</td></tr> <tr><td>75</td><td>2571</td><td>2603</td><td>2590</td></tr> <tr><td>85</td><td>2213</td><td>2075</td><td>2108</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	3118	3176	3236	55	2987	3076	3144	65	2811	2925	2952	75	2571	2603	2590	85	2213	2075	2108																																																								
Vertical Angle	Horizontal Angle																																																																																																																																																												
	0°	45°	90°	-45°																																																																																																																																																									
0	918	918	918	918																																																																																																																																																									
5	915	914	915	914																																																																																																																																																									
15	886	885	888	885																																																																																																																																																									
25	819	823	828	823																																																																																																																																																									
35	724	731	741	731																																																																																																																																																									
45	607	618	630	618																																																																																																																																																									
55	472	486	497	486																																																																																																																																																									
65	327	340	344	340																																																																																																																																																									
75	183	186	185	186																																																																																																																																																									
85	53	50	51	50																																																																																																																																																									
Degrees	Lumens	% Luminaire																																																																																																																																																											
0-30	716	26.8																																																																																																																																																											
0-40	1174	44.0																																																																																																																																																											
0-60	2084	78.0																																																																																																																																																											
0-90	2671	100.0																																																																																																																																																											
Angle	End	45°	Cross																																																																																																																																																										
45	3118	3176	3236																																																																																																																																																										
55	2987	3076	3144																																																																																																																																																										
65	2811	2925	2952																																																																																																																																																										
75	2571	2603	2590																																																																																																																																																										
85	2213	2075	2108																																																																																																																																																										
Coefficients of Utilization EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)					<table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="2">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td colspan="8">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>RCR</td> <td colspan="8"></td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td> </tr> <tr> <td></td> <td>1</td><td>108</td><td>104</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>93</td> </tr> <tr> <td></td> <td>2</td><td>97</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td> </tr> <tr> <td></td> <td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>77</td><td>69</td><td>73</td><td>68</td> </tr> <tr> <td></td> <td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>59</td><td>66</td><td>58</td> </tr> <tr> <td></td> <td>5</td><td>75</td><td>61</td><td>53</td><td>72</td><td>60</td><td>53</td><td>58</td><td>52</td> </tr> <tr> <td></td> <td>6</td><td>69</td><td>56</td><td>46</td><td>68</td><td>55</td><td>46</td><td>53</td><td>46</td> </tr> <tr> <td></td> <td>7</td><td>64</td><td>51</td><td>41</td><td>63</td><td>50</td><td>41</td><td>47</td><td>40</td> </tr> <tr> <td></td> <td>8</td><td>59</td><td>46</td><td>38</td><td>57</td><td>46</td><td>36</td><td>44</td><td>36</td> </tr> <tr> <td></td> <td>9</td><td>56</td><td>42</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td> </tr> <tr> <td></td> <td>10</td><td>53</td><td>39</td><td>30</td><td>51</td><td>39</td><td>30</td><td>38</td><td>30</td> </tr> </tbody> </table>								Ceiling (pcc)	80%			70%			50%		70	50	30	70	50	30	50	30	Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%								RCR									Room Cavity Ratio	0	118	118	118	115	115	115	111	111		1	108	104	98	106	101	96	96	93		2	97	90	82	95	88	81	84	79		3	90	79	70	86	77	69	73	68		4	81	69	60	80	68	59	66	58		5	75	61	53	72	60	53	58	52		6	69	56	46	68	55	46	53	46		7	64	51	41	63	50	41	47	40		8	59	46	38	57	46	36	44	36		9	56	42	34	55	41	34	40	33		10	53	39	30	51	39	30	38	30
Ceiling (pcc)	80%			70%			50%																																																																																																																																																						
	70	50	30	70	50	30	50	30																																																																																																																																																					
Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																												
RCR																																																																																																																																																													
Room Cavity Ratio	0	118	118	118	115	115	115	111	111																																																																																																																																																				
	1	108	104	98	106	101	96	96	93																																																																																																																																																				
	2	97	90	82	95	88	81	84	79																																																																																																																																																				
	3	90	79	70	86	77	69	73	68																																																																																																																																																				
	4	81	69	60	80	68	59	66	58																																																																																																																																																				
	5	75	61	53	72	60	53	58	52																																																																																																																																																				
	6	69	56	46	68	55	46	53	46																																																																																																																																																				
	7	64	51	41	63	50	41	47	40																																																																																																																																																				
	8	59	46	38	57	46	36	44	36																																																																																																																																																				
	9	56	42	34	55	41	34	40	33																																																																																																																																																				
	10	53	39	30	51	39	30	38	30																																																																																																																																																				

2x2 DuaLED, 3400 nominal delivered lumens

LER – 117

Catalog No. 2SDL34L840-2-D-UNV-DIM Test No. 35427 S/MH 1.3 Lamp Type LED Lumens/Lamp 3450 Input Watts 29.3 Comparative yearly lighting energy cost per 1000 lumens – \$2.03 based on 3000 hrs. and \$.08 pwr KWH. The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology. Photometric values based on test performed in compliance with LM-79.	Candela distribution				Light Distribution			Average Luminance																																																																																																																																																					
	<table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>1186</td><td>1186</td><td>1186</td><td>1186</td></tr> <tr><td>5</td><td>1182</td><td>1181</td><td>1182</td><td>1181</td></tr> <tr><td>15</td><td>1145</td><td>1143</td><td>1147</td><td>1143</td></tr> <tr><td>25</td><td>1058</td><td>1062</td><td>1069</td><td>1062</td></tr> <tr><td>35</td><td>935</td><td>945</td><td>958</td><td>945</td></tr> <tr><td>45</td><td>784</td><td>799</td><td>813</td><td>799</td></tr> <tr><td>55</td><td>609</td><td>628</td><td>641</td><td>628</td></tr> <tr><td>65</td><td>421</td><td>439</td><td>442</td><td>439</td></tr> <tr><td>75</td><td>236</td><td>238</td><td>238</td><td>238</td></tr> <tr><td>85</td><td>68</td><td>63</td><td>65</td><td>63</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	1186	1186	1186	1186	5	1182	1181	1182	1181	15	1145	1143	1147	1143	25	1058	1062	1069	1062	35	935	945	958	945	45	784	799	813	799	55	609	628	641	628	65	421	439	442	439	75	236	238	238	238	85	68	63	65	63	<table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>925</td><td>26.8</td></tr> <tr><td>0-40</td><td>1516</td><td>43.9</td></tr> <tr><td>0-60</td><td>2692</td><td>78.0</td></tr> <tr><td>0-90</td><td>3451</td><td>100.0</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	925	26.8	0-40	1516	43.9	0-60	2692	78.0	0-90	3451	100.0	<table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>4024</td><td>4101</td><td>4177</td></tr> <tr><td>55</td><td>3856</td><td>3977</td><td>4058</td></tr> <tr><td>65</td><td>3620</td><td>3774</td><td>3802</td></tr> <tr><td>75</td><td>3309</td><td>3344</td><td>3337</td></tr> <tr><td>85</td><td>2842</td><td>2621</td><td>2725</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	4024	4101	4177	55	3856	3977	4058	65	3620	3774	3802	75	3309	3344	3337	85	2842	2621	2725																																																								
Vertical Angle	Horizontal Angle																																																																																																																																																												
	0°	45°	90°	-45°																																																																																																																																																									
0	1186	1186	1186	1186																																																																																																																																																									
5	1182	1181	1182	1181																																																																																																																																																									
15	1145	1143	1147	1143																																																																																																																																																									
25	1058	1062	1069	1062																																																																																																																																																									
35	935	945	958	945																																																																																																																																																									
45	784	799	813	799																																																																																																																																																									
55	609	628	641	628																																																																																																																																																									
65	421	439	442	439																																																																																																																																																									
75	236	238	238	238																																																																																																																																																									
85	68	63	65	63																																																																																																																																																									
Degrees	Lumens	% Luminaire																																																																																																																																																											
0-30	925	26.8																																																																																																																																																											
0-40	1516	43.9																																																																																																																																																											
0-60	2692	78.0																																																																																																																																																											
0-90	3451	100.0																																																																																																																																																											
Angle	End	45°	Cross																																																																																																																																																										
45	4024	4101	4177																																																																																																																																																										
55	3856	3977	4058																																																																																																																																																										
65	3620	3774	3802																																																																																																																																																										
75	3309	3344	3337																																																																																																																																																										
85	2842	2621	2725																																																																																																																																																										
Coefficients of Utilization EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)					<table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="2">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td colspan="8">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>RCR</td> <td colspan="8"></td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td> </tr> <tr> <td></td> <td>1</td><td>108</td><td>104</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>93</td> </tr> <tr> <td></td> <td>2</td><td>97</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td> </tr> <tr> <td></td> <td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>77</td><td>69</td><td>73</td><td>68</td> </tr> <tr> <td></td> <td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>59</td><td>66</td><td>58</td> </tr> <tr> <td></td> <td>5</td><td>75</td><td>61</td><td>53</td><td>72</td><td>60</td><td>53</td><td>58</td><td>52</td> </tr> <tr> <td></td> <td>6</td><td>69</td><td>56</td><td>46</td><td>68</td><td>55</td><td>46</td><td>53</td><td>46</td> </tr> <tr> <td></td> <td>7</td><td>64</td><td>51</td><td>41</td><td>63</td><td>50</td><td>41</td><td>47</td><td>40</td> </tr> <tr> <td></td> <td>8</td><td>59</td><td>46</td><td>38</td><td>57</td><td>46</td><td>36</td><td>44</td><td>36</td> </tr> <tr> <td></td> <td>9</td><td>56</td><td>42</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>33</td> </tr> <tr> <td></td> <td>10</td><td>53</td><td>39</td><td>30</td><td>51</td><td>39</td><td>30</td><td>38</td><td>30</td> </tr> </tbody> </table>								Ceiling (pcc)	80%			70%			50%		70	50	30	70	50	30	50	30	Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%								RCR									Room Cavity Ratio	0	118	118	118	115	115	115	111	111		1	108	104	98	106	101	96	96	93		2	97	90	82	95	88	81	84	79		3	90	79	70	86	77	69	73	68		4	81	69	60	80	68	59	66	58		5	75	61	53	72	60	53	58	52		6	69	56	46	68	55	46	53	46		7	64	51	41	63	50	41	47	40		8	59	46	38	57	46	36	44	36		9	56	42	34	55	41	34	40	33		10	53	39	30	51	39	30	38	30
Ceiling (pcc)	80%			70%			50%																																																																																																																																																						
	70	50	30	70	50	30	50	30																																																																																																																																																					
Wall (pw)	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																																												
RCR																																																																																																																																																													
Room Cavity Ratio	0	118	118	118	115	115	115	111	111																																																																																																																																																				
	1	108	104	98	106	101	96	96	93																																																																																																																																																				
	2	97	90	82	95	88	81	84	79																																																																																																																																																				
	3	90	79	70	86	77	69	73	68																																																																																																																																																				
	4	81	69	60	80	68	59	66	58																																																																																																																																																				
	5	75	61	53	72	60	53	58	52																																																																																																																																																				
	6	69	56	46	68	55	46	53	46																																																																																																																																																				
	7	64	51	41	63	50	41	47	40																																																																																																																																																				
	8	59	46	38	57	46	36	44	36																																																																																																																																																				
	9	56	42	34	55	41	34	40	33																																																																																																																																																				
	10	53	39	30	51	39	30	38	30																																																																																																																																																				

2SDL DuaLED surface LED 2x2

2100, 2700, 3400, 3800, or 4400 lumens

2x2 DuaLED, 3800 nominal delivered lumens

LER – 117

Catalog No. 2SDL38L840-2-D-UNV-DIM Test No. 35428 S/MH 1.3 Lamp Type LED Lumens/Lamp 3849 Input Watts 32.9 Comparative yearly lighting energy cost per 1000 lumens – \$2.05 based on 3000 hrs. and \$.08 pwr KWH. The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology. Photometric values based on test performed in compliance with LM-79.	Candela distribution <table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>1323</td><td>1323</td><td>1323</td><td>1323</td></tr> <tr><td>5</td><td>1319</td><td>1317</td><td>1319</td><td>1317</td></tr> <tr><td>15</td><td>1277</td><td>1276</td><td>1279</td><td>1276</td></tr> <tr><td>25</td><td>1181</td><td>1185</td><td>1192</td><td>1185</td></tr> <tr><td>35</td><td>1044</td><td>1054</td><td>1068</td><td>1054</td></tr> <tr><td>45</td><td>875</td><td>891</td><td>907</td><td>891</td></tr> <tr><td>55</td><td>680</td><td>700</td><td>716</td><td>700</td></tr> <tr><td>65</td><td>470</td><td>490</td><td>495</td><td>490</td></tr> <tr><td>75</td><td>264</td><td>266</td><td>267</td><td>266</td></tr> <tr><td>85</td><td>76</td><td>71</td><td>73</td><td>71</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	1323	1323	1323	1323	5	1319	1317	1319	1317	15	1277	1276	1279	1276	25	1181	1185	1192	1185	35	1044	1054	1068	1054	45	875	891	907	891	55	680	700	716	700	65	470	490	495	490	75	264	266	267	266	85	76	71	73	71	Light Distribution <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>1032</td><td>26.8</td></tr> <tr><td>0-40</td><td>1692</td><td>43.9</td></tr> <tr><td>0-60</td><td>3003</td><td>78.0</td></tr> <tr><td>0-90</td><td>3850</td><td>100</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1032	26.8	0-40	1692	43.9	0-60	3003	78.0	0-90	3850	100	Average Luminance <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>4492</td><td>4574</td><td>4659</td></tr> <tr><td>55</td><td>4302</td><td>4431</td><td>4532</td></tr> <tr><td>65</td><td>4040</td><td>4206</td><td>4250</td></tr> <tr><td>75</td><td>3699</td><td>3734</td><td>3742</td></tr> <tr><td>85</td><td>3171</td><td>2958</td><td>3054</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	4492	4574	4659	55	4302	4431	4532	65	4040	4206	4250	75	3699	3734	3742	85	3171	2958	3054																																				
	Vertical Angle		Horizontal Angle																																																																																																																																						
0°		45°	90°	-45°																																																																																																																																					
0	1323	1323	1323	1323																																																																																																																																					
5	1319	1317	1319	1317																																																																																																																																					
15	1277	1276	1279	1276																																																																																																																																					
25	1181	1185	1192	1185																																																																																																																																					
35	1044	1054	1068	1054																																																																																																																																					
45	875	891	907	891																																																																																																																																					
55	680	700	716	700																																																																																																																																					
65	470	490	495	490																																																																																																																																					
75	264	266	267	266																																																																																																																																					
85	76	71	73	71																																																																																																																																					
Degrees	Lumens	% Luminaire																																																																																																																																							
0-30	1032	26.8																																																																																																																																							
0-40	1692	43.9																																																																																																																																							
0-60	3003	78.0																																																																																																																																							
0-90	3850	100																																																																																																																																							
Angle	End	45°	Cross																																																																																																																																						
45	4492	4574	4659																																																																																																																																						
55	4302	4431	4532																																																																																																																																						
65	4040	4206	4250																																																																																																																																						
75	3699	3734	3742																																																																																																																																						
85	3171	2958	3054																																																																																																																																						
	Coefficients of Utilization EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20) <table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="3">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td>70</td> <td>50</td> <td>30</td> <td>70</td> <td>50</td> <td>30</td> <td>50</td> <td>30</td> </tr> <tr> <td>RCR</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td> <td>118</td> <td>118</td> <td>118</td> <td>115</td> <td>115</td> <td>115</td> <td>111</td> </tr> <tr> <td></td> <td>1</td> <td>108</td> <td>104</td> <td>98</td> <td>106</td> <td>101</td> <td>96</td> <td>96</td> </tr> <tr> <td></td> <td>2</td> <td>97</td> <td>90</td> <td>82</td> <td>95</td> <td>88</td> <td>81</td> <td>84</td> </tr> <tr> <td></td> <td>3</td> <td>90</td> <td>79</td> <td>70</td> <td>86</td> <td>77</td> <td>69</td> <td>73</td> </tr> <tr> <td></td> <td>4</td> <td>81</td> <td>69</td> <td>60</td> <td>80</td> <td>68</td> <td>59</td> <td>66</td> </tr> <tr> <td></td> <td>5</td> <td>75</td> <td>61</td> <td>53</td> <td>72</td> <td>60</td> <td>53</td> <td>58</td> </tr> <tr> <td></td> <td>6</td> <td>69</td> <td>56</td> <td>46</td> <td>68</td> <td>55</td> <td>46</td> <td>53</td> </tr> <tr> <td></td> <td>7</td> <td>64</td> <td>51</td> <td>41</td> <td>63</td> <td>50</td> <td>41</td> <td>47</td> </tr> <tr> <td></td> <td>8</td> <td>59</td> <td>46</td> <td>38</td> <td>57</td> <td>46</td> <td>36</td> <td>44</td> </tr> <tr> <td></td> <td>9</td> <td>56</td> <td>42</td> <td>34</td> <td>55</td> <td>41</td> <td>34</td> <td>40</td> </tr> <tr> <td></td> <td>10</td> <td>53</td> <td>39</td> <td>30</td> <td>51</td> <td>39</td> <td>30</td> <td>38</td> </tr> </tbody> </table>	Ceiling (pcc)	80%			70%			50%			70	50	30	70	50	30	50	30	Wall (pw)	70	50	30	70	50	30	50	30	RCR	Zonal cavity method - Effective floor reflectance = 20%									Room Cavity Ratio	0	118	118	118	115	115	115	111		1	108	104	98	106	101	96	96		2	97	90	82	95	88	81	84		3	90	79	70	86	77	69	73		4	81	69	60	80	68	59	66		5	75	61	53	72	60	53	58		6	69	56	46	68	55	46	53		7	64	51	41	63	50	41	47		8	59	46	38	57	46	36	44		9	56	42	34	55	41	34	40		10	53	39	30	51	39	30	38
Ceiling (pcc)	80%			70%			50%																																																																																																																																		
	70	50	30	70	50	30	50	30																																																																																																																																	
Wall (pw)	70	50	30	70	50	30	50	30																																																																																																																																	
RCR	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																								
Room Cavity Ratio	0	118	118	118	115	115	115	111																																																																																																																																	
	1	108	104	98	106	101	96	96																																																																																																																																	
	2	97	90	82	95	88	81	84																																																																																																																																	
	3	90	79	70	86	77	69	73																																																																																																																																	
	4	81	69	60	80	68	59	66																																																																																																																																	
	5	75	61	53	72	60	53	58																																																																																																																																	
	6	69	56	46	68	55	46	53																																																																																																																																	
	7	64	51	41	63	50	41	47																																																																																																																																	
	8	59	46	38	57	46	36	44																																																																																																																																	
	9	56	42	34	55	41	34	40																																																																																																																																	
	10	53	39	30	51	39	30	38																																																																																																																																	

2x2 DuaLED, 4400 nominal delivered lumens

LER – 114

Catalog No. 2SDL44L840-2-D-UNV-DIM Test No. 35429 S/MH 1.3 Lamp Type LED Lumens/Lamp 4670 Input Watts 40.9 Comparative yearly lighting energy cost per 1000lumens – \$2.07 based on 3000 hrs. and \$.08 pwr KWH. The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology. Photometric values based on test performed in compliance with LM-79.	Candela distribution <table border="1"> <thead> <tr> <th rowspan="2">Vertical Angle</th> <th colspan="4">Horizontal Angle</th> </tr> <tr> <th>0°</th> <th>45°</th> <th>90°</th> <th>-45°</th> </tr> </thead> <tbody> <tr><td>0</td><td>1603</td><td>1603</td><td>1603</td><td>1603</td></tr> <tr><td>5</td><td>1598</td><td>1598</td><td>1600</td><td>1598</td></tr> <tr><td>15</td><td>1548</td><td>1548</td><td>1553</td><td>1548</td></tr> <tr><td>25</td><td>1430</td><td>1438</td><td>1447</td><td>1438</td></tr> <tr><td>35</td><td>1264</td><td>1278</td><td>1296</td><td>1278</td></tr> <tr><td>45</td><td>1059</td><td>1081</td><td>1101</td><td>1081</td></tr> <tr><td>55</td><td>824</td><td>850</td><td>870</td><td>850</td></tr> <tr><td>65</td><td>571</td><td>596</td><td>601</td><td>596</td></tr> <tr><td>75</td><td>319</td><td>325</td><td>324</td><td>325</td></tr> <tr><td>85</td><td>93</td><td>87</td><td>90</td><td>87</td></tr> </tbody> </table>	Vertical Angle	Horizontal Angle				0°	45°	90°	-45°	0	1603	1603	1603	1603	5	1598	1598	1600	1598	15	1548	1548	1553	1548	25	1430	1438	1447	1438	35	1264	1278	1296	1278	45	1059	1081	1101	1081	55	824	850	870	850	65	571	596	601	596	75	319	325	324	325	85	93	87	90	87	Light Distribution <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>1252</td><td>26.8</td></tr> <tr><td>0-40</td><td>2052</td><td>44.0</td></tr> <tr><td>0-60</td><td>3641</td><td>78.0</td></tr> <tr><td>0-90</td><td>4668</td><td>100.0</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1252	26.8	0-40	2052	44.0	0-60	3641	78.0	0-90	4668	100.0	Average Luminance <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>5436</td><td>5546</td><td>5651</td></tr> <tr><td>55</td><td>5212</td><td>5377</td><td>5500</td></tr> <tr><td>65</td><td>4901</td><td>5113</td><td>5161</td></tr> <tr><td>75</td><td>4475</td><td>4553</td><td>4535</td></tr> <tr><td>85</td><td>3880</td><td>3618</td><td>3730</td></tr> </tbody> </table>	Angle	End	45°	Cross	45	5436	5546	5651	55	5212	5377	5500	65	4901	5113	5161	75	4475	4553	4535	85	3880	3618	3730																																				
	Vertical Angle		Horizontal Angle																																																																																																																																						
0°		45°	90°	-45°																																																																																																																																					
0	1603	1603	1603	1603																																																																																																																																					
5	1598	1598	1600	1598																																																																																																																																					
15	1548	1548	1553	1548																																																																																																																																					
25	1430	1438	1447	1438																																																																																																																																					
35	1264	1278	1296	1278																																																																																																																																					
45	1059	1081	1101	1081																																																																																																																																					
55	824	850	870	850																																																																																																																																					
65	571	596	601	596																																																																																																																																					
75	319	325	324	325																																																																																																																																					
85	93	87	90	87																																																																																																																																					
Degrees	Lumens	% Luminaire																																																																																																																																							
0-30	1252	26.8																																																																																																																																							
0-40	2052	44.0																																																																																																																																							
0-60	3641	78.0																																																																																																																																							
0-90	4668	100.0																																																																																																																																							
Angle	End	45°	Cross																																																																																																																																						
45	5436	5546	5651																																																																																																																																						
55	5212	5377	5500																																																																																																																																						
65	4901	5113	5161																																																																																																																																						
75	4475	4553	4535																																																																																																																																						
85	3880	3618	3730																																																																																																																																						
	Coefficients of Utilization EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20) <table border="1"> <thead> <tr> <th rowspan="2">Ceiling (pcc)</th> <th colspan="3">80%</th> <th colspan="3">70%</th> <th colspan="3">50%</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>Wall (pw)</td> <td>70</td> <td>50</td> <td>30</td> <td>70</td> <td>50</td> <td>30</td> <td>50</td> <td>30</td> </tr> <tr> <td>RCR</td> <td colspan="9">Zonal cavity method - Effective floor reflectance = 20%</td> </tr> <tr> <td>Room Cavity Ratio</td> <td>0</td> <td>119</td> <td>119</td> <td>119</td> <td>116</td> <td>116</td> <td>116</td> <td>111</td> </tr> <tr> <td></td> <td>1</td> <td>108</td> <td>104</td> <td>99</td> <td>106</td> <td>101</td> <td>97</td> <td>97</td> </tr> <tr> <td></td> <td>2</td> <td>98</td> <td>90</td> <td>83</td> <td>96</td> <td>88</td> <td>82</td> <td>85</td> </tr> <tr> <td></td> <td>3</td> <td>90</td> <td>79</td> <td>71</td> <td>87</td> <td>77</td> <td>70</td> <td>74</td> </tr> <tr> <td></td> <td>4</td> <td>82</td> <td>70</td> <td>61</td> <td>80</td> <td>69</td> <td>60</td> <td>66</td> </tr> <tr> <td></td> <td>5</td> <td>75</td> <td>62</td> <td>53</td> <td>73</td> <td>61</td> <td>53</td> <td>59</td> </tr> <tr> <td></td> <td>6</td> <td>70</td> <td>56</td> <td>47</td> <td>68</td> <td>55</td> <td>47</td> <td>53</td> </tr> <tr> <td></td> <td>7</td> <td>64</td> <td>51</td> <td>42</td> <td>63</td> <td>50</td> <td>42</td> <td>48</td> </tr> <tr> <td></td> <td>8</td> <td>60</td> <td>46</td> <td>38</td> <td>58</td> <td>46</td> <td>37</td> <td>44</td> </tr> <tr> <td></td> <td>9</td> <td>56</td> <td>43</td> <td>34</td> <td>55</td> <td>42</td> <td>34</td> <td>41</td> </tr> <tr> <td></td> <td>10</td> <td>53</td> <td>39</td> <td>31</td> <td>51</td> <td>39</td> <td>31</td> <td>38</td> </tr> </tbody> </table>	Ceiling (pcc)	80%			70%			50%			70	50	30	70	50	30	50	30	Wall (pw)	70	50	30	70	50	30	50	30	RCR	Zonal cavity method - Effective floor reflectance = 20%									Room Cavity Ratio	0	119	119	119	116	116	116	111		1	108	104	99	106	101	97	97		2	98	90	83	96	88	82	85		3	90	79	71	87	77	70	74		4	82	70	61	80	69	60	66		5	75	62	53	73	61	53	59		6	70	56	47	68	55	47	53		7	64	51	42	63	50	42	48		8	60	46	38	58	46	37	44		9	56	43	34	55	42	34	41		10	53	39	31	51	39	31	38
Ceiling (pcc)	80%			70%			50%																																																																																																																																		
	70	50	30	70	50	30	50	30																																																																																																																																	
Wall (pw)	70	50	30	70	50	30	50	30																																																																																																																																	
RCR	Zonal cavity method - Effective floor reflectance = 20%																																																																																																																																								
Room Cavity Ratio	0	119	119	119	116	116	116	111																																																																																																																																	
	1	108	104	99	106	101	97	97																																																																																																																																	
	2	98	90	83	96	88	82	85																																																																																																																																	
	3	90	79	71	87	77	70	74																																																																																																																																	
	4	82	70	61	80	69	60	66																																																																																																																																	
	5	75	62	53	73	61	53	59																																																																																																																																	
	6	70	56	47	68	55	47	53																																																																																																																																	
	7	64	51	42	63	50	42	48																																																																																																																																	
	8	60	46	38	58	46	37	44																																																																																																																																	
	9	56	43	34	55	42	34	41																																																																																																																																	
	10	53	39	31	51	39	31	38																																																																																																																																	

