


Day-Brite CFI

by  Signify

Linear

LSW LED
wall mount

3400, 3900, 4400, 4900lm



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Day-Brite / CFI LSW LED wall mount is a specification grade luminaire with prismatic acrylic lens. Only 3 7/8" deep, it meets Americans with Disabilities Act (wall mounted). Ideal for or over mirror, over bed, corridor, stairwell and bulletin board applications.

Ordering guide

Example: **LS4R34A40UDZT-GLR**

Family	Fixture Length	Lens Type	Lumen Package	Color Temperature	Voltage	Driver Type	Options
LS	4	R				—	
LS Surface/Wall	4 48" (Nominal size)	R Linear prismatic virgin acrylic lens	34A 3400 delivered lumens 39A 3900 delivered lumens 44A 4400 delivered lumens 49A 4900 delivered lumens	40 4000K 35 3500K	U Universal voltage 120-277V 347 347V	DZT 0-10V dimming driver SZT 100/40 step dimming driver (46A only)	EMLED Integral emergency battery pack GLR Fusing, fast blow



LS LED wall mount

3400, 3900, 4400, or 4900 lumens

Features

- For wall mounted applications.
- Can be vertically or horizontally mounted on wall.
- Field replaceable LED array and drivers accessible from below.
- Integrated thermal management system conducts heat away from LEDs and transfers it to the surrounding environment.
- Factory calibrated intelligent driver capable of providing various lumen outputs to balance energy savings with lighting application needs.
- High efficiency LEDs have 50,000 hour rated life at L70.
- Predicted L70 lifetime is based on LED manufacturer's supplied LM-80 data and in-situ laboratory testing.
- Only 3 7/8" deep, meets Americans with Disabilities Act for wall mounted fixtures.
- Low brightness .125 thick linear prismatic virgin acrylic refractor.
- Invisible spring steel latches align refractor to housing.
- 20 gauge cold rolled steel post painted baked white enamel end caps.
- Five-year warranty on luminaire, LED boards and driver.

Specifications

- **Materials:** Chassis Parts—Die-formed code gauge cold rolled steel. End Caps—20 gauge cold rolled steel.
- **Finish:** Chassis exterior—Post painted white baked acrylic enamel. End Caps—Post painted baked white enamel. Rust preventative under-coating.
- **Refractor:** Low brightness .125 linear prismatic, extruded virgin acrylic lens.
- **Electrical:** LED boards and drivers are RoHS (Restriction of Hazardous Substances) compliant.
- **Labels:** cULus listed for damp locations.

Dimensions

