### LIGHTOLIER

## Downlighting

LyteCaster LED 3" Accent by (\$) ignify





L3RS Round Shower Light

Lightolier LyteCaster LED Accent shower light features a 3.5" luminaire height that conserves plenum space. The modular and interchangeable light engine allows for an easy future upgrade. The accent shower light is wet location listed and comes in 2 standard finish options.

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

### Complete product = Frame-in kit + Light engine + Trim Order each separately


Ordering guide: Frame-In kit Example: L3AE1								
Series	Frame type				Dimming	B		Input voltage
L3 LyteCaster 3" Accent	A AirSeal IC, New Construction, Screw AN AirSeal IC, New Construction, Nail C Remodeler Non-IC		E ELV/	Triac dimming		1 120V		
	N New Cor	nstruction N	on-IC		<b>Z10</b> 0-	10V		<b>U</b> Universal (120-277V)
Ordering guide: Ligh	Ordering guide: Light engine Example: L308830NF							
Series	Lumens 08	CRI	сст	В	eam		Opt	ion
L3 LyteCaster 3" Accent	08 800	<b>8</b> 80	<b>27</b> 2700K <b>30</b> 3000K <b>35</b> 3500K	S N F	NF Narrow flood, 44°			
		<b>9</b> 90	<b>27</b> 2700K <b>30</b> 3000K <sup>1</sup>	S N F	F Narrov	w flood, 44°	cw	CrispWhite <sup>1</sup>
Ordering guide: Rou	nd trim					Example: L	3RSA	<u> </u>
Series	Shape R	Luminai	re type	Fir	nish	Flange		•
L3 LyteCaster 3" Accent	R Round	<b>S</b> Sho	ower light			<b>W</b> White <b>A</b> Aluminur	n	•



<sup>1. 3000</sup>K and CrispWhite must be ordered together.


## Round Shower Light

#### **Assembled configuration:**




 LED Module Extruded Aluminum clear anodized finish heat sink with thermal interface material efficiently transfers heat away from LED. Includes strain relieved low voltage whip with snap interconnector for quick, tool less assembly of power connection. Tool-less assembly to trim.

3. LED Module can be installed before or after trim installation.



- 5. Reflector: Aluminum Reflector Cone.
- 6. Die Cast Aluminum Trim Flange.
- 7. Lens: Frosted Glass


Note: LED module allows for field replaceable optics. Order separately.




## Round Shower Light

#### L3AE1 & L3ANE1 new construction in IC AirSeal frame-in kits

Bottom view




Side view



#### Round trim

Side view



#### Light engine



#### Features

- 1. Housing: #23 ga. (.026") thick Galvanized steel. cULus listed for direct contact with thermal insulation (IC rated). AirSeal housing minimizes air leakage to less than 2 CFM at 1.57PSF (or 75PA), which complies with Title 24, the International Energy Conversation Code, and Washington State Energy Code (Section 502.4). This helps to reduce heat loss and condensation in ceiling. Internal access door for inspection of junction box.
- 2. Lower frame and top cover: #23 ga. (026") thick Galvanized steel. Accommodates ceilings up to 1" (25.4 mm) thick. Bottom cover provided with a .5" (6.2mm) lip and 4 embossed indicator lines to simplify alignment during installation. Housing can be locked into position on the mounting bars with locking screws.
- 3. Junction box: 2 ½" (64mm) x 5 3/8" (137mm) x 2" (51mm) #21 ga. (.032") thick galvanized steel, cULus listed 90 degrees C rated supply conductors. Rated for branch circuit wiring supplying connected luminaires (daisy chaining).
- 4. Mounting bars: #16 ga. (.059") thick galvanized steel. Bars pivot for easy attachment and wire in from below the ceiling line. Bars can extend to accommodate 16" (406mm) to 24" (610mm) O.C. joist spacing. Bars can accommodate 12" (305mm) O.C. joist spacing after slight field modification (see instruction sheet). Features integral selftapping screw phillips/square drive for attachment to wood or metal construction. Also available with integral nails (N). Attaches to T-bar ceilings without accessories Bars installed on shortest dimension of frame can be easily rotated 90° from original position.
- 5. Electronic dimming driver:
  - Class 2 electronic LED Driver, with less than 1 second start up, RoHS compliant, suitable for damp locations. 120v 50/06Hz >.9 power factor. Sound rating Class "A" (<24dB). Complies with FCC,CFR title 47 part 15 Class A for EMI/RFI. Dimmable with standard electronic low voltage (ELV) & Triac dimmers. Dims to less than or equal to 10% of relative high output. 5 year limited warranty.
- 6. Ceiling cutout: 3 3/4" diameter.

#### **Electrical**

Input voltage 120v, Input freq.: 50/60 hZ, Input current .25 amps, Input Power 12W, Power factor >.9

#### Warranty

5 year limited warranty. (visit philips.com/warranties for details)


#### Labels

cULus type IC listed suitable for wet location. AirSeal.


### Round Shower Light

#### L3NZ10V New construction non IC 0-10V frame-in kit

Bottom view




Side view



#### **Round trim**

### Side view



#### Light engine



#### **Features**

- Non-IC housing: #23 ga. (.026")
   thick Galvanized steel. cULus listed for damp locations.
   AirSeal housing minimizes air leakage to less than 2CFM at 1.57 PSF (or 75PA), complies with Title 24, International Energy Conversation Code, and Washington State Energy Code (section 502.4) Frame provided with internal access door for inspection of junction box.
- 2. Lower frame and top cover: #23 ga. (026 ") thick Galvanized steel. Accommodates ceilings up to 1" (25.4 mm) thick. Bottom cover provided with a .5" (6.2mm) lip and 4 embossed indicator lines to simplify alignment during installation. Housing can be locked into position on the mounting bars with locking screws.
- 3. Junction box: 2 ½" (64mm) x 5 3/8" (137mm) x 2" (51mm) #21 ga. (.032") thick galvanized steel, cULus listed 90 degrees C rated supply conductors. Rated for branch circuit wiring supplying connected luminaires (daisy chaining).
- 4. Mounting bars: #16 ga. (.059") thick galvanized steel. Bars pivot for easy attachment and wire in from below the ceiling line. Bars can extend to accommodate 16" (406mm) to 24" (610mm) O.C. joist spacing. Bars can accommodate 12" (305mm) O.C. joist spacing after slight field modification. (see instruction sheet) Features integral selftapping screw phillips/square drive screws for attachment to wood or metal construction. Attaches to T-bar ceilings without accessories. Bars installed on shortest dimension of frame can be easily rotated 90° from original position.
- 5. Electronic dimming driver: Class 2 electronic LED driver, RoHS compliant, suitable for damp location. 120/277v 50/06Hz >.9 power factor. MTP (module thermal protection) current cutback up to 10% to prevent overheating. Sound rating Class "A" (<24dB). Complies with FCC, CFR title 47 part 15 Class B for EM/RFI. Dimming Protocol (0-10v). Dims to less than or equal to 10% of relative high output.
- 6. Ceiling cutout: 3 3/4" diameter.

#### **Electrical**

Input voltage: 120/277, input freq.:50/60hZ. Input current .14A/.06A Input Power 16.4W, Power factor >.9

#### Warranty

5 year limited warranty. (visit philips.com/warranties for details)


#### Labels

cULus listed suitable for wet location. AirSeal. Inherently Protected. IP rated.


### Round Shower Light

#### L3CE1 Non-IC Remodeler kit

#### Bottom view




#### Side view



#### **Round trim**

#### Side view



#### Light engine



#### **Features**

- Non-IC housing: #25 ga. (025") thick Galvanized steel. Provided with 2 plates steel retaining springs that can accommodate ceiling thickness up to 1" (25.4mm) thick. Philips screw driver required to tighten springs that secure housing to ceiling.
- 2. **Junction box**: #22 ga. (.034") thick Galvanized steel. cULus ,suitable for damp locations. Junction box assembly swivels for tight plenum spaces. Snap off cover permits wiring access.
- 3. Electronic dimming driver (same as new construction): Class 2 electronic LED Driver, with less than 1 second start up, RoHS compliant, suitable for damp locations. 120v 50/06Hz >.9 power factor. Sound rating Class "A" (<24dB). Complies with FCC,CFR title 47 part 15 Class B for EMI/RFI. Dimmable with standard electronic low voltage (ELV) & Triac dimmers. Dims to less than or equal to 10% of relative high output. 5 year limited warranty.
- Trim compatibility: Not compatible with adjustable trims except for L3RG series Gimbals.
- 5. Ceiling cutout 3  $\frac{3}{4}$ " diameter.

#### **Electrical**

Input voltage 120v, Input freq.: 50/60 hZ, Input current .25 amps, Input Power 12W, Power factor >.9

#### Warranty

5 year limited warranty. (visit philips.com/warranties for details)

#### Labels

cULus listed suitable for wet location, inherently protected (IP rated).

## Round Shower Light

#### **Adjustment factors**


#### Color temperature (CCT)

2700K = 88%	
3000K = 96%	
3500K = 100%	

#### Color Rendering Index (CRI)

	80 = 100%	
	90 = 85%	
90 Crisp \	(CW) = 78% White	

#### Beam spread: Spot



Angle	Mean CP	Lumen
0	790	
5	756	69
10	663	
15	551	152
20	427	1.47
25 30	319 235	147
35	169	107
40	123	107
45	90	71
50	67	
55	52	47
60	41	
65	32	32
70 75	25 19	21
80	14	21
85	8	8
90	Ō	_

#### Frame: L3NZ10U Light engine: L308835S

Trim: L3RSA			Report no <sup>3</sup> : 543GF
Output lumens: Input Watts <sup>1</sup> : Beam angle: Spacing Criterion:	654lm 11.8 W 43° 0.7	Efficacy: CCT <sup>2</sup> : CRI:	55.4lm/W 3500 K ≥80

#### Single unit data

Height to Lighted Plane	Initial Center Beam Foot-Candles	Beam Dia. (ft)*
5'	32	3.5'
6'	22	4.2'
7'	16	4.9'
8'	12	5.6'
9'	10	6.3'


* Beam diameter is where foot-candles
drop to 50% of maximum

#### Zonal lumens & percentages

Zone	Lumens	%Luminaire
0-30	368	56.3%
0-40	475	72.7%
0-60	593	90.7%
0-90	654	100.0%

#### Beam spread: Narrow flood

#### Candela Curves



Angle	Mean CP	Lumens
0	757	
5	727	67
10	644	
15	543	150
20	428	
25	324	149
30	242	
35	176	112
40	129	
45 50	95 71	75
50 55	55	50
60	43	30
65	34	34
70	27	J-1
75	20	22
80	14	
85	8	9
90	0	
	ı	ı

#### Frame: L3NZ10U Light engine: L308835NF

Trim: L3RSA			Report no <sup>3</sup> : 532GFR
Output lumens: Input Watts <sup>1</sup> : Beam angle: Spacing Criterion:	11.8 W 44°	Efficacy: CCT <sup>2</sup> : CRI:	56.4lm/W 3500K ≥80

#### Single unit data

Height to Lighted Plane	Initial Center Beam Foot-Candles	Beam Dia. (ft)*
5'	30	3.5'
6'	21	4.2'
7'	15	4.9'
8'	12	5.6'
9'	9	6.3'

<sup>\*</sup> Beam diameter is where foot-candles drop to 50% of maximum.

Zone	Lumens	%Luminaire
0-30 0-40 0-60 0-90	366 477 601 665	55.0% 71.7% 90.3% 100.0%

Zonal lumens & percentages


<sup>1.</sup> Wattage: controlled to within ± 10%

<sup>2.</sup> Correlated Color Temperature: within specs as defined in ANSI\_NEMA\_ANSLG C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.

<sup>3.</sup> Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

## Round Shower Light

#### Beam spread: Flood



Angle	Mean CP	Lumer
0	683	
5	661	61
10	599	
15	521	144
20	426	
25	334	154
30	257	
35	191	121
40 45	142 105	02
45 50	78	82
55	60	54
60	46	] 54
65	37	36
70	29	
75	22	23
80	15	
85	9	10
90	0	
	'	'

#### Frame: L3NZ10U Light engine: L308835F

Irim: L3RSA		Report no <sup>3</sup> : 524G		
Output lumens: Input Watts¹: Beam angle: Spacing Criterion:	11.8 W 50°	Efficacy: CCT <sup>2</sup> : CRI:	57.9 lm/W 3500 K ≥80	

Single unit da	ta
Height to	Initi

Height to	Initial Center Beam	Beam	
Lighted Plane	Foot-Candles	Dia. (ft)*	
5'	27	4.0'	
6'	19	4.8'	
7'	14	5.6'	
8' 9'	14 11 8	6.4' 7.2'	

<sup>\*</sup> Beam diameter is where foot-candles drop to 50% of maximum.

Zonal lumens & percentages

0-30 359 52.5% 0-40 479 70.0% 0-60 615 89.9%	Zone	Lumens	%Luminaire
0-90 684 100.0%	0-40	479	70.0%

- 2. Correlated Color Temperature: within specs as defined in ANSI\_NEMA\_ANSLG C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.
- 3. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

#### **Electrical Specifications**

Frame-in kit	Input volts	Input freq.	Input current	LED drive current	Input power	LED power	THD factor	Power factor
L3AE1	120V	50/60Hz	.090 A	260 ma	10.64 W	8.76 W	<20%	> .9
L3ANE1	120V	50/60Hz	.090 A	260 ma	10.64 W	8.76 W	<20%	> .9
L3CE1	120V	50/60Hz	.090 A	260 ma	10.64 W	8.76 W	<20%	> .9
1.20171011	120V	50/60Hz	.102 A	260 ma	11.8 W	9.74 W	<10%	>.8
L3NZ10U	277V	50/60Hz	.047 A	260 ma	11.8 W	8.90 W	<10%	> .8



<sup>1.</sup> Wattage: controlled to within ± 10%