



Alkco's **CareWell LED** eco bed light is a valuable solution for healthcare spaces. This fixture utilizes dual lamp compartments to deliver illumination without direct glare. The CareWell LED eco bed light is multi-functional and can apply for both headwall and foot-wall installation with compartment shielding options.

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

#### Ordering guide

Example: **ALE50L8304DSUNVDIM2-HDSR**

Family	Lumens	Color	Length	Lens	Voltage	Dimming	Options
ALE CareWell LED eco bed light	<b>50L</b> 5000 nominal delivered lumens, 2500 ambient, 2500 reading <b>75L</b> 7500 nominal delivered lumens, 5000 ambient, 2500 reading	<b>830</b> 80CRI, 3000K <b>835</b> 80CRI, 3500K <b>840</b> 80CRI, 4000K <b>850</b> 80CRI, 5000K	4 4'	DS Diffuse	120 UNV 120V Universal Voltage 120-277	<b>DIM1U<sup>3</sup></b> 0-10V dimming, up compartment <b>DIM2</b> 0-10V dimming, up and down compartment	<b>HDSL<sup>1</sup></b> 4-position pull cord switch for sequential control of indirect and direct lamp compartments, left end (as facing luminaire) <b>HDSR<sup>1</sup></b> 4-position pull cord switch for sequential control of indirect and direct lamp compartments, right end (as facing luminaire) <b>HDSM<sup>1</sup></b> 4-position pull cord switch for sequential control of indirect and direct lamp compartments, middle (as facing luminaire) <b>PCSL<sup>1</sup></b> Pull cord switch for on-off control of direct light compartment, left end (as facing luminaire) <b>PCSR<sup>1</sup></b> Pull cord switch for on-off control of direct light compartment, right end (as facing luminaire) <b>PCSM<sup>1</sup></b> Pull cord switch for on-off control of direct light compartment, middle (as facing luminaire) <b>CO/L<sup>1</sup></b> Grounded convenient outlet 120V only, left end (as facing luminaire) <b>CO/R<sup>1</sup></b> Grounded convenient outlet 120V only, right end (as facing luminaire) <b>LVC<sup>2</sup></b> Low voltage controller, Curbell #LVC-060 <b>EMLED NL</b> Integral emergency battery pack LED Night Light, 3.5W, 2700K
<b>Accessories (order separately)</b> <div> <input type="checkbox"/> </div> <b>PSC</b> Pillow switch control (control with cord and wall plate)							

# ALE CareWell eco LED bed light

5000 or 7500 lumens

## Features


- Installation is completed in three simple steps.
- Optional 4-position pull cord switch provides sequential control of dual lamp compartments.
- Long life LEDs provide 50,000 hours of rated life (L70).
- Minimum 80 CRI LEDs.

## Specifications

- **Construction:** Back plate is formed from 18 gauge galvanized steel and shroud assembly is formed from 20 gauge cold rolled steel.
- **Finish:** Shroud assembly is painted after fabrication with polyester powder coat paint.
- **Lens:** Smooth frosted acrylic lens on both sides.
- **Light Sources:** CareWell eco is available with 3000, 3500, or 4000K CCT LEDs
- **Electrical:** Class 2 LED driver is provided for each lamp compartment.
- **Wooden Casework:** Provided by others. Metal fixture only.
- **Five year limited luminaire warranty:** Includes LED boards and driver (emergency driver and batteries have a three year warranty in models so equipped). Visit [www.philips.com/warranties](http://www.philips.com/warranties) for complete warranty information.
- **Switching:** As standard the fixture is wired for separate switching of the indirect and direct lamp compartments with switches provided by others. An optional 4-position pull cord switch (HDS) can be selected that provides sequential control of the two lamp compartments, and an optional single pull cord switch (PCS) is available for on-off control of direct lamp compartment. The pull switch is supplied with a plastic pull cord that is latex-free, stain resistant, and easy to clean with standard disinfectant. There is also an optional low voltage controller (LVC option) that is compatible with industry standard bed control systems (by others) and can be field wired for either separate or sequential switching of indirect and direct lamp compartments.
- **Installation:** Installation is completed in three easy steps. The back plate is mounted over the junction box and secured to the wall studs or with wall anchors. The shroud assembly attaches to the back plate with two screws. Decorative shroud provided by others.
- **Listing:** cETLus listed to UL and CSA standards, suitable for damp locations

## General Notes

- \* All options are factory installed
- \* All accessories are field installed
- \* Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



# SSTR24 SurgiCare LED luminaire 2x4

## Surgical suite luminaire

### Photometry

#### 4' CareWell eco, 7500 nominal lumens, 3000K, Downlight Only

<div>Catalog No.</div> <div>Test No.</div> <div>Source</div> <div>Color Temp.</div> <div>Lumens</div> <div>Input Watts</div> <div>Direction</div> <div>Comp Yearly Energy Cost at \$0.08/KWh = \$3.29</div> <div>The photometric results were obtained in the laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</div> <div>Photometric values based on test performed in compliance with LM-79.</div>	<div>ALE75L8304DSUNV</div> <div>34669</div> <div>LED</div> <div>3000K</div> <div>2455</div> <div>34</div> <div>Downlight</div> <div></div>	<div>Candlepower</div> <table><tr><th>Angle</th><th>End</th><th>45</th><th>Cross</th></tr><tr><td>0</td><td>934</td><td>934</td><td>934</td></tr><tr><td>5</td><td>921</td><td>929</td><td>937</td></tr><tr><td>15</td><td>884</td><td>892</td><td>892</td></tr><tr><td>25</td><td>810</td><td>808</td><td>801</td></tr><tr><td>35</td><td>705</td><td>697</td><td>683</td></tr><tr><td>45</td><td>581</td><td>569</td><td>556</td></tr><tr><td>55</td><td>444</td><td>434</td><td>418</td></tr><tr><td>65</td><td>300</td><td>291</td><td>278</td></tr><tr><td>75</td><td>155</td><td>149</td><td>143</td></tr><tr><td>85</td><td>33</td><td>33</td><td>33</td></tr></table>	Angle	End	45	Cross	0	934	934	934	5	921	929	937	15	884	892	892	25	810	808	801	35	705	697	683	45	581	569	556	55	444	434	418	65	300	291	278	75	155	149	143	85	33	33	33	<div>Light Distribution</div> <table><tr><th>Degrees</th><th>Lumens</th><th>% Luminaire</th></tr><tr><td>(0-30)</td><td>712</td><td>29.0</td></tr><tr><td>(0-40)</td><td>1147</td><td>46.7</td></tr><tr><td>(0-60)</td><td>1972</td><td>80.3</td></tr><tr><td>(0-90)</td><td>2456</td><td>100.0</td></tr></table>	Degrees	Lumens	% Luminaire	(0-30)	712	29.0	(0-40)	1147	46.7	(0-60)	1972	80.3	(0-90)	2456	100.0	<div>Average Luminance</div> <div>(Cd/sq. meter)</div> <table><tr><th>Zone</th><th>End</th><th>45</th><th>Cross</th></tr><tr><td>45</td><td>7611</td><td>7456</td><td>7274</td></tr><tr><td>55</td><td>7172</td><td>7011</td><td>6740</td></tr><tr><td>65</td><td>6568</td><td>6373</td><td>6095</td></tr><tr><td>75</td><td>5531</td><td>5334</td><td>5109</td></tr><tr><td>85</td><td>3516</td><td>3474</td><td>3453</td></tr></table>	Zone	End	45	Cross	45	7611	7456	7274	55	7172	7011	6740	65	6568	6373	6095	75	5531	5334	5109	85	3516	3474	3453																																											
Angle	End	45	Cross																																																																																																																															
0	934	934	934																																																																																																																															
5	921	929	937																																																																																																																															
15	884	892	892																																																																																																																															
25	810	808	801																																																																																																																															
35	705	697	683																																																																																																																															
45	581	569	556																																																																																																																															
55	444	434	418																																																																																																																															
65	300	291	278																																																																																																																															
75	155	149	143																																																																																																																															
85	33	33	33																																																																																																																															
Degrees	Lumens	% Luminaire																																																																																																																																
(0-30)	712	29.0																																																																																																																																
(0-40)	1147	46.7																																																																																																																																
(0-60)	1972	80.3																																																																																																																																
(0-90)	2456	100.0																																																																																																																																
Zone	End	45	Cross																																																																																																																															
45	7611	7456	7274																																																																																																																															
55	7172	7011	6740																																																																																																																															
65	6568	6373	6095																																																																																																																															
75	5531	5334	5109																																																																																																																															
85	3516	3474	3453																																																																																																																															
<div>Coefficients of Utilization</div> <div>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</div> <table><tr><th>Ceil</th><th colspan="3">80</th><th colspan="3">70</th><th colspan="2">50</th></tr><tr><td>Wall</td><td>70</td><td>50</td><td>30</td><td>70</td><td>50</td><td>30</td><td>50</td><td>30</td></tr><tr><td>RCR</td><td colspan="3"></td><td colspan="3"></td><td colspan="2"></td></tr><tr><td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td></tr><tr><td>1</td><td>109</td><td>104</td><td>100</td><td>106</td><td>102</td><td>97</td><td>97</td><td>94</td></tr><tr><td>2</td><td>98</td><td>91</td><td>84</td><td>96</td><td>89</td><td>82</td><td>85</td><td>81</td></tr><tr><td>3</td><td>91</td><td>80</td><td>71</td><td>88</td><td>79</td><td>70</td><td>76</td><td>68</td></tr><tr><td>4</td><td>82</td><td>70</td><td>63</td><td>81</td><td>69</td><td>61</td><td>67</td><td>59</td></tr><tr><td>5</td><td>77</td><td>64</td><td>55</td><td>73</td><td>63</td><td>54</td><td>60</td><td>53</td></tr><tr><td>6</td><td>70</td><td>57</td><td>48</td><td>68</td><td>56</td><td>47</td><td>55</td><td>46</td></tr><tr><td>7</td><td>66</td><td>52</td><td>44</td><td>64</td><td>51</td><td>42</td><td>50</td><td>41</td></tr><tr><td>8</td><td>60</td><td>47</td><td>39</td><td>59</td><td>46</td><td>39</td><td>46</td><td>38</td></tr><tr><td>9</td><td>56</td><td>44</td><td>35</td><td>56</td><td>42</td><td>34</td><td>41</td><td>34</td></tr><tr><td>10</td><td>54</td><td>40</td><td>33</td><td>52</td><td>40</td><td>32</td><td>39</td><td>32</td></tr></table>					Ceil	80			70			50		Wall	70	50	30	70	50	30	50	30	RCR									0	118	118	118	115	115	115	111	111	1	109	104	100	106	102	97	97	94	2	98	91	84	96	89	82	85	81	3	91	80	71	88	79	70	76	68	4	82	70	63	81	69	61	67	59	5	77	64	55	73	63	54	60	53	6	70	57	48	68	56	47	55	46	7	66	52	44	64	51	42	50	41	8	60	47	39	59	46	39	46	38	9	56	44	35	56	42	34	41	34	10	54	40	33	52	40	32	39	32
Ceil	80			70			50																																																																																																																											
Wall	70	50	30	70	50	30	50	30																																																																																																																										
RCR																																																																																																																																		
0	118	118	118	115	115	115	111	111																																																																																																																										
1	109	104	100	106	102	97	97	94																																																																																																																										
2	98	91	84	96	89	82	85	81																																																																																																																										
3	91	80	71	88	79	70	76	68																																																																																																																										
4	82	70	63	81	69	61	67	59																																																																																																																										
5	77	64	55	73	63	54	60	53																																																																																																																										
6	70	57	48	68	56	47	55	46																																																																																																																										
7	66	52	44	64	51	42	50	41																																																																																																																										
8	60	47	39	59	46	39	46	38																																																																																																																										
9	56	44	35	56	42	34	41	34																																																																																																																										
10	54	40	33	52	40	32	39	32																																																																																																																										

#### 4' CareWell eco, 7500 nominal lumens, 3000K, Uplight Only

<b>Catalog No.</b>	ALE75L8304DSUNV	<b>Candlepower</b>				<b>Light Distribution</b>			
<b>Test No.</b>	34671	<b>Angle</b>	<b>End</b>	<b>45</b>	<b>Cross</b>	<b>Degrees</b>	<b>Lumens</b>	<b>% Luminaire</b>	
<b>Source</b>	LED	85	0	0	0	(90-120)	924	18.7	
<b>Color Temp.</b>	3000K	95	53	47	54	(90-130)	1697	34.4	
<b>Lumens</b>	4933	105	290	279	272	(90-150)	3472	70.4	
<b>Input Watts</b>	66	115	588	569	551	(90-180)	4934	100.0	
<b>Direction</b>	Uplight	125	887	863	840	(0-180)	4935	100.0	
		135	1174	1150	1125				
		145	1438	1417	1394				
		155	1665	1653	1638				
		165	1831	1834	1829				
		175	1920	1930	1929				
<b>Comp Yearly Energy Cost at \$0.08/KWh = \$3.24</b>									
The photometric results were obtained in the laboratory which is NVLAP accredited by the National Institute of Standards and Technology.									
Photometric values based on test performed in compliance with LM-79.									
		<b>Coefficients of Utilization</b>							
		EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)							
		<b>Ceiling</b>	<b>80</b>			<b>70</b>			<b>50</b>
		<b>Wall</b>	70	50	30	70	50	30	50 30
		<b>RCR</b>							
		0	118	118	118	115	115	115	111 111
		1	109	104	100	106	102	97	97 94
		2	98	91	84	96	89	82	85 81
		3	91	80	71	88	79	70	76 68
		4	82	70	63	81	69	61	67 59
		5	77	64	55	73	63	54	60 53
		6	70	57	48	68	56	47	55 46
		7	66	52	44	64	51	42	50 41
		8	60	47	39	59	46	39	46 38
		9	56	44	35	56	42	34	41 34
		10	54	40	33	52	40	32	39 32

### Buy American Act of 1933 (BAA):

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit [www.signify.com/baa](http://www.signify.com/baa) to view a current list of BAA-compliant products to confirm this product's current compliance.

