

Made from tapered 6" to 4" (152 to 102 mm) round aluminum shaft welded to a cast-aluminum anchor plate. After tapering and welding, the entire shaft assembly is heat-treated to T6 temper. A 3" by 5" (76 by 127 mm) maintenance opening is complete with cover and copper ground lug

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

example: RTAF800-F-12-LS-BE2TX

Pole Family	Wall Thickness	Nominal Height	Options	Finish
RTAF800				
RTAF800	F .125"	12 12'	LS Provision for loudspeaker outlet	BE2TX Midnight Blue Textured
		14 14'	PH7 Button-type photoelectric cell (specify operating voltage)	BE6TX Ocean Blue Textured
		16 16'	DR Duplex receptacle (120V line voltage only)	BE8TX Royal Blue Textured
		18 18'	GFI DR with common ground fault interrupter (120V line voltage only)	BG2TX Sandstone Gold Textured
	V 0.25"	12 12'	BA Banner arm	BKTX Black Textured
		14 14'	PS Plant support	BRTX Bronze Textured
		16 16'	MPL Mid-pole luminaire	GN4TX Blue Green Textured
		18 18'		GN6TX Forest Green Textured
				GN8TX Dark Forest Green Textured
				GNTX Green Textured
				GY3TX Medium Grey Textured
				RD2TX Burgundy Textured
			RD4TX Scarlet Textured	
			WHTX White Textured	
			GR Gray Sandtex	
			NP Natural Alum.	
			TG Hammer-tone	
			TS Hammer-tone Silver	

Note: The recommended method for calculating EPA (Effective Projected Area) is in accordance with AASHTO 2001 standards: for three seconds, the pole is tested in wind gusts equivalent to the strongest winds on record over the past 50 years, and with a 50 pound load (22.7 kg) placed at 1 foot (305 mm) above its center.

Outdoor Poles and Brackets

RTAF800 – Aluminum Fluted Pole

Pole Data

Pole Family	Catalog Number	Nominal Height (ft)	Nominal Height (m)	Tenon Section (in)	Tenon Section (mm)	Wall Thickness (in)	Wall Thickness (mm)	Weight (lbs)	Weight (kg)	EPA Rating 90 MPH (sq. ft.)	EPA Rating 110 MPH (sq. ft.)	EPA Rating 120 MPH (sq. ft.)	EPA Rating 150 MPH (sq. ft.)	Anchor Bolts (in)	Anchor Bolts (mm)
RTAF800	RTAF800F-12	12	3.66	4	102	0.125	3.2	58	26	17.15	10.97	8.99	5.26	1-36	25-914
RTAF800	RTAF800V-12	12	3.66	4	102	0.25	4.8	83	38	30	24.26	20.2	12.47	1-36	25-914
RTAF800	RTAF800F-14	14	4.27	4	102	0.125	3.2	62	28	14.17	8.81	7.11	3.97	1-36	25-914
RTAF800	RTAF800V-14	14	4.27	4	102	0.25	6.4	91	41	30	20.34	16.84	10.22	1-36	25-914
RTAF800	RTAF800F-16	16	4.88	4	102	0.125	3.2	67	30	11.88	7.11	5.65	2.92	1-36	25-914
RTAF800	RTAF800V-16	16	4.88	4	102	0.25	6.4	100	45	27.06	17.33	14.26	8.46	1-36	25-914
RTAF800	RTAF800F-18	18	5.49	4	102	0.125	3.2	71	32	9.77	5.55	4.29	1.98	1-36	25-914
RTAF800	RTAF800V-18	18	5.49	4	102	0.25	6.4	109	49	23.03	14.52	11.82	6.81	1-36	25-914

Specifications

Base cover

Decorative base cover made from two cast-aluminum pieces fastened together with stainless steel hardware around the base of the pole. There is no door in the base cover to access the maintenance opening.

Finish

Color to be in accordance with the AAMA 2603 standard. Application of polyester powder coat paint (4 mils/100 microns) with \pm 1 mils/24 microns of tolerance. The Thermosetting resins provides a discoloration resistant finish in accordance with the ASTM D2244 standard, as well as luster retention in keeping with the ASTM D523 standard and humidity proof in accordance with the ASTM D2247 standard.

Outdoor Poles and Brackets

RTAF800 – Aluminum Fluted Pole

Dimensions

