

Read and understand these instructions before installing luminaire.


This luminaire is intended for installation in accordance with the National Electrical Code and local regulations. To assure full compliance with local codes and regulations, check with your local electrical inspector before installation. To prevent electrical shock, turn off electricity at fuse box before proceeding. Allow fixture to cool before handling.

Retain these instructions for maintenance reference.

INSTRUCTIONS FOR SURFACE MOUNTING OF LYTESPAN® MONOPOINT FOR USE WITH FIXTURES SPECIFIED FOR USE WITH LYTESPAN® TRACK

CAUTION

- **THIS MONOPOINT IS RATED FOR A MAX 660W 120V 60HZ AC CIRCUIT.**
- **DO NOT INSTALL THIS MONOPOINT IN WET OR DAMP LOCATIONS.**
- **DO NOT INSTALL THE MONOPOINT LESS THAN 5 FEET ABOVE THE FLOOR.**
- **DO NOT INSTALL ANY FIXTURE ASSEMBLY CLOSER THAN 6 INCHES FROM ANY CURTAIN OR SIMILAR COMBUSTIBLE.**
- **TO PREVENT ELECTRICAL SHOCK, TURN OFF POWER AT FUSE BOX BEFORE INSTALLING MONOPOINT.**
- **INSTRUCTIONS FOR GROUNDING PER INSTRUCTION SHEET OF THE FEED-IN KIT MUST BE FOLLOWED. FAILURE TO DO SO MAY RESULT IN A HAZARDOUS CONDITION.**
- **USE ONLY #12 OR 14 GA. AWG SOLID WIRE (NOT STRANDED WIRE) RATED FOR MIN. 90°C FOR SUPPLY TO MONOPOINT.**
- **DO NOT ATTEMPT TO ENERGIZE ANYTHING OTHER THAN TRACK LIGHTING FIXTURES ON THE MONOPOINT. TO REDUCE THE RISK OF FIRE AND ELECTRICAL SHOCK, DO NOT ATTEMPT TO CONNECT POWER TOOLS, EXTENSION CORDS, APPLIANCES AND THE LIKE TO THE MONOPOINT.**



INSTRUCTIONS FOR SURFACE MOUNTING OF MONOPOINT:

1. Install 4" octagonal or round OUTLET BOX (by others).
2. Make wiring connections:
Black fixture lead to black supply lead;
white fixture lead to white supply lead.
Green or uninsulated wire is a GROUND WIRE and must be connected to a grounding TERMINAL or a GROUND WIRE in the OUTLET BOX. Use wire nuts (local hardware item). (Fig. 1)
3. Place wire connections into OUTLET BOX and fasten MOUNTING BRACKET as shown in Fig. 2.
4. Fasten CANOPY to MOUNTING BRACKET with SCREWS (Fig. 2).

