

CHLORIDE

by  Signify

Exit/Emergency

CUR series

Recessed lay-in unit
Chicago Approved



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Example: CUR6L27W

Catalog Number	Battery	Voltage	Wattage	Housing Color
CUR6L27W	Lead Acid	6	27	White
CUR6L50W	Lead Acid	6	50	White
CUR12L50W	Lead Acid	12	50	White
CUR6L27B	Lead Acid	6	27	Black
CUR6L50B	Lead Acid	6	50	Black
CUR12L50B	Lead Acid	12	50	Black

Operation

Model No.	Supply Voltage	Input Watts	Max. Amps
CUR6L27	120/277	11W	0.11A/0.04A
CUR6L50	120/277	18W	0.17A/0.010A
CUR12L50	120/277	26W	0.25A/0.10A

codes and standards

- UL listed to standard 924
- NFPA 101 (Life Safety Code)
- NFPA 70 (National Electric Code)
- OSHA standards
- City of Chicago codes
- UL listed for damp locations 68°F (20°C) to 122°F (50°C).

construction

- Housing is constructed of durable 20-gauge steel housing.
- Housing color is standard neutral white finish, black finish is optional.

installation

- Unit is for ceiling installation. Mount the unit across the two foot T-bar span. Chain hook holes are provided on the ends of the enclosure.

electronics

- Charge rate/power "ON" LED indicator light and push to test switch for mandated code compliance testing.
- Low Voltage Battery Disconnect protects the battery from being severely damaged by deep discharge during prolonged power failures.
- Emergency units feature a fully automatic charger designed to recharge the battery within 24 hours.
- 120/277V dual input.

lamps

- Unit has two 6V, 12 Watt or two 12V, 12 Watt halogen lamp heads.

battery

- Maintenance-free sealed lead acid battery.
- Provides a minimum of 90 minutes emergency illumination while in the emergency mode.

warranty

- Five year warranty. (Lamps not included.)



CUR Recessed lay-in unit, Chicago Approved

27W and 50W

dimensions

