



Ordering guide

Example: HFP910 P3 A N

Product Code	Post Diameter	Finish	Arm Accessory
HFP910	P3	A	N
HFP910 Single	P3 ¹ 3" Post Mount	A Black	N None

1. A Tenon to be 3" O.D. x 9" Tall.
2. Order 2 3/8" O.D. Horizontal Arm Mount Adaptor (TFHAM) separately.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications

Housing

6063-T6 Extruded aluminum. PolyTech custom blended polyethylene.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. Polymer has molded-in color and texture for color fastness and durability. For larger projects where a custom color is required, contact the factory for more information.

Certifications

Manufactured to ISO 9001:2008 Standards.

Warranty

Three-year limited warranty.

Tenon/Top	EPA	
3"x9"	2.75 sq. ft.	
Height	Length	Overall Length
41 4/5" (106 cm)	70" (178 cm)	83 3/4" (213 cm)

