

## Ordering guide

Example: HFP420 P4 A N

Product Code	Post Diameter	Finish	Arm Accessory
<b>HFP420</b>	<b>P4</b>		<b>N</b>
HFP420 Twin	P4 4" Post Mount	<b>A</b> Black <b>B</b> White <b>G</b> Verde <b>H</b> Bronze <b>I</b> Gray <b>J</b> Green	N None

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## Specifications

### Housing

6063-T6 Extruded aluminum.


### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

### Warranty

Three-year limited warranty.

Height	Length	EPA
32 1/4" (82 cm)	45 3/4" (116 cm)	1.60 sq. ft.



### Note

Slip fits onto 4" O.D. x 4" long tenon or post top.