

# ColorGraze MX4 Powercore

Linear exterior LED wall grazing luminaires with RGBW or RGBA light

Date: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Firm Name: \_\_\_\_\_  
 Project: \_\_\_\_\_

ColorGraze MX4 Powercore is a high-performance, exterior linear luminaire designed to highlight architectural features ranging from surface textures and molding details to archways and windows. Graze RGBW luminaires add a separate white LED creating better-quality whites compared to RGB. Graze RGBA luminaires add a separate amber LED which expands the available range of colors to include warmer tones such as rich gold, yellow, and orange shades. Multiple luminaire lengths, and beam angles support a large range of façade or surface illumination applications. Low-profile housing, connectorized cabling, a universal power input range, and direct line voltage operation make Graze luminaires easy to install and operate.

- Tailor light output to specific applications—Available in four standard lengths (1 ft, 2 ft, 3 ft, and 4 ft), and five standard 9° x 9°, 10° x 60°, 15° x 30°, 30° x 60°, and 60° x 30° beam angles.
- Flexible integration—Graze's ultra-low profile lets it fit discretely into almost any layout, from simple to elaborate.



[Product page](#)

Beam Angle	9° x 9°, 10° x 60°, 15° x 30°, 30° x 60°, 60° x 30°
Lumens per foot*	543 to 655
Efficacy†	30.1 to 36.3
LED Channels	Red/Green/Blue/Amber, Red/Green/Blue/White

Input Voltage	100 to 277 VAC, auto-ranging, 50/60 Hz
Housing Material	Extruded anodized aluminium
Approbations	UL/cUL, FCC Class A, CE, PSE, CQC, C-Tick
Environment	Dry/Damp/Wet Location, IP66
Applications	Wall Grazing, Wall Washing

## RGBA Specification Sheets

PDF Download	Beam Angle	Lumens*	Efficacy†	Power	Weight	Item Number	12 NC
<a href="#">RGBA, 9° x 9° Beam Angle, 305 mm (1 ft)</a>	9° x 9°	566	31.2	18.5 W	1 kg (2.1 lb)	423-000002-00	910503704702
<a href="#">RGBA, 9° x 9° Beam Angle, 610 mm (2 ft)</a>	9° x 9°	1,132	31.2	37 W	2.1 kg (4.6 lb)	423-000002-05	910503704707
<a href="#">RGBA, 9° x 9° Beam Angle, 914 mm (3 ft)</a>	9° x 9°	1,698	31.2	55.5 W	3.2 kg (7.1 lb)	423-000002-10	910503704712
<a href="#">RGBA, 9° x 9° Beam Angle, 1219 mm (4 ft)</a>	9° x 9°	2,264	31.2	74 W	4.2 kg (9.3 lb)	423-000002-15	910503704717
<a href="#">RGBA, 10° x 60° Beam Angle, 305 mm (1 ft)</a>	10° x 60°	543	30.1	18.5 W	1 kg (2.1 lb)	423-000002-01	910503704703
<a href="#">RGBA, 10° x 60° Beam Angle, 610 mm (2 ft)</a>	10° x 60°	1,086	30.1	37 W	2.1 kg (4.6 lb)	423-000002-06	910503704708
<a href="#">RGBA, 10° x 60° Beam Angle, 914 mm (3 ft)</a>	10° x 60°	1,629	30.1	55.5 W	3.2 kg (7.1 lb)	423-000002-11	910503704713
<a href="#">RGBA, 10° x 60° Beam Angle, 1219 mm (4 ft)</a>	10° x 60°	2,172	30.1	74 W	4.2 kg (9.3 lb)	423-000002-16	910503704718



## RGBA Specification Sheets (cont.)

PDF Download	Beam Angle	Lumens*	Efficacy <sup>†</sup>	Power	Weight	Item Number	12 NC
<a href="#">RGBA, 15° x 30° Beam Angle, 305 mm (1 ft)</a>	15° x 30°	555	30.9	18.5 W	1 kg (2.1 lb)	423-000002-02	910503704704
<a href="#">RGBA, 15° x 30° Beam Angle, 610 mm (2 ft)</a>	15° x 30°	1,110	30.9	37 W	2.1 kg (4.6 lb)	423-000002-07	910503704709
<a href="#">RGBA, 15° x 30° Beam Angle, 914 mm (3 ft)</a>	15° x 30°	1,665	30.9	55.5 W	3.2 kg (7.1 lb)	423-000002-12	910503704714
<a href="#">RGBA, 15° x 30° Beam Angle, 1219 mm (4 ft)</a>	15° x 30°	2,220	30.9	74 W	4.2 kg (9.3 lb)	423-000002-17	910503704719
<a href="#">RGBA, 30° x 60° Beam Angle, 305 mm (1 ft)</a>	30° x 60°	547	30.1	18.5 W	1 kg (2.1 lb)	423-000002-03	910503704705
<a href="#">RGBA, 30° x 60° Beam Angle, 610 mm (2 ft)</a>	30° x 60°	1,094	30.1	37 W	2.1 kg (4.6 lb)	423-000002-08	910503704710
<a href="#">RGBA, 30° x 60° Beam Angle, 914 mm (3 ft)</a>	30° x 60°	1,641	30.1	55.5 W	3.2 kg (7.1 lb)	423-000002-13	910503704715
<a href="#">RGBA, 30° x 60° Beam Angle, 1219 mm (4 ft)</a>	30° x 60°	2,188	30.1	74 W	4.2 kg (9.3 lb)	423-000002-18	910503704720
<a href="#">RGBA, 60° x 30° Beam Angle, 305 mm (1 ft)</a>	60° x 30°	561	31	18.5 W	1 kg (2.1 lb)	423-000002-04	910503704706
<a href="#">RGBA, 60° x 30° Beam Angle, 610 mm (2 ft)</a>	60° x 30°	1,122	31	37 W	2.1 kg (4.6 lb)	423-000002-09	910503704711
<a href="#">RGBA, 60° x 30° Beam Angle, 914 mm (3 ft)</a>	60° x 30°	1,683	31	55.5 W	3.2 kg (7.1 lb)	423-000002-14	910503704716
<a href="#">RGBA, 60° x 30° Beam Angle, 1219 mm (4 ft)</a>	60° x 30°	2,244	31	74 W	4.2 kg (9.3 lb)	423-000002-19	910503704721

## RGBW Specification Sheets

PDF Download	Beam Angle	Lumens*	Efficacy <sup>†</sup>	Power	Weight	Item Number	12 NC
<a href="#">RGBW, 9° x 9° Beam Angle, 305 mm (1 ft)</a>	9° x 9°	655	36.3	18.5 W	1 kg (2.1 lb)	423-000001-00	910503704681
<a href="#">RGBW, 9° x 9° Beam Angle, 610 mm (2 ft)</a>	9° x 9°	1,310	36.3	37 W	2.1 kg (4.6 lb)	423-000001-05	910503704686
<a href="#">RGBW, 9° x 9° Beam Angle, 914 mm (3 ft)</a>	9° x 9°	1,965	36.3	55.5 W	3.2 kg (7.1 lb)	423-000001-10	910503704691
<a href="#">RGBW, 9° x 9° Beam Angle, 1219 mm (4 ft)</a>	9° x 9°	2,620	36.3	74 W	4.2 kg (9.3 lb)	423-000001-15	910503704696
<a href="#">RGBW, 10° x 60° Beam Angle, 305 mm (1 ft)</a>	10° x 60°	619	34.9	18.5 W	1 kg (2.1 lb)	423-000001-01	910503704682
<a href="#">RGBW, 10° x 60° Beam Angle, 610 mm (2 ft)</a>	10° x 60°	1,238	34.9	37 W	2.1 kg (4.6 lb)	423-000001-06	910503704687
<a href="#">RGBW, 10° x 60° Beam Angle, 914 mm (3 ft)</a>	10° x 60°	1,857	34.9	55.5 W	3.2 kg (7.1 lb)	423-000001-11	910503704692
<a href="#">RGBW, 10° x 60° Beam Angle, 1219 mm (4 ft)</a>	10° x 60°	2,476	34.9	74 W	4.2 kg (9.3 lb)	423-000001-16	910503704697
<a href="#">RGBW, 15° x 30° Beam Angle, 305 mm (1 ft)</a>	15° x 30°	622	34.4	18.5 W	1 kg (2.1 lb)	423-000001-02	910503704683
<a href="#">RGBW, 15° x 30° Beam Angle, 610 mm (2 ft)</a>	15° x 30°	1,244	34.4	37 W	2.1 kg (4.6 lb)	423-000001-07	910503704688
<a href="#">RGBW, 15° x 30° Beam Angle, 914 mm (3 ft)</a>	15° x 30°	1,866	34.4	55.5 W	3.2 kg (7.1 lb)	423-000001-12	910503704693
<a href="#">RGBW, 15° x 30° Beam Angle, 1219 mm (4 ft)</a>	15° x 30°	2,488	34.4	74 W	4.2 kg (9.3 lb)	423-000001-17	910503704698
<a href="#">RGBW, 30° x 60° Beam Angle, 305 mm (1 ft)</a>	30° x 60°	628	34.9	18.5 W	1 kg (2.1 lb)	423-000001-03	910503704684
<a href="#">RGBW, 30° x 60° Beam Angle, 610 mm (2 ft)</a>	30° x 60°	1,256	34.9	37 W	2.1 kg (4.6 lb)	423-000001-08	910503704689
<a href="#">RGBW, 30° x 60° Beam Angle, 914 mm (3 ft)</a>	30° x 60°	1,884	34.9	55.5 W	3.2 kg (7.1 lb)	423-000001-13	910503704694
<a href="#">RGBW, 30° x 60° Beam Angle, 1219 mm (4 ft)</a>	30° x 60°	2,512	34.9	74 W	4.2 kg (9.3 lb)	423-000001-18	910503704699
<a href="#">RGBW, 60° x 30° Beam Angle, 305 mm (1 ft)</a>	60° x 30°	634	34.8	18.5 W	1 kg (2.1 lb)	423-000001-04	910503704685
<a href="#">RGBW, 60° x 30° Beam Angle, 610 mm (2 ft)</a>	60° x 30°	1,268	34.8	37 W	2.1 kg (4.6 lb)	423-000001-09	910503704690
<a href="#">RGBW, 60° x 30° Beam Angle, 914 mm (3 ft)</a>	60° x 30°	1,902	34.8	55.5 W	3.2 kg (7.1 lb)	423-000001-14	910503704695
<a href="#">RGBW, 60° x 30° Beam Angle, 1219 mm (4 ft)</a>	60° x 30°	2,536	34.8	74 W	4.2 kg (9.3 lb)	423-000001-19	910503704701

\* 305 mm (1 ft) lumen output measurements comply with IES LM-79-08 testing procedures. 610 mm (2 ft), 914 mm (3 ft), and 1219 mm (4 ft) measurements are estimated based on the 305

<sup>†</sup> Efficacy measurements are estimated based on the 305 mm (1 ft) measurements.



© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics  
www.colorkinetics.com/ls/rgb/colorgraze-mx4-powercore/