

Outdoor

Poles and Brackets

RTA61 Traditional Aluminum Pole

Made from a 12 flute, mandrel-formed, aluminum tapered shaft 5" round (127 mm) welded to a 8-5/8" round (219 mm) extruded aluminum pole base which them is welded to both the top and bottom of a cast aluminum anchor plate. After tapering, forming and welding, the entire shaft assembly is heat-treated to T6 temper. A 4-1/2" by 10" (114 by 254 mm) maintenance opening is complete with cover and copper ground lug.

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notos	

Ordering guide

example: RTA61-F-10-LS-BE2TX

Pole Family RTA61	Wall Thickness	Nominal Height	Options	Finish
RTA61	F 0.125"	10 10'	LS Provision for loudspeaker outlet	BE2TX Midnight Blue Textured
		11 11'	PH7 Button-type photoelectric cell (specify operating voltage)	BE6TX Ocean Blue Textured
		12 12'	DR Duplex receptacle (120V line voltage. only)	BE8TX Royal Blue Textured
		13 13'	GFI DR with common ground fault interrupter (120V line voltage only)	BG2TX Sandstone Gold Textured
		14 14'	BA Banner arm	BKTX Black Textured
		15 15'	PS Plant support	BRTX Bronze Textured
	V 0.25"	10 10'	MPL Mid-pole luminaire	GN4TX Blue Green Textured
		11 11'		GN6TX Forest Green Textured
		12 12'		GN8TX Dark Forest Green Textured
		13 13'		GNTX Green Textured
		14 14'		GY3TX Medium Grey Textured
		15 15'		RD2TX Burgundy Textured
				RD4TX Scarlet Textured
				WHTX White Textured
				GR Gray Sandtex
				NP Natural Alum.
				TG Hammer-tone
				TS Hammer-tone Silver

Note: The recommended method for calculating EPA (Effective Projected Area) is in accordance with AASHTO 2001 standards: for three seconds, the pole is tested in wind gusts equivalent to the strongest winds on record over the past 50 years, and with a 50 pound load (22.7 kg) placed at 1 foot (305 mm) above its center.

Outdoor Poles and Brackets

RTA61 - Traditional Aluminum Pole

Pole Data

Pole Family	Catalog Number	Nominal Height (ft)	Nominal Height (m)	Tenon Section (in)	Tenon Section (mm)	Wall Thickness (in)	Wall Thickness (mm)	Weight (lbs)	Weight (kg)	EPA Rating 90 MPH (sq. ft.)	EPA Rating 110 MPH (sq. ft.)	EPA Rating 120 MPH (sq. ft.)	EPA Rating 150 MPH (sq. ft.)	Anchor Bolts (in)	Anchor Bolts (mm)
RTA61	RTA61F-10	10	3.05	4	102	0.125	3.2	44	97	20.43	13.62	11.39	7.11	3/4-20	19-508
RTA61	RTA61V-10	10	3.05	4	102	0.25	6.4	57	26	30	27.99	23.57	15.02	3/4-20	19-508
RTA61	RTA61F-11	11	3.35	4	102	0.125	3.2	46	21	17.88	11.8	9.83	6.08	3/4-20	19-508
RTA61	RTA61V-11	11	3.35	4	102	0.25	6.4	60	27	30	24.59	20.67	13.09	3/4-20	19-508
RTA61	RTA61F-12	12	3.66	4	102	0.125	3.2	47	21	15.75	10.3	8.54	5.2	3/4-20	19-508
RTA61	RTA61V-12	12	3.66	4	102	0.25	6.4	63	29	30	21.78	18.27	11.51	3/4-20	19-508
RTA61	RTA61F-13	13	3.97	4	102	0.125	3.2	49	22	13.97	9.01	7.45	4.44	3/4-20	19-508
RTA61	RTA61V-13	13	3.97	4	102	0.25	6.4	67	30	29.17	19.44	16.27	10.18	3/4-20	19-508
RTA61	RTA61F-14	14	4.27	4	102	0.125	3.2	50	23	12.47	7.93	6.51	3.79	3/4-20	19-508
RTA61	RTA61V-14	14	4.27	4	102	0.25	6.4	70	32	26.29	17.45	14.58	9.05	3/4-20	19-508
RTA61	RTA61F-15	15	4.57	4	102	0.125	3.2	52	24	11.14	6.99	5.69	3.24	3/4-20	19-508
RTA61	RTA61V-15	15	4.57	4	102	0.25	6.4	73	33	23.83	15.73	13.09	8.07	3/4-20	19-508

Specifications

Base cover

Decorative base cover made from cast-aluminum pieces mechanically assembled together with stainless steel hardware around base of the pole.

Finish

Color to be in accordance with the AAMA 2603 standard. Application of polyester powder coat paint (4 mils/100 microns) with ±1 mils/24 microns of tolerance. The Thermosetting resins provides a discoloration resistant finish in accordance with the ASTM D2244 standard, as well as luster retention in keeping with the ASTM D523 standard and humidity proof in accordance with the ASTM D2247 standard.

Outdoor Poles and Brackets

RTA61 - Traditional Aluminum Pole

Dimensions



