

iW Graze QLX Powercore

Performance linear exterior LED wall grazing luminaires with intelligent white light

Date: _____
 Type: _____
 Firm Name: _____
 Project: _____

iW Graze QLX Powercore is a high-performance, exterior linear luminaire perfect for surface illumination applications calling for a balance of cost and performance. It is designed to highlight architectural features ranging from surface textures and molding details to archways and windows. Graze Intelligent White luminaires offer channels of cool, neutral, and warm white LEDs to offer color temperatures ranging from 2700 K to 6500 K. Multiple luminaire lengths, beam angles, output levels, and power consumption levels support a large range of façade or surface illumination applications. Low-profile housing, connectorized cabling, a universal power input range, and direct line voltage operation make Graze luminaires easy to install and operate.

- Tailor light output to specific applications—Available in four standard lengths (1 ft, 2 ft, 3 ft, and 4 ft), four performance levels (MX, QLX, QLX 5W, and EC), and six standard 9° x 9°, 10° x 60°, 15° x 30°, 30° x 60°, 60° x 30°, and 90° x 90° (EC only) beam angles.
- Flexible integration—Graze's ultra-low profile lets it fit discretely into almost any layout, from simple to elaborate.



[Product page](#)

Beam Angle	9° x 9°, 10° x 60°, 15° x 30°, 30° x 60°, 60° x 30°
Lumens per foot*	624 to 673
Efficacy†	31.5 to 33.9
Color Temperature§	2700 K to 6500 K

Input Voltage	100 to 277 VAC, auto-ranging, 50/60 Hz
Housing Material	Extruded anodized aluminium
Approbations	UL/cUL, FCC Class A, CE, PSE, C-Tick
Environment	Dry/Damp/Wet Location, IP66
Applications	Wall Grazing, Wall Washing

Specification Sheets

PDF Download	Beam Angle	Lumens*	Efficacy†	CRI‡	Power	Weight	Item Number	12 NC
9° x 9° Beam Angle, 305 mm (1 ft)	9° x 9°	661	33.7	83	15 W	1 kg (2.1 lb)	523-000079-20	910503703664
9° x 9° Beam Angle, 610 mm (2 ft)	9° x 9°	1,322	33.7	83	30 W	2.1 kg (4.6 lb)	523-000079-25	910503703669
9° x 9° Beam Angle, 914 mm (3 ft)	9° x 9°	1,983	33.7	83	45 W	3.2 kg (7.1 lb)	523-000079-30	910503703674
9° x 9° Beam Angle, 1219 mm (4 ft)	9° x 9°	2,644	33.7	83	60 W	4.2 kg (9.3 lb)	523-000079-35	910503703679
10° x 60° Beam Angle, 305 mm (1 ft)	10° x 60°	624	31.5	83	15 W	1 kg (2.1 lb)	523-000079-21	910503703665
10° x 60° Beam Angle, 610 mm (2 ft)	10° x 60°	1,248	31.5	83	30 W	2.1 kg (4.6 lb)	523-000079-26	910503703670
10° x 60° Beam Angle, 914 mm (3 ft)	10° x 60°	1,872	31.5	83	45 W	3.2 kg (7.1 lb)	523-000079-31	910503703675
10° x 60° Beam Angle, 1219 mm (4 ft)	10° x 60°	2,496	31.5	83	60 W	4.2 kg (9.3 lb)	523-000079-36	910503703680



Specification Sheets (cont.)

PDF Download	Beam Angle	Lumens*	Efficacy [†]	CRI [‡]	Power	Weight	Item Number	I2 NC
15° x 30° Beam Angle, 305 mm (1 ft)	15° x 30°	673	33.7	83	15 W	1 kg (2.1 lb)	523-000079-22	910503703666
15° x 30° Beam Angle, 610 mm (2 ft)	15° x 30°	1,346	33.7	83	30 W	2.1 kg (4.6 lb)	523-000079-27	910503703671
15° x 30° Beam Angle, 914 mm (3 ft)	15° x 30°	2,019	33.7	83	45 W	3.2 kg (7.1 lb)	523-000079-32	910503703676
15° x 30° Beam Angle, 1219 mm (4 ft)	15° x 30°	2,692	33.7	83	60 W	4.2 kg (9.3 lb)	523-000079-37	910503703681
30° x 60° Beam Angle, 305 mm (1 ft)	30° x 60°	658	33.6	83	15 W	1 kg (2.1 lb)	523-000079-23	910503703667
30° x 60° Beam Angle, 610 mm (2 ft)	30° x 60°	1,316	33.6	83	30 W	2.1 kg (4.6 lb)	523-000079-28	910503703672
30° x 60° Beam Angle, 914 mm (3 ft)	30° x 60°	1,974	33.6	83	45 W	3.2 kg (7.1 lb)	523-000079-33	910503703677
30° x 60° Beam Angle, 1219 mm (4 ft)	30° x 60°	2,632	33.6	83	60 W	4.2 kg (9.3 lb)	523-000079-38	910503703682
60° x 30° Beam Angle, 305 mm (1 ft)	60° x 30°	658	33.9	83	15 W	1 kg (2.1 lb)	523-000079-24	910503703668
60° x 30° Beam Angle, 610 mm (2 ft)	60° x 30°	1,316	33.9	83	30 W	2.1 kg (4.6 lb)	523-000079-29	910503703673
60° x 30° Beam Angle, 914 mm (3 ft)	60° x 30°	1,974	33.9	83	45 W	3.2 kg (7.1 lb)	523-000079-34	910503703678
60° x 30° Beam Angle, 1219 mm (4 ft)	60° x 30°	2,632	33.9	83	60 W	4.2 kg (9.3 lb)	523-000079-39	910503703683

* 305 mm (1 ft) lumen output measurements comply with IES LM-79-08 testing procedures. 610 mm (2 ft), 914 mm (3 ft), and 1219 mm (4 ft) measurements are estimated based on the 305 mm (1 ft) measurements.

[†] Efficacy measurements are estimated based on the 305 mm (1 ft) measurements.

[‡] Correlated color temperature (CCT) complies with ANSI C78.377-2008 for the chromaticity of solid state lighting products.

[§] CRI refers to CRI Ra value, CRI R9 refers to R9 value in accordance with IESNA LM-79 standards.

